

Cable

Multiple Core

pro-POWER



Specifications:

One x 75Ω Video Core:

Conductor : 7/0.2mm copper strand
Insulation : PVC
Screen : Wound copper strand drain wire (32/0.15mm)
Colour : Yellow

Four x Signal/Aux Cores:

Conductor : 7/0.2mm copper strand
Insulation : PVC
Colours : Red, Blue, White and Green

Overall:

Screen : Aluminium sheath
Nominal diameter : 5mm
Nominal conductive cross-section : 0.22mm² each core
Insulation : PVC White
Reel Length (Metric) : 100m
No. of Conductors : 5
Screen Type Primary : Foil
Conductor Material : Copper
Primary Conductor Resistance : 75Ω

Part Number Table

Description	Part Number
Cable, Covert Camera, 100m	CB02515

Important Notice : This data sheet and its contents (the "Information") belong to the members of the Premier Farnell group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. pro-POWER is the registered trademark of the Group. © Premier Farnell plc 2012.

www.element14.com
www.farnell.com
www.newark.com
www.cpc.co.uk

pro-POWER