

**Productname :** MOUSSE STP ULTRA  
**Ref.Nr.:** BDS001411\_3\_20130214**Creationdate :** 14.02.13 Version : 1.0  
**Replaces:** AB403600**SECTION 1: Identification of the substance/mixture and of the company/undertaking****1.1. Product identifier****MOUSSE STP ULTRA**  
Aerosol**1.2. Relevant identified uses of the substance or mixture and uses advised against**

Sealants and Isolation

**1.3. Details of the supplier of the safety data sheet****CRC Industries Europe bvba**  
Touwslagerstraat 1  
9240 Zele  
Belgium  
Tel.: +32(0)52/45.60.11  
Fax.: +32(0)52/45.00.34  
E-mail : hse@crcind.com

Subsidiaries		Tel	Fax
CRC Industries Finland Oy	Asemanrinne 13, 08500 Lohja	+358/(19)32.921	+358/(19)383.676
CRC Industries France	6, avenue du marais, C.S. 90028, 95102 Argenteuil Cedex	01.34.11.20.00	01.34.11.09.96
CRC Industries Deutschland GmbH	Südring 9, D-76473 Iffezheim	(07229) 303.0	(07229)30 32 66
CRC INDUSTRIES IBERIA S.L.U.	GREMIO DEL CUERO-PARC.96, POLIGONO INDUSTRI. DE HONTORIA, 40195 SEGOVIA	0034/921.427.546	0034/921.436.270
CRC Industries Sweden	Kryptongatan 14, 431 53 Mölndal	0046/31 706 84 80	0046/31 27 39 91

**1.4. Emergency telephone number****CRC Industries Europe, Belgium:** Tel.: +32(0)52/45.60.11 (office hours)**SECTION 2: Hazards identification****2.1. Classification of the substance or mixture****Classification according to 67/548/EEC or 1999/45/EC:****Health:** not classified  
**Physical:** EXTREMELY FLAMMABLE  
**Environment:** not classified

Productname : MOUSSE STP ULTRA  
 Ref.Nr.: BDS001411\_3\_20130214

Creationdate : 14.02.13 Version : 1.0  
 Replaces: AB403600

## 2.2. Label elements

Warning symbol(s) : EXTREMELY FLAMMABLE



Risk-phrase(s) : None

Safety-phrase(s) :  
 S2: Keep out of the reach of children.  
 S3: Keep in a cool place.  
 S16: Keep away from sources of ignition - No smoking.  
 S46: If swallowed, seek medical advice immediately and show this container or label.  
 S51: Use only in well-ventilated areas.  
 S56: Dispose of this material and its container to hazardous or special waste collection point.

Extra label elements according to Aerosol Dispenser Directive 75/324/EC: Without adequate ventilation formation of explosive mixtures may be possible.

Pressurised container: protect from sunlight and do not expose to temperatures exceeding 50°C. Do not pierce or burn, even after use. Do not spray on a naked flame or any incandescent material.

## 2.3. Other hazards

None

# SECTION 3: Composition/information on ingredients

## 3.1. Substances

Not applicable.

## 3.2. Mixtures

Hazardous ingredient	CAS-nr.	EC-nr	w/w %	symbol	R-phrases*	Notes
isobutane (<= 0,1 % butadiene)	75-28-5	200-857-2	10-25	F+	12	
dimethyl ether	115-10-6	204-065-8	5-10	F+	12	A
Silane, ethenyltrimethoxy-	2768-02-7	220-449-8	5-10	Xn	R10,R20	
propane	74-98-6	200-827-9	5-10	F+	12	B
<b>Explanation notes</b>						
A : substance with Community workplace exposure limit						
B : substance with national established workplace exposure limit						

Hazardous ingredient	Registration number	CAS-nr.	EC-nr	w/w %	Hazard Class and Category	Hazard statement	Notes
isobutane (<= 0,1 % butadiene)		75-28-5	200-857-2	10-25	Flam. Gas 1, Press. Gas, Carc. 1A, Muta. 1B	H220,H350,H340	
dimethyl ether	01-2119472128-37	115-10-6	204-065-8	5-10	Flam. Gas 1, Press. Gas	H220,H280	A



**Productname :** MOUSSE STP ULTRA  
**Ref.Nr.:** BDS001411\_3\_20130214

**Creationdate :** 14.02.13 Version : 1.0  
**Replaces:** AB403600

propane		74-98-6	200-827-9	5-10	Flam. Gas 1, Press. Gas	H220	B
<b>Explanation notes</b>							
A : substance with Community workplace exposure limit							
B : substance with national established workplace exposure limit							

(\* Explanation phrases : see chapter 16)

## SECTION 4: First aid measures

### 4.1. Description of first aid measures

<b>Contact with eyes :</b>	If substance has got into eyes, immediately wash out with plenty of water Seek medical attention if irritation persists
<b>Contact with skin :</b>	Remove contaminated clothing immediately and drench affected skin with plenty of water. Then wash with soap and water Seek medical attention if irritation persists
<b>Inhalation :</b>	Fresh air, keep warm and at rest. Seek medical attention if ill effects occur
<b>Ingestion :</b>	If swallowed accidentally, do not induce vomiting and seek medical advice.

### 4.2. Most important symptoms and effects, both acute and delayed

<b>Inhalation :</b>	Excessive inhalation of solvent vapours may give rise to nausea, headaches and dizziness
<b>Ingestion :</b>	May cause gastrointestinal disturbances Symptoms : sore throat, abdominal pain, nausea, vomiting
<b>Skin contact :</b>	May cause irritation. Symptoms : redness and pain
<b>Eye contact :</b>	May cause irritation. Symptoms : redness and pain

### 4.3. Indication of any immediate medical attention and special treatment needed

<b>General Advice :</b>	If you feel unwell, seek medical advice (show the label where possible) If symptoms persist always call a doctor
-------------------------	---

## SECTION 5: Firefighting measures

### 5.1. Extinguishing media

foam, carbon dioxide or dry agent

### 5.2. Special hazards arising from the substance or mixture

Aerosols may explode if heated above 50°C  
 Forms hazardous decomposition products  
 CO,CO2



**Productname :** MOUSSE STP ULTRA  
**Ref.Nr.:** BDS001411\_3\_20130214

**Creationdate :** 14.02.13 Version : 1.0  
**Replaces:** AB403600

### 5.3. Advice for firefighters

Keep container(s) exposed to fire cool, by spraying with water  
In case of fire, do not breathe fumes

## SECTION 6: Accidental release measures

### 6.1. Personal precautions, protective equipment and emergency procedures

Shut off all ignition sources  
Ensure adequate ventilation  
Wear suitable protective clothing and gloves.

### 6.2. Environmental precautions

Do not allow to enter public sewers and watercourses  
If polluted water reaches drainage systems or water courses, immediately inform appropriate authorities

### 6.3. Methods and material for containment and cleaning up

Absorb spillage in suitable inert material  
Place in appropriate container

### 6.4. Reference to other sections

For further information see section 8

## SECTION 7: Handling and storage

### 7.1. Precautions for safe handling

Keep away from heat and sources of ignition  
Take precautionary measures against static discharges  
Equipment should be earthed  
Use explosion-proof electrical/ventilating/lighting/.../equipment.  
Use only non-sparking tools.  
Do not breathe aerosols or vapours.  
Ensure adequate ventilation  
Avoid contact with skin and eyes.  
Wash thoroughly after use  
Wear protective gloves/protective clothing/eye protection/face protection.

### 7.2. Conditions for safe storage, including any incompatibilities

Pressurized container : protect from sunlight and do not expose to temperatures exceeding 50°C.  
Keep in a cool, dry, well ventilated place  
Keep out of reach of children.

### 7.3. Specific end use(s)



**Productname :** MOUSSE STP ULTRA  
**Ref.Nr.:** BDS001411\_3\_20130214  
**Creationdate :** 14.02.13 Version : 1.0  
**Replaces:** AB403600

Sealants and Isolation

## SECTION 8: Exposure controls/personal protection

### 8.1. Control parameters

#### Exposure limits :

Hazardous ingredient	CAS-nr.	method	
<b>EU established exposure limits:</b>			
dimethyl ether	115-10-6	TWA	1000 ppm
<b>National established exposure limits, United Kingdom</b>			
dimethyl ether	115-10-6	TWA	400 ppm
		STEL	500 ppm

### 8.2. Exposure controls

<b>Control procedures :</b>	Ensure adequate ventilation Keep away from heat and sources of ignition Take precautionary measures against static discharges
<b>Personal protection :</b>	Take precautions to avoid contact with skin and eyes when handling the product. Ensure adequate ventilation
<b>inhalation :</b>	In case of insufficient ventilation, wear suitable respiratory equipment. Air purifying respirator equipped with organic gas/vapor cartridge (type A or AX)
<b>hands and skin :</b>	Wear suitable protective gloves against chemicals (nitrile)
<b>eyes :</b>	Wear safety goggles.

## SECTION 9: Physical and chemical properties

### 9.1. Information on basic physical and chemical properties

(for aerosols data for the product without propellant)

<b>Apperance : physical state :</b>	Liquid under pressure.
<b>colour :</b>	White.
<b>odour :</b>	Characteristic odor.
<b>pH :</b>	Not applicable.
<b>Boiling point/range :</b>	Not available.
<b>Flash point :</b>	- 97 °C
<b>Evaporation rate :</b>	Not available.
<b>Explosion limits : upper limit :</b>	8.5 %
<b>lower limit :</b>	1.8 %
<b>Vapour pressure :</b>	Not available.
<b>Relative density :</b>	0.90 g/cm <sup>3</sup> (@ 20°C).



**Productname :** MOUSSE STP ULTRA  
**Ref.Nr.:** BDS001411\_3\_20130214

**Creationdate :** 14.02.13 Version : 1.0  
**Replaces:** AB403600

**Solubility in water :** Insoluble in water  
**Auto-ignition :** > 200 °C  
**Viscosity :** Not available.

## 9.2. Other information

# SECTION 10: Stability and reactivity

## 10.1. Reactivity

No hazardous reactions known if used for its intended purpose

## 10.2. Chemical stability

Stable

## 10.3. Possibility of hazardous reactions

No hazardous reactions known if used for its intended purpose

## 10.4. Conditions to avoid

Avoid overheating

## 10.5. Incompatible materials

Strong oxidising agent

## 10.6. Hazardous decomposition products

CO,CO2

# SECTION 11: Toxicological information

## 11.1. Information on toxicological effects

**Inhalation :** Inhalation of solvent vapours may give rise to nausea, headaches and dizziness  
**Ingestion :** May cause gastrointestinal disturbances  
**Skin contact :** Prolonged skin contact will result in defatting of the skin, leading to irritation, and in some cases, dermatitis  
Repeated exposure may cause skin dryness or cracking.  
**Eye contact :** May cause irritation.

## Toxicological data :

No information available



Productname : MOUSSE STP ULTRA  
Ref.Nr.: BDS001411\_3\_20130214

Creationdate : 14.02.13 Version : 1.0  
Replaces: AB403600

## SECTION 12: Ecological information

### 12.1. Toxicity

not classified

### Ecotoxicological data:

No information available

### 12.2. Persistence and degradability

No experimental data available

### 12.3. Bioaccumulative potential

No experimental data available

### 12.4. Mobility in soil

Insoluble in water

### 12.5. Results of PBT and vPvB assessment

No information available

### 12.6. Other adverse effects

No experimental data available

## SECTION 13: Disposal considerations

### 13.1. Waste treatment methods

**Product :** This material and its container must be disposed of in a safe way.  
Do not discharge into drains or the environment, dispose to an authorised waste collection point.

**Contaminated packaging :** Disposal should be in accordance with local, state or national legislation

## SECTION 14: Transport information

### 14.1. UN number

UN-number : 1950



**Productname :** MOUSSE STP ULTRA  
**Ref.Nr.:** BDS001411\_3\_20130214

**Creationdate :** 14.02.13 Version : 1.0  
**Replaces:** AB403600

#### 14.2. UN proper shipping name

Proper shipping name: AEROSOLS

#### 14.3. Transport hazard class(es)

Class: 2.1  
ADR/RID - Classification code: 5F

#### 14.4. Packing group

Packing group: Not applicable.

#### 14.5. Environmental hazards

ADR/RID - Environmentally hazardous: No  
IMDG - Marine pollutant: No  
IATA/ICAO - Environmentally hazardous: No

#### 14.6. Special precautions for user

ADR/RID - Tunnelcode: (D)  
IMDG - Ems: F-D, S-U  
IATA/ICAO - PAX: 203  
IATA/ICAO - CAO: 203

#### 14.7. Transport in bulk according to Annex II of MARPOL73/78 and the IBC Code

Not applicable.

### SECTION 15: Regulatory information

#### 15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture

The Safety Data Sheet is compiled according to the current European requirements.  
Dir. 2008/47/EC amendment of the aerosol dispenser directive 75/324/EEC.  
EU-directive 99/45/EC  
Regulation (EC) No 1272/2008  
Regulation (EC) No 1907/2006 (REACH)

#### 15.2. Chemical safety assessment

No information available

### SECTION 16: Other information





**Productname :** MOUSSE STP ULTRA  
**Ref.Nr.:** BDS001411\_3\_20130214

**Creationdate :** 14.02.13 Version : 1.0  
**Replaces:** AB403600

---

\*Explanation risk-phrases: R12: Extremely flammable.  
RR10  
R20: Harmful by inhalation.

\*Explanation hazard statements: H220 : Extremely flammable gas.  
H280 : Contains gas under pressure; may explode if heated.  
H340 : May cause genetic defects .  
H350 : May cause cancer .

This product should be stored, handled and used in accordance with good industrial hygiene practices and in conformity with any legal regulation.

The information contained herewith is based on the present state of our knowledge and is intended to describe our products from the point of view of safety requirements. It does not guarantee any specific properties. Apart from any fair dealing for purposes of study, research and review of health, safety and environmental risks, no part of these documents may be reproduced by any process without written permission from CRC.

