



SECTION 1: Identification of the substance/mixture and of the company/undertaking

Product identifier

Name of product Repair Stick Copper (GB)
Code-Nr. 105300

Relevant identified uses of the substance or mixture and uses advised against

Recommended intended purpose(s)
2-Component Epoxy Resins

Details of the supplier of the safety data sheet

Manufacturer/distributor WEICON GmbH & Co. KG
Königsberger Straße 255, DE-48157 Münster
Postbox 84 60, DE-48045 Münster
Phone ++49(0)251 / 9322 - 0, Fax ++49(0)251 / 9322-244
E-Mail : info@weicon.de
Internet : www.weicon.de

Advice

Abteilung Angebote, Verkauf, Export
Phone ++49(0)251 / 9322 - 0
E-mail (competent person):
info@weicon.de

Emergency telephone number

Emergency advice Giftnotruf Bonn: Bei Vergiftungen (in case of poisoning)
Phone ++49(0)228-19 240

SECTION 2: Hazards identification

Classification of the substance or mixture

Classification according to 67/548/EEC or 1999/45/EC

Xi; R36/38
R43
R52/53

R-phrases

36/38 Irritating to eyes and skin.
43 May cause sensitisation by skin contact.
52/53 Harmful to aquatic organisms, may cause long-term adverse effects in the aquatic environment.

Label elements

Labelling according to 67/548/EEC or 1999/45/EC

Remarks for labelling

The product is classified and labelled in accordance with EC directives/German regulations on dangerous substances.

Xi Irritant

R-phrases

36/38 Irritating to eyes and skin.
43 May cause sensitisation by skin contact.
52/53 Harmful to aquatic organisms, may cause long-term adverse effects in the aquatic environment.

S-phrases

2 Keep out of the reach of children.
28 After contact with skin, wash immediately with plenty of water and soap.
37/39 Wear suitable gloves and eye/face protection.
46 If swallowed, seek medical advice immediately and show this container or label.
51 Use only in well-ventilated areas.



Hazardous ingredients for labeling

reaction product: bisphenol-A-(epichlorhydrin) epoxy resin (number average molecular weight \leq 700)

Special rules for supplemental label elements for certain mixtures

Contains epoxy constituents. See information supplied by the manufacturer.

Other hazards

No information available.

SECTION 3: Composition/ information on ingredients

Mixtures

Hazardous ingredients

CAS No	EC No	Name	[% weight]	Classification according to 67/548/EEC
90-72-2	202-013-9	2,4,6-tris(dimethylaminomethyl)phenol	1 - 10	Xn R22; Xi R36/38
25068-38-6	500-033-5	reaction product: bisphenol-A-(epichlorhydrin) epoxy resin (number average molecular weight \leq 700)	15 - 24	Xi R36/38; R43; N R51-53

CAS No	EC No	Name	[% weight]	Classification according to Regulation (EC) No 1272/2008 [CLP/GHS]
90-72-2	202-013-9	2,4,6-tris(dimethylaminomethyl)phenol	1 - 10	Acute Tox. 4, H302 / Eye Irrit. 2, H319 / Skin Irrit. 2, H315
25068-38-6	500-033-5	reaction product: bisphenol-A-(epichlorhydrin) epoxy resin (number average molecular weight \leq 700)	15 - 24	Eye Irrit. 2, H319 / Skin Irrit. 2, H315 / Skin Sens. 1, H317 / Aquatic Chronic 2, H411

REACH

CAS No	Name	REACH registration number
25068-38-6	reaction product: bisphenol-A-(epichlorhydrin) epoxy resin (number average molecular weight \leq 700)	01-2119456619-26-xxxx

Description

2-component epoxy sticks

SECTION 4: First aid measures

Description of first aid measures

General information

Remove contaminated soaked clothing immediately.

In case of inhalation

In the event of symptoms refer for medical treatment.

In case of skin contact

Do not use solvents or thinners.

In case of contact with skin wash off with water.

In case of eye contact

May cause superficial burns.

In case of contact with eyes rinse thoroughly with water.

Call for a doctor immediately.

In case of ingestion

Do not induce vomiting.

Call for a doctor immediately.

If swallowed by mistake drink plenty of water and seek medical treatment.

Rinse out mouth thoroughly with water.



Most important symptoms and effects, both acute and delayed

No information available.

Indication of any immediate medical attention and special treatment needed

Treatment (Advice to doctor)

In the event of pulmonary irritation treat initially with dexamethasone metered-dose aerosol.

SECTION 5: Firefighting measures

Extinguishing media

Suitable extinguishing media

Foam
Dry fire-extinguishing substance
Carbon dioxide
water mist

Special hazards arising from the substance or mixture

Fire gas of organic material has to be classed invariably as respiratory poison.
Nitrogen oxides (NO_x)
Carbon monoxide (CO)

Advice for firefighters

Special protective equipment for fire-fighters

Use breathing apparatus with independent air supply.
Fire-fighting operations, rescue and clearing work under effect of combustion and smoulder gases just may be done with breathing apparatus.

SECTION 6: Accidental release measures

Personal precautions, protective equipment and emergency procedures

Ensure adequate ventilation.
Remove persons to safety.
Use personal protective clothing.

Environmental precautions

Inform pollution control authorities if product gets into the sewerage systems or open waters.
Do not discharge into the drains or bodies of water..

Methods and material for containment and cleaning up

Send in suitable containers for recovery or disposal.
Take up with absorbent material.

Reference to other sections

No information available.

SECTION 7: Handling and storage

Precautions for safe handling

Advice on safe handling

Care for thoroughly room ventilation, if necessary use in well ventilated area with local exhaust ventilation at workplace.

Advice on protection against fire and explosion

Pay attention to general rules of internal fire prevention.

Conditions for safe storage, including any incompatibilities

Requirements for storage rooms and vessels

Keep in closed original container.

Further information on storage conditions

Protect from direct solar radiation.
Store container at cool and aired place.
Store in a dry place.
Protect from heat/overheating.



Specific end use(s)
No information available.

SECTION 8: Exposure controls/personal protection

Control parameters
No information available.

Exposure controls

Respiratory protection

In case of insufficient ventilation or long-term effect use breathing apparatus.

Hand protection

In the cases of special applications, it is recommended to check the chemical resistance with the manufacturer of the gloves.
Glove material specification [make/type, thickness, permeation time/life, wetting resistance]: natural rubber, 0,6mm; 480min; 60min;

Chemical protective gloves must be chosen carefully in view of their design and depending on the dependence on the concentration and amounts of dangerous goods used in the specific working tasks.

Eye protection

safety goggles
Face shield

Skin protection

protective clothing

General protective measures

Avoid contact with eyes and skin
Do not inhale gases/vapours/aerosols.

Hygiene measures

At work do not eat, drink, smoke or take drugs.
Wash hands before breaks and after work.

SECTION 9: Physical and chemical properties

Information on basic physical and chemical properties

Form

pasty

Colour

various

Odour

hardly noticeable

Important health, safety and environmental information

	Value	Temperature	at	Method	Remark
Flash point	> 200 °C				
Density	not determined				
Solubility in water					insoluble

Other information

No information available.

SECTION 10: Stability and reactivity

Reactivity

No information available.

Chemical stability

No information available.



Possibility of hazardous reactions

No information available.

Conditions to avoid

No information available.

Incompatible materials

Materials to avoid

Reactions with strong acids and alkalis.
Reactions with strong oxidising agents.

Hazardous decomposition products

Carbon monoxide and carbon dioxide.
Nitrous oxides (NOx)
Toxic gases/vapours

SECTION 11: Toxicological information

Information on toxicological effects

Acute toxicity/Irritability/Sensitization

	Value/Validation	Species	Method	Remark
Irritability skin	irritant	rabbit		
Irritability eye	irritant	rabbit eye		
Skin sensitization	sensitizing			

Experiences made from practice

Sensitization through skin contact possible.

Additional information

The product is to be handled with the caution usual with chemicals.
Other hazardous properties may not be excluded.

SECTION 12: Ecological information

Toxicity

No information available.

Persistence and degradability

No information available.

Bioaccumulative potential

No information available.

Mobility in soil

No information available.

Results of PBT and vPvB assessment

This substance does not meet the PBT/vPvB criteria of REACH, annex XIII.

Other adverse effects

General regulation

Do not allow uncontrolled leakage of product into the environment.
Product is not allowed to be discharged into aquatic environment.



SECTION 13: Disposal considerations

Waste treatment methods

Recommendations for the product

Cured material may be considered inert and disposed of as builders waste.
Remove in accordance with local official regulations.

Recommendations for packaging

Untampered packaging may be treated as household waste.
Packaging that cannot be cleaned should be disposed of like the product.

SECTION 14: Transport information

Transport/further information

No dangerous goods as defined by the transport regulations - ADR/RID, IMDG, ICAO/IATA-DGR.

Special precautions for user

No information available.

Transport in bulk according to Annex II of MARPOL 73/78 and the IBC Code

not applicable

SECTION 15: Regulatory information

Safety, health and environmental regulations/legislation specific for the substance or mixture

VOC standard

Remark

Daten separat anfragen / Request data separately.

Chemical Safety Assessment

Chemical safety assessments for substances in this mixture were not carried out.

SECTION 16: Other information

Recommended uses and restrictions

National and local regulations concerning chemicals shall be observed.

Further information

The information contained herein is based on the state of our knowledge. It characterizes the product with regard to the appropriate safety precautions. It does not represent a guarantee of the properties of the product.

Wording of the R/H-phrases specified in chapter 3 (not the classification of the mixture!)

R 22 Harmful if swallowed.

R 36/38 Irritating to eyes and skin.

R 43 May cause sensitisation by skin contact.

R 51/53 Toxic to aquatic organisms, may cause long-term adverse effects in the aquatic environment.

H302 Harmful if swallowed.

H315 Causes skin irritation.

H317 May cause an allergic skin reaction.

H319 Causes serious eye irritation.

H411 Toxic to aquatic life with long lasting effects.