


M30 Connectors

Female Crimp Housing and Contacts

A range of 1.25mm pitch male and female connectors, for cable-to-board applications.


- ❖ Loose or reeled contacts.
- ❖ Suitable for use with male connectors shown on page 102.



HOUSING

CALCULATION

A	$B + 2.9$
B	$1.25 \times (\text{No. of contacts per row} - 1)$



HAND CRIMP TOOL




ORDER CODE

Z30-021

❖ Instruction sheets available at www.harwin.com/downloads/instructions


CONTACTS



TYPE	AWG	ORDER CODE
Reeled	26 - 30	M30-1050046
Loose	26 - 30	M30-1060046

- ❖ Order codes for reeled contacts refer to one reel of 10,000 contacts.
- ❖ Order codes for loose contacts refer to one pack of 100 contacts.

WIRE STRIPPING DETAILS



HOW TO ORDER

M30 - 1 XX XX XX

SERIES CODE

TYPE

05	Reeled contact
06	Loose contact
10	Housing

FINISH

00	Housing	
46	Tin (Contacts)	

NO. OF CONTACTS PER ROW

02 to 15	Housing
00	Contacts

All dimensions in mm.