



For more Information  
please call

1-800-Belden1

### General Description:

Connecting Tool

### Usage (Overall)

**Suitable Applications:** To terminate cables, pigtails or cross-connect wires on any 110 product.

**Related Parts:** 110 Connector, Tool Pouch, Pigtails, Cross-Connect Wire.

### Physical Characteristics (Connectivity)

#### Dimensions

Dimensions:

Height (in.)	Width (in.)	Length (in.)
1.500	1.000	6.250

#### Materials

Materials:

Description	Material
Handle	Plastic
Blade	Metal

#### Color

**Color:** Black

#### Weight

**Weight:** 0.250 lbs.

#### Packaging

**Packaging:** Individual packaged in carton.

### Mechanical Characteristics (Connectivity)

**Storage Temperature Range:** -40°C To +70°C

**Installation Temperature Range:** -10°C To +60°C

### Applicable Specifications and Agency Compliance (Overall)

#### Suitability

**Suitability - Indoor:** Yes - Indoor

### Transmission Characteristics (Connectivity)

### Notes (Overall)

**Notes:** Visit our web site at <http://www.belden.com>

#### Product Family

### Put Ups and Colors:

Item #	Putup	Ship Weight	Color	Notes	Item Desc
AX100749	1 EA	0.364 LB			110 TOOL ASSEMBLY

### Test Reports

#### a) UL

- i) UL Test Reports are available on-line through the UL Client Document Access web portal.
- ii) UL Inspection Reports are also available through the UL Client Document Access web portal.

#### b) CSA

- i) CSA "Descriptive Report and Test Results" documents are available on the CSA Gateway Portal.
- ii) CSA Inspection Reports are maintained on the CSA issued 'flash drive' at each manufacturing location.

\* other test data may be available if requested at time of order.

Revision Number: 1    Revision Date: 08-03-2010

© 2012 Belden, Inc.  
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.