# **Detailed Specifications & Technical Data**

# **ENGLISH MEASUREMENT VERSION**



# 9259 Coax - 75 Ohm Coax

For more Information please call

1-800-Belden1



# **General Description:**

22 AWG stranded (7x30) .030" bare copper conductor, foam polyethylene insulation, bare copper braid shield (95% coverage), PVC jacket.

1

# **Physical Characteristics (Overall)**

# Conductor

#### AWG:

# Coax	AWG	Stranding	<b>Conductor Material</b>	Dia. (in.)
1	22	7x30	BC - Bare Copper	.030

Total Number of Conductors:

#### Insulation

#### **Insulation Material:**

Insulation Material	Dia. (in.)
FPE - Foam Polyethylene	.146

#### **Outer Shield**

### **Outer Shield Material:**

Type	Outer Shield Material	Coverage (%)
Braid	BC - Bare Copper	95

### **Outer Jacket**

### **Outer Jacket Material:**

Outer Jacket Material
PVC - Polyvinyl Chloride

### **Overall Cable**

Overall Nominal Diameter: 0.241 in.

# **Mechanical Characteristics (Overall)**

Operating Temperature Range:	-40°C To +80°C	
Non-UL Temperature Rating:	80°C	
Bulk Cable Weight:	33 lbs/1000 ft.	
Max. Recommended Pulling Tension:	65 lbs.	
Min. Bend Radius/Minor Axis:	2.500 in.	

# **Applicable Specifications and Agency Compliance (Overall)**

# **Applicable Standards & Environmental Programs**

NEC/(UL) Specification:	CM		
CEC/C(UL) Specification:	CM		
AWM Specification:	UL Style 1354 (30 V 80°C)		
EU CE Mark:	Yes		
EU Directive 2000/53/EC (ELV):	Yes		
EU Directive 2002/95/EC (RoHS):	Yes		
EU RoHS Compliance Date (mm/dd/yyyy):	01/01/2004		

Page 1 of 3 12-30-2012

# **Detailed Specifications & Technical Data**





# 9259 Coax - 75 Ohm Coax

EU Directive 2002/96/EC (WEEE):	Yes
EU Directive 2003/11/EC (BFR):	Yes
CA Prop 65 (CJ for Wire & Cable):	Yes
MII Order #39 (China RoHS):	Yes
RG Type:	59/U
Flame Test	
UL Flame Test:	UL1685 UL Loading
Suitability	
Suitability - Indoor:	Yes
Suitability - Outdoor:	Yes
Plenum/Non-Plenum	
Plenum (Y/N):	No
Plenum Number:	89259 or 82259

# **Electrical Characteristics (Overall)**

Nom. Characteristic Impedance:



Nom. Inductance:



Nom. Capacitance Conductor to Shield:



Nominal Velocity of Propagation:



Nominal Delay:



Nom. Conductor DC Resistance:



**Nominal Outer Shield DC Resistance:** 

DCR @ 20°C (Ohm/1000 ft) 2.6

# Nom. Attenuation:

Freq. (MHz)	Attenuation (dB/100 ft.)
1	.30
5	.65
10	.90
50	2.1
100	3.0
200	4.5
400	6.6
700	8.9
900	10.1
1000	10.9

Max. Operating Voltage - UL:

Voltage 300 V RMS

Page 2 of 3 12-30-2012

# **Detailed Specifications & Technical Data**

#### **ENGLISH MEASUREMENT VERSION**



9259 Coax - 75 Ohm Coax

# **Notes (Overall)**

Notes: For CCTV Applications.

# **Put Ups and Colors:**

Item #	Putup	Ship Weight	Color	Notes	Item Desc
9259 010U1000	1,000 FT	35.000 LB	BLACK		#22 PE RG 59/U TYPE
9259 010U500	500 FT	18.000 LB	BLACK		#22 PE RG 59/U TYPE
9259 010100	100 FT	4.100 LB	BLACK		#22 PE RG 59/U TYPE
9259 0101000	1,000 FT	37.000 LB	BLACK	С	#22 PE RG 59/U TYPE
9259 010500	500 FT	18.500 LB	BLACK	С	#22 PE RG 59/U TYPE
9259 0105000	5,000 FT	180.000 LB	BLACK	С	#22 PE RG 59/U TYPE

#### Notes:

C = CRATE REEL PUT-UP.

# **Test Reports**

i) UL Test Reports are available on-line through the UL Client Document Access web portal.

ii) UL Inspection Reports are also available through the UL Client Document Access web portal.

b) CŚA

i) CSA "Descriptive Report and Test Results" documents are available on the CSA Gateway Portal.

ii) CSA Inspection Reports are maintained on the CSA issued 'flash drive' at each manufacturing location.

Revision Number: 1 Revision Date: 05-14-2007

© 2012 Belden, Inc All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not

Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

Belden declares this product to be in compliance with EU LVD (Low Voltage Directive 73/23/EEC), as amended by directive 93/68/EEC.

<sup>\*</sup> other test data may be available if requested at time of order.