

**Surface Mount TRANSZORB® Transient Voltage Suppressors**

DO-214AA (SMBJ)

FEATURES

- Unidirectional polarity only
- Peak pulse power: 600 W (10/1000 μ s)
- Excellent clamping capability
- Very fast response time
- Meets MSL level 1, per J-STD-020C, LF max peak of 260 °C
- Solder Dip 260 °C, 40 seconds
- Component in accordance to RoHS 2002/95/EC and WEEE 2002/96/EC

**TYPICAL APPLICATIONS**

Use in sensitive electronics protection against voltage transients induced by inductive load switching and lighting on ICs, MOSFET, signal lines of sensor units specifically for protecting 3.3 V supplied sensitive equipment against transient overvoltages.

MECHANICAL DATA

Case: DO-214AA (SMBJ)

Epoxy meets UL 94V-0 flammability rating

Terminals: Matte tin plated leads, solderable per J-STD-002B and JESD22-B102D

E3 suffix for commercial grade, HE3 suffix for high reliability grade (AEC Q101 qualified)

Polarity: Color band denotes cathode end

MAJOR RATINGS AND CHARACTERISTICS

$V_{(BR)}$	3.3 V
P_{PPM}	600 W
I_{FSM}	60 A
T_j max.	175 °C

MAXIMUM RATINGS ($T_A = 25$ °C unless otherwise noted)

PARAMETER	SYMBOL	VALUE	UNIT
Peak pulse power dissipation ^(1,2)	P_{PPM}	600	W
Peak pulse current with a 10/1000 μ s waveform (see Fig. 1)	I_{PPM}	50	A
Peak pulse current with a 8/20 waveform (see Fig. 1)	I_{PPM}	200	A
Non repetitive peak forward surge current 8.3 ms single half sine-wave ⁽²⁾	I_{FSM}	60	A
Power dissipation on infinite heatsink, $T_L = 75$ °C	$P_{M(AV)}$	5	W
Operating junction and storage temperature range	T_J, T_{STG}	- 65 to + 175	°C

Note:

(1) Non-repetitive current pulse, per Fig. 1

(2) Mounted on 0.2 x 0.2" (5.0 x 5.0 mm) copper pads to each terminal

ELECTRICAL CHARACTERISTICS ($T_A = 25$ °C unless otherwise noted)

DEVICE TYPE	DEVICE MARKING CODE	BREAKDOWN VOLTAGE $V_{(BR)}$ AT I_T		MAXIMUM REVERSE LEAKAGE CURRENT I_R AT V_{WM}		MAXIMUM CLAMPING VOLTAGE V_C AT I_{PPM}		MAXIMUM CLAMPING VOLTAGE V_C AT I_{PPM}		TYPICAL TEMP. COEFFICIENT OF $V_{(BR)}$	TYPICAL JUNCTION CAPACITANCE C_J AT 0 V, 1 MHz
		MIN		MAX		10/1000 μ s		8/20 μ s			
		V	mA	μ A	V	V	A	V	A		
SMBJ3V3	KC	4.1	1.0	200	3.3	7.3	50	10.3	200	- 5.3	5200

THERMAL CHARACTERISTICS ($T_A = 25\text{ }^\circ\text{C}$ unless otherwise noted)			
PARAMETER	SYMBOL	VALUE	UNIT
Typical thermal resistance, junction to lead ⁽¹⁾	$R_{\theta JL}$	20	$^\circ\text{C/W}$
Typical thermal resistance, junction to ambient ⁽²⁾	$R_{\theta JA}$	100	

Note:

- (1) Thermal resistance from junction to lead - Mounted on 0.2 x 0.2" (5.0 x 5.0 mm) copper pads to each terminal
- (2) Thermal resistance from junction to ambient - Mounted on the recommended P.C.B. pad layout

ORDERING INFORMATION				
PREFERRED P/N	UNIT WEIGHT (g)	PREFERRED PACKAGE CODE	BASE QUANTITY	DELIVERY MODE
SMBJ3V3-E3/52	0.096	52	750	7" Diameter Plastic Tape & Reel
SMBJ3V-E3/5B	0.096	5B	3200	13" Diameter Plastic Tape & Reel

RATINGS AND CHARACTERISTICS CURVES

($T_A = 25\text{ }^\circ\text{C}$ unless otherwise noted)




Figure 1. Pulse Waveform




Figure 3. Relative Variation of Leakage Current vs. Junction Temperature




Figure 2. Peak Pulse Power Rating Curve




Figure 4. Clamping Voltage vs. Peak Pulse Current (T_j initial = $25\text{ }^\circ\text{C}$)




Figure 5. Typical Junction Capacitance




Figure 7. Typical Peak Forward Voltage Drop vs. Peak Forward Current





Figure 6. Typical Transient Thermal Impedance

PACKAGE OUTLINE DIMENSIONS in inches (millimeters)




Notice

Specifications of the products displayed herein are subject to change without notice. Vishay Intertechnology, Inc., or anyone on its behalf, assumes no responsibility or liability for any errors or inaccuracies.

Information contained herein is intended to provide a product description only. No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document. Except as provided in Vishay's terms and conditions of sale for such products, Vishay assumes no liability whatsoever, and disclaims any express or implied warranty, relating to sale and/or use of Vishay products including liability or warranties relating to fitness for a particular purpose, merchantability, or infringement of any patent, copyright, or other intellectual property right.

The products shown herein are not designed for use in medical, life-saving, or life-sustaining applications. Customers using or selling these products for use in such applications do so at their own risk and agree to fully indemnify Vishay for any damages resulting from such improper use or sale.