



Main

Range of product	LT3
Device short name	LT3SA
Product or component type	Thermistor protection units

Complementary

Control circuit voltage	115...230 V AC 50/60 Hz
Control circuit voltage limits	0.85...1.1 U _c
Contacts type and composition	1 NC + 1 NO dual voltage
[I _{th}] conventional free air thermal current	5 A output control relay
[U _i] rated insulation voltage	500 V AC output control relay
[U _e] rated operational voltage	250 V AC 50/60 Hz output control relay
Signalling function	Fault indication Voltage indication
Reset	Automatic reset
Probe interchangeability	Label mark A IEC 60034-11
Hold-in power consumption W	≥ 1 W
Hold-in power consumption VA	< 2,5 VA
Resistance	1500...1650 Ohm reset 2700...3100 Ohm tripping
Number of probes	≤ 6
Input voltage	< 2.5 V 1500 Ohm for probe < 7.5 V IEC 60034-11 4000 Ohm for probe
Short circuit detection resistance	< 20 Ohm
Condition of use	Connection of probes 500 m ≥ 1,5 mm ² Connection of probes 400 m ≥ 1 mm ²
[U _{imp}] rated impulse withstand voltage	2,5 kV
Operational power in VA	100 VA 220 V 500000 cycles
Breaking capacity	2 A DC-13 24 V DC 3 A AC-16 250 V AC 6 A AC-16 120 V AC
Connections - terminals	Cage type connector power circuit 2 0,75...2,5 mm ² flexible with Cage type connector power circuit 1 0,75...2,5 mm ² flexible with Cage type connector power circuit 1 1...2,5 mm ² flexible without Cage type connector power circuit 2 1...2,5 mm ² flexible without Cage type connector power circuit 2 0,75...2,5 mm ² solid with Cage type connector power circuit 1 0,75...2,5 mm ² solid with Cage type connector power circuit 1 1...2,5 mm ² solid without Cage type connector power circuit 2 1...2,5 mm ² solid without
Tightening torque	0,8 N.m
Height	100 mm
Width	22,5 mm
Depth	100 mm
Product weight	0,22 kg

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Environment

Standards	IEC 60034-11 VDE 0660
Product certifications	LROS (Lloyds register of shipping)
IP degree of protection	IP20 IEC 60529 IP20 VDE 0106
Ambient air temperature for operation	-25...60 °C
Ambient air temperature for storage	-40...85 °C IEC 60068-2-1 -40...85 °C IEC 60068-2-2
Operating altitude	> 1500...3000 m with derating in temperature ≤ 1500 m without derating in temperature
Vibration resistance	1 gn 25...150 Hz IEC 60068-2-6 2.5 gn 2...25 Hz IEC 60068-2-6
Shock resistance	5 gn 11 ms IEC 60068-2-27
Electromagnetic compatibility	Immunity to microbreaks and voltage drops IEC 61000-4-11 Resistance to electrostatic discharge level 3 IEC 61000-4-2 Resistance to fast transient level 3 IEC 61000-4-4 Surge resistance 1.2/50-8/20 level 4 IEC 61000-4-5 Susceptibility to electromagnetic fields level 3 IEC 61000-4-3
RoHS EUR conformity date	0844
RoHS EUR status	Compliant