



SAFETY DATA SHEET HEADSET CLENE

SECTION 1: IDENTIFICATION OF THE SUBSTANCE/MIXTURE AND OF THE COMPANY/UNDERTAKING

1.1. Product identifier

Product name HEADSET CLENE
Product No. HSC
AHSC050
ZA

1.2. Relevant identified uses of the substance or mixture and uses advised against

Identified uses Office Equipment Cleaning Product
Uses advised against No specific uses advised against are identified.

1.3. Details of the supplier of the safety data sheet

Supplier AF INTERNATIONAL. A division of HK
WENTWORTH LTD
ASHBY PARK
COALFIELD WAY
ASHBY de la ZOUCH
LEICESTERSHIRE. LE65 1JR
UNITED KINGDOM
+44 (0) 1530 419600
+44 (0) 1530 416640
info@hkw.co.uk

1.4. Emergency telephone number

+44 (0)1530 419600 between 8.30am - 5.00pm Mon – Fri

SECTION 2: HAZARDS IDENTIFICATION

2.1. Classification of the substance or mixture

Classification (1999/45/EEC) Not classified.

2.2. Label elements

Risk Phrases

NC Not classified.

2.3. Other hazards

SECTION 3: COMPOSITION/INFORMATION ON INGREDIENTS

3.2. Mixtures

PROPAN-2-OL	5-10%
CAS-No.: 67-63-0	EC No.: 200-661-7
Classification (EC 1272/2008) Flam. Liq. 2 - H225 Eye Irrit. 2 - H319 STOT SE 3 - H336	Classification (67/548/EEC) F;R11 Xi;R36 R67

The Full Text for all R-Phrases and Hazard Statements are Displayed in Section 16.

Composition Comments

Ingredients not listed are classified as non-hazardous or at a concentration below reportable levels.

HEADSET CLENE

SECTION 4: FIRST AID MEASURES

4.1. Description of first aid measures

Inhalation

Due to the small packaging the risk of inhalation is minimal.

Ingestion

Due to the small packaging the risk of ingestion is minimal. Rinse mouth thoroughly. Get medical attention.

Skin contact

Due to the small packaging the risk of skin contact is minimal. Wash the skin immediately with soap and water. Get medical attention if irritation persists after washing.

Eye contact

Due to the small packaging the risk of eye contact is minimal. Rinse with water. Contact physician if discomfort continues.

4.2. Most important symptoms and effects, both acute and delayed

4.3. Indication of any immediate medical attention and special treatment needed

Treat symptomatically

SECTION 5: FIREFIGHTING MEASURES

5.1. Extinguishing media

Extinguishing media

This product is not flammable. Use fire-extinguishing media appropriate for surrounding materials.

5.2. Special hazards arising from the substance or mixture

Hazardous combustion products

None under normal conditions.

Unusual Fire & Explosion Hazards

No unusual fire or explosion hazards noted.

Specific hazards

Due to the small packaging, the risk of inhaling gases formed in a fire is minimal.

5.3. Advice for firefighters

Special Fire Fighting Procedures

No specific fire fighting procedure given.

SECTION 6: ACCIDENTAL RELEASE MEASURES

6.1. Personal precautions, protective equipment and emergency procedures

Wear protective clothing as described in Section 8 of this safety data sheet.

6.2. Environmental precautions

Not relevant considering the small amounts used.

6.3. Methods and material for containment and cleaning up

Not relevant

6.4. Reference to other sections

Wear protective clothing as described in Section 8 of this safety data sheet. See section 11 for more detailed information on health effects and symptoms. For waste disposal, see section 13.

SECTION 7: HANDLING AND STORAGE

7.1. Precautions for safe handling

No specific usage precautions noted.

7.2. Conditions for safe storage, including any incompatibilities

Keep in original container.

7.3. Specific end use(s)

The identified uses for this product are detailed in Section 1.2.

SECTION 8: EXPOSURE CONTROLS/PERSONAL PROTECTION

8.1. Control parameters

HEADSET CLENE

Name	STD	TWA - 8 Hrs		STEL - 15 Min		Notes
PROPAN-2-OL	WEL	400 ppm	999 mg/m3	500 ppm	1250 mg/m3	

WEL = Workplace Exposure Limit.

Ingredient Comments

WEL = Workplace Exposure Limits

8.2. Exposure controls

Engineering measures

Not relevant

Hand protection

Hand protection not required.

Eye protection

Not relevant

Other Protection

Not relevant

Hygiene measures

Not relevant

SECTION 9: PHYSICAL AND CHEMICAL PROPERTIES

9.1. Information on basic physical and chemical properties

Appearance	Impregnated cloth, card or tissue
Odour	Characteristic.
Relative density	N/A @ 20 °c
Vapour pressure	2.35 kPa @ 20 °c
Viscosity	@ °c
Flash point	>55 CC (Closed cup).

9.2. Other information

SECTION 10: STABILITY AND REACTIVITY

10.1. Reactivity

There are no known reactivity hazards associated with this product.

10.2. Chemical stability

Stable under normal temperature conditions.

10.3. Possibility of hazardous reactions

Not applicable.

Hazardous Polymerisation

Will not polymerise.

10.4. Conditions to avoid

Not relevant

10.5. Incompatible materials

Materials To Avoid

No specific, or groups of materials are likely to react to produce a hazardous situation.

10.6. Hazardous decomposition products

None under normal conditions.

SECTION 11: TOXICOLOGICAL INFORMATION

11.1. Information on toxicological effects

Other Health Effects

This substance has no evidence of carcinogenic properties.

HEADSET CLENE

Health Warnings

No specific health warnings noted. No specific acute or chronic health impact noted, but this chemical may still have adverse impact on human health, either in general or on certain individuals with pre-existing or latent health problems.

Toxicological information on ingredients.

PROPAN-2-OL (CAS: 67-63-0)

Acute toxicity:

Acute Toxicity (Oral LD50)

5280 mg/kg Rat

Acute Toxicity (Dermal LD50)

12800 mg/kg Rabbit

Acute Toxicity (Inhalation LC50)

72.6 mg/l (vapours) Rat 4 hours

SECTION 12: ECOLOGICAL INFORMATION

Ecotoxicity

Not regarded as dangerous for the environment.

12.1. Toxicity

Ecological information on ingredients.

PROPAN-2-OL (CAS: 67-63-0)

Acute Toxicity - Fish

LC50 96 hours 9640 mg/l Pimephales promelas (Fat-head Minnow)

Acute Toxicity - Aquatic Invertebrates

EC50 48 hours 13299 mg/l Daphnia magna

Acute Toxicity - Aquatic Plants

EC50 72 hours > 1.000 mg/l Scenedesmus subspicatus

Acute Toxicity - Microorganisms

EC50 > 1.000 mg/l Activated sludge

12.2. Persistence and degradability

12.3. Bioaccumulative potential

Bioaccumulative potential

No data available on bioaccumulation.

12.4. Mobility in soil

Mobility:

Not relevant, due to the form of the product.

12.5. Results of PBT and vPvB assessment

This product does not contain any PBT or vPvB substances.

12.6. Other adverse effects

None known.

SECTION 13: DISPOSAL CONSIDERATIONS

13.1. Waste treatment methods

No specific disposal method required.

SECTION 14: TRANSPORT INFORMATION

General

The product is not covered by international regulation on the transport of dangerous goods (IMDG, IATA, ADR/RID).

HEADSET CLENE

Road Transport Notes	Not Classified
Rail Transport Notes	Not classified.
Sea Transport Notes	Not classified.
Air Transport Notes	Not classified.

14.1. UN number**14.2. UN proper shipping name****14.3. Transport hazard class(es)**

ADR/RID/ADN Class Not classified for transportation.

Transport Labels

No transport warning sign required.

14.4. Packing group**14.5. Environmental hazards**

Environmentally Hazardous Substance/Marine Pollutant

No.

14.6. Special precautions for user**14.7. Transport in bulk according to Annex II of MARPOL73/78 and the IBC Code**

Not applicable.

SECTION 15: REGULATORY INFORMATION

15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture**Uk Regulatory References**

Chemicals (Hazard Information & Packaging) Regulations.

The Control of Substances Hazardous to Health Regulations 2002 (S.I 2002 No. 2677) with amendments.

Approved Code Of Practice

Classification and Labelling of Substances and Preparations Dangerous for Supply.

Guidance Notes

Workplace Exposure Limits EH40.

EU Legislation

Dangerous Substance Directive 67/548/EEC.

Dangerous Preparations Directive 1999/45/EC.

System of specific information relating to Dangerous Preparations. 2001/58/EC.

Commission Directive 2000/39/EC of 8 June 2000 establishing a first list of indicative occupational exposure limit values in implementation of Council Directive 98/24/EC on the protection of the health and safety of workers from the risks related to chemical agents at work.

Regulation (EC) No 1907/2006 of the European Parliament and of the Council of 18 December 2006 concerning the Registration, Evaluation, Authorisation and Restriction of Chemicals (REACH), establishing a European Chemicals Agency, amending Directive 1999/45/EC and repealing Council Regulation (EEC) No 793/93 and Commission Regulation (EC) No 1488/94 as well as Council Directive 76/769/EEC and Commission Directives 91/155/EEC, 93/67/EEC, 93/105/EC and 2000/21/EC, including amendments.

Authorisations (Title VII Regulation 1907/2006)

No specific authorisations are noted for this product.

Restrictions (Title VIII Regulation 1907/2006)

No specific restrictions of use are noted for this product.

15.2. Chemical Safety Assessment

SECTION 16: OTHER INFORMATION

Revision Comments

Revised in accordance with CHIP3 and EU Directives 1999/45/EC and 2001/58/EC

Issued By

Helen O'Reilly

Revision Date

JULY 2012

HEADSET CLENE

Revision	6
SDS No.	11167
Risk Phrases In Full	
R11	Highly flammable
R36	Irritating to eyes.
NC	Not classified.
R67	Vapours may cause drowsiness and dizziness.
Hazard Statements In Full	
H225	Highly flammable liquid and vapour.
H319	Causes serious eye irritation.
H336	May cause drowsiness or dizziness.

Disclaimer

This information relates only to the specific material designated and may not be valid for such material used in combination with any other materials or in any process. Such information is, to the best of the company's knowledge and belief, accurate and reliable as of the date indicated. However, no warranty guarantee or representation is made to its accuracy, reliability or completeness. It is the user's responsibility to satisfy himself as to the suitability of such information for his own particular use.