


## MECHANICAL DETAILS

<b>Shell Style Model</b>	HG* : Fixed receptacle nut fixing watertight or vacuum-tight
<b>Keying</b>	1 key (alpha=0, plug: male contacts, receptacle: female contacts)
<b>Housing Material</b>	Brass (chrome plated) shell and collet nut, nickel plated brass latch sleeve and mid pieces
<b>Cable Fixing</b>	0 - 0 mm
<b>Variant 2</b>	P : Watertight

	A	B	E	L	M	S3	e
Mm.	20	21.5	9	30	4.5	19	M16x1.0
In.	0.79	0.85	0.35	1.18	0.18	0.75	



## Available Download

 [unipole\\_multipole.pdf](#)


## PERFORMANCE DETAIL

<b>Insert</b>	1K.306 : 6 Low Voltage
<b>Insulator</b>	L: PEEK
<b>Specifications</b>	
<b>Contact Type:</b>	Solder
<b>Max. Matings:</b>	5000
<b>Contact Dia.:</b>	0.7 mm (0.028in)
<b>Bucket Dia.:</b>	0.8 mm (0.031in)
<b>Max. Solid</b>	0.34 mm <sup>2</sup> (AWG 22)
<b>Max. Stranded</b>	0.34 mm <sup>2</sup> (AWG 22)
<b>R (max):</b>	6.1 mOhm









## OTHER CHARACTERISTICS

<b>Shell Style/Model</b>	Libellé
<b>Humidity (max):</b>	<=95% [at 60 deg C /140 F]
<b>Vibration:</b>	15 g [10 Hz - 2000 Hz]
<b>Shock Resistance:</b>	100 g [ 6 ms]
<b>Salt Spray</b>	>144 hr
<b>Climatical</b>	20/80/21
<b>Shielding (min):</b>	95 dB (10 MHz)
<b>Shielding (min):</b>	80 dB (1 GHz)
<b>R leak (He) (max):</b>	0.0000001 mbar <sup>*</sup> l/s (if vacuum-tested)
<b>Pressure</b>	60 bars
<b>IP Rating</b>	68



## Related links

-  [Contact](#)
-  [Quote Request](#)
-  [Catalogs Downloads](#)
-  [Catalogs Requests](#)
-  [Sample Request](#)
-  [3D drawings](#)



HGG.1K.306.CLLP