



Agilent 34420A NanoVolt/Micro-Ohm Meter

Data Sheet



- 7½ digits resolution
- 100 pV, 100 nΩ sensitivity
- 1.3 nVrms, 8 nVpp noise performance
- Built-in low noise 2 channel scanner
- Direct SPRT, RTD, Thermistor, and Thermocouple measurements

Nanovolt Performance at a Microvolt Price

The Agilent Technologies 34420A nanoVolt/micro-Ohm meter is a high-sensitivity multimeter optimized for performing low-level measurements. It combines low-noise voltage measurements with resistance and temperature functions, setting a new standard in low-level flexibility and performance.

Take the Uncertainty Out of Your Low-Level Measurements

Low-noise input amplifiers and a highly tuned input protection scheme bring reading noise down to 8 nVpp. Combine this with 7½ digits of resolution, selectable analog and digital filtering, 2 ppm basic 24-hour dcV accuracy, and a shielded, copper pin connector and you've got accurate, repeatable measurements you can count on.

Two Input Channels

An integral two-channel programmable scanner simplifies voltage comparisons. Built-in ratio and difference functions enable automated two channel measurements without the need for an external nanoVolt scanner. Both channels share the same low noise specifications to ensure accurate comparisons.

Built-In Resistance and Temperature

The 34420A combines its low-noise nano-Volt input circuits with a high-stability current source to provide precise low-level resistance measurements – no more hassling with the cost and complexity of an external current source. Three resistance modes are included:

- Standard
- Low-power
- Voltage-limited for dry-circuit testing

Offset compensation is also provided to minimize thermal EMFs and associated errors.

SPRT Measurements

Built-in ITS-90 conversion routines accept the calibration coefficients from your SPRT probe for direct temperature measurement and conversion. Thermocouples, thermistors, and RTDs are also supported.

Unequaled Versatility

The 34420A gives you the versatility to tackle your most challenging tasks, both on the benchtop and in your automated system. Standard features include RS-232 and GPIB interfaces, SCPI and Keithley 181 programming language, 1024-reading memory, scaling and statistics, and a chart recorder analog output.

Agilent IntuiLink: Easy Data Access

The included Agilent IntuiLink software allows your captured data to be put to work easily, using PC applications such as Microsoft Excel® or Word® to analyze, interpret, display, print, and document the data you get from the 34420A. You can specify the meter setup and take a single reading or log data to the Excel spreadsheet in specified time intervals. To find out more about IntuiLink visit www.agilent.com/find/intuilink

Quality You Can Count On

The 34420A gives you the quality and reliability you expect from Agilent Technologies. From the product's proven >150,000 hour Mean Time Between Failure, to its standard 1-year warranty, Agilent stands behind you to bring a new level of confidence to your low-level measurements.

Specifications

Accuracy Specifications \pm (% of reading + % of range) ¹

| Function | Range ² | Test Current | 24 Hour 23 °C \pm 1 °C | 90 Day 23 °C \pm 5 °C | 1 Year 23 °C \pm 5 °C | Temperature Coefficient 0 °C—18 °C 28 °C—55 °C | Maximum per Lead Resistance |
|--|---------------------------|----------------|-----------------------------|----------------------------|----------------------------|---|-----------------------------------|
| dc Voltage | 1.000000 mV ³ | | 0.0025 + .0020 | 0.0040 + .0020 | 0.0050 + .0020 | 0.0004 + .0001 | |
| | 10.000000 mV ³ | | 0.0025 + .0002 | 0.0040 + .0002 | 0.0050 + .0003 | 0.0004 + .0001 | |
| | 100.000000 mV | | 0.0015 + .0003 | 0.0030 + .0004 | 0.0040 + .0004 | 0.0004 + .00006 | |
| | 1.0000000 V | | 0.0010 + .0003 | 0.0025 + .0004 | 0.0035 + .0004 | 0.0004 + .00004 | |
| | 10.000000 V | | 0.0002 + .0001 | 0.0020 + .0004 | 0.0030 + .0004 | 0.0001 + .00002 | |
| | 100.00000 V ⁴ | | 0.0010 + .0004 | 0.0025 + .0005 | 0.0035 + .0005 | 0.0004 + .00005 | |
| Resistance ⁵ | 1.0000000 Ω | 10 mA | 0.0015 + .0002 | 0.0050 + .0002 | 0.0070 + .0002 | 0.0005 + .00002 | 1 Ω |
| | 10.000000 Ω | 10 mA | 0.0015 + .0002 | 0.0040 + .0002 | 0.0060 + .0002 | 0.0005 + .00001 | 1 Ω |
| | 100.000000 Ω | 10 mA | 0.0015 + .0002 | 0.0040 + .0002 | 0.0060 + .0002 | 0.0005 + .00001 | 10 Ω |
| | 1.0000000 K Ω | 1 mA | 0.0015 + .0002 | 0.0040 + .0002 | 0.0060 + .0002 | 0.0005 + .00001 | 100 Ω |
| | 10.000000 K Ω | 100 μ A | 0.0015 + .0002 | 0.0040 + .0002 | 0.0060 + .0002 | 0.0005 + .00001 | 1 K Ω |
| | 100.000000 K Ω | 10 μ A | 0.0015 + .0003 | 0.0040 + .0004 | 0.0060 + .0004 | 0.0005 + .00002 | 1 K Ω |
| 1.0000000 M Ω | 5 μ A | 0.0020 + .0003 | 0.0050 + .0004 | 0.0070 + .0004 | 0.0006 + .00003 | 1 K Ω | |
| Low Power Resistance ⁵ | 1.0000000 Ω | 10 mA | 0.0015 + .0002 | 0.0050 + .0002 | 0.0070 + .0002 | 0.0005 + .00002 | 1 Ω |
| | 10.000000 Ω | 10 mA | 0.0015 + .0002 | 0.0040 + .0002 | 0.0060 + .0002 | 0.0005 + .00001 | 1 Ω |
| | 100.000000 Ω | 1 mA | 0.0015 + .0002 | 0.0040 + .0002 | 0.0060 + .0002 | 0.0005 + .00001 | 10 Ω |
| | 1.0000000 K Ω | 100 μ A | 0.0015 + .0002 | 0.0040 + .0002 | 0.0060 + .0002 | 0.0005 + .00001 | 100 Ω |
| | 10.000000 K Ω | 10 μ A | 0.0015 + .0004 | 0.0040 + .0004 | 0.0060 + .0004 | 0.0005 + .00001 | 1 K Ω |
| | 100.000000 K Ω | 5 μ A | 0.0015 + .0012 | 0.0040 + .0015 | 0.0060 + .0015 | 0.0005 + .00003 | 1 K Ω |
| 1.0000000 M Ω | 5 μ A | 0.0020 + .0003 | 0.0050 + .0004 | 0.0070 + .0004 | 0.0006 + .00003 | 1 K Ω | |
| Voltage Limited Resistance ^{5,6} | 10.000000 Ω | 1 mA | 0.0020 + .0002 | 0.0050 + .0002 | 0.0070 + .0002 | 0.0005 + .00002 | 1 Ω |
| | 100.000000 Ω | 100 μ A | 0.0025 + .0002 | 0.0050 + .0002 | 0.0070 + .0002 | 0.0005 + .00002 | 5 Ω |

Channel 1 / Channel 2 (dcV Ratio) Ratio Error in % = Channel 1 accuracy in % + Channel 2 accuracy in %
 Channel 1-Channel 2 (dcV Difference) Difference Error = Channel 1 (% of reading + % of range) + Channel 2 (% of reading + % of range)

| Temperature | (resolution = 0.001 °C) | |
|---------------------------|-------------------------|-------------------------------------|
| SPRT ⁷ | | SPRT Probe Accuracy + 0.003°C |
| RTD | | RTD Probe Accuracy + 0.05°C |
| Thermistor | | Thermistor Probe Accuracy + 0.1°C |
| Thermocouple ⁸ | | Thermocouple Probe Accuracy + 0.2°C |

DC Voltage Noise ⁹

| Range | Observation Period | | |
|--------|--------------------------|--------------------------------|-------------------------------|
| | 2-Minute RMS Noise | 2-Minute Peak-Peak Noise | 24-Hour Peak-Peak Noise |
| 1 mV | 1.3 nVrms | 8 nVpp | 12 nVpp |
| 10 mV | 1.5 nVrms | 10 nVpp | 14 nVpp |
| 100 mV | 10 nVrms | 65 nVpp | 80 nVpp |
| 1 V | 100 nVrms | 650 nVpp | 800 nVpp |
| 10 V | 450 nVrms | 3 μ Vpp | 3.7 μ Vpp |
| 100 V | 11 μ Vrms | 75 μ Vpp | 90 μ Vpp |

DC Voltage Noise vs Source Resistance ¹⁰

| Source Resistance | Noise | Analog Filter | Digital Filter |
|----------------------|-----------|------------------|-------------------|
| 0 Ω | 1.3 nVrms | Off | Med |
| 100 Ω | 1.7 nVrms | Off | Med |
| 1k Ω | 4 nVrms | Off | Med |
| 10k Ω | 13 nVrms | Off | Med |
| 100k Ω | 41 nVrms | On | Med |
| 1M Ω | 90 nVrms | On | Slow |

- Specifications are for Channel 1 or Channel 2, after 2-hour warm-up, resolution at 7.5 digits (100 NPLC), with FILTERS off. RESISTANCE specifications are for 4-wire Ohms or 2-wire ohms using Null. Without Null, add 0.2 Ohms additional error in 2-wire Ohms function. For Analog Filter ON, add 0.002% of reading.
- 20% overrange on all ranges except 5% on Voltage Limited Resistance.
- After using Math Null. If Null is not used add 100 nanoVolts.
- Channel 1 only.
- Channel 1 only. Resistance measurements, for NPLC <1, add 160 μ Ω rms noise.
- Voltage limit can be set to 20 mV (default), 100 mV, or 500 mV. Measured resistance plus Channel 1 HI and LO lead resistance is limited to 10.5 Ω on the 10 Ω range and 105 Ω on the 100 Ω range.
- For 25 Ω SPRT with triple-point of water check within the last 4 hours. Without the triple-point of water check, add 0.013°C for 24 hours, add 0.035°C for 90 day, and add 0.055°C for 1 year specifications.
- For fixed reference junction. Add 0.3 μ C for external reference junction, add 2.0 μ C for internal reference junction.
- After a 2-hour warm-up, \pm 1 μ C, 6.5 digits (10 PLC) with Analog Filter Off and Digital Filter Medium (50 reading average). 2-minute rms and 24-hour noise typical. For measurements using 0.02 or 0.2 NPLC, add 800 nV rms noise.
- Typical noise behavior for Ch 1 or Ch 2, after 2 hour warm-up, 6.5 digits (10 PLC), 2 minute observation period on 1 mV range. For peak-to-peak noise, multiply rms noise by 6.

Measurement Characteristics

| | |
|--|--|
| DC Voltage | |
| Measurement Method: Continuously integrating multi-slope III A-D Converter | |
| A-D Linearity: 0.00008% of reading + 0.00005% of range | |
| Input Resistance: 100V (Ch1 only): 10 MΩ +/- 1% 1mV through 10V: > 10 GΩ, in parallel with < 3.6 nF | |
| Input Bias Current: <50 pA at 25 °C | |
| Injected Current: <50 nA pp at 50 or 60 Hz | |
| Input Protection: 150 V peak any input terminal to Channel 1 LO, continuous | |
| Channel-to-channel switching error (typical): 3 nV | |
| Channel Isolation: Isolation between input channels >10 ¹⁰ Ω | |
| Earth Isolation: 350 V peak any input terminal to earth. Impedance from any input terminal to earth is >10 GΩ and <400 pF | |
| Maximum Voltage: Channel 1 LO to Channel 2 LO, 150V peak | |
| Resistance | |
| Measurement Method: Selectable 4-wire or 2-wire ohms. Current Source referenced to Channel 1 LO input | |
| Offset Compensation: Used on all ranges except 100 kΩ and 1 MΩ. Can be turned off if desired | |
| Protection: 150 V peak | |
| Open Circuit Voltage: For Resistance and Low Power Resistance <14 V, 20 mV, 100 mV, 500 mV selectable clamp | |
| Temperature | |
| SPRT: ITS-90 calibrated temperature with the range of -190°C to +660°C | |
| Thermocouple: ITS-90 conversions of Type B, E, J, K, N, R, S, T | |
| Thermistor: 5 kΩ | |
| RTD: Type α = .00385 and α = .00392. R ₀ from 4.9 Ω to 2.1 kΩ. ITS -90 (IEC-751) Callendar Van Dusen conversion. | |
| Measurement Noise Rejection 60 (50) Hz¹ | |
| dc CMRR: 140 dB ac CMRR: 70 dB | |
| Integration Time | Normal Mode Rejection² |
| 200 plc/3.335 s (4 s) | 110 dB ³ |
| 100 plc/1.675 s (2 s) | 105 dB ³ |
| 20 plc/334 ms (400 ms) | 100 dB ³ |
| 10 plc/167 ms (200 ms) | 95 dB ³ |
| 2 plc/33.3 ms (40 ms) | 90 dB |
| 1 plc/16.7 ms (20 ms) | 60 dB |
| <1 plc | 0 |

Operating Characteristics⁴

| Function | Digits | Integration Time | Readings/s ⁵ |
|--|-----------------|------------------|-------------------------|
| dcV Thermocouple | 7½ | 200 plc | .15 (.125) |
| | 7½ | 100 plc | .3 (.25) |
| | 6½ | 20 plc | 1.5 (1.25) |
| | 6½ | 10 plc | 3 (2.5) |
| | 5½ | 1 plc | 25 (20.8) |
| | 5½ | 0.2 plc | 100 (100) |
| Resistance dcV1/DCV2 dcV 1-2 RTD Thermistor 0.2 plc | 7½ | 200 plc | .075 (.062) |
| | 7½ | 100 plc | .15 (.125) |
| | 6½ | 20 plc | .75 (.625) |
| | 6½ | 10 plc | 1.5 (1.25) |
| | 5½ | 1 plc | 12.5 (10.4) |
| | 50 (50) 41/2 | | |
| 0.02 plc | 125 (125) | | |

System Speeds⁶

Configuration Rates: 26/s to 50/s
Aurorance Rate (Volts): >30/s
ASCII reading to RS-232: 55/s
ASCII reading to GPIB: 250/s
Max. Internal Trigger Rate: 250/s
Max. Ext. Trig. Rate to Memory: 250/s

Triggering and Memory

Reading HOLD Sensitivity:
10%, 1%, 0.1%, or 0.01% of range
Samples/Trigger: 1 to 50,000
Trigger Delay: 0 to 3600 s; 10 μs step size
External Trigger Delay: <1 ms
External Trigger Jitter: <500 μs
Memory: 1024 readings

Math Functions

NULL (Channel 1 dcV, Channel 2 dcV,
Difference, Resistance, Temperature)
STATS (Min, Max, Average, Peak-Peak,
Standard Deviation, Number of readings)

SCALE (Allows linear scaling as $y = mx+b$)

CHART NULL (Establishes zero for rear panel
output)

Filter (Analog or Digital or Both)

Analog:
Low pass 2 pole @ 13Hz, available for dcV
on
1 mV, 10 mV, 100 mV range

Digital:
Moving average filter, 10 (fast), 50 (medium),
or 100 (slow) reading averages.

- For 1 kΩ unbalanced in LO lead.
- For power line frequency ± 0.1%, Filters OFF. For Digital Filter slow add 20 db, for medium or fast add 10 db for NPLC³ 1.
- For power line frequency ± 1%, use 80 db, for ± 3% use 60 db.
- Speeds are for delay 0, Display OFF, Filters OFF, Offset Compensation OFF.
- Reading speeds for 60 Hz or (50 Hz), 100 mV through 100 V ranges. 1 mV range 30/s MAX, 10 mV range 170/s MAX, thermocouple 120/s MAX.
- Speeds are for NPLC 0.02, Delay 0, Display OFF, Chart Out OFF.

Chart Out (Analog Out)

Maximum output: ± 3V
Resolution: 16 bits
Accuracy: ± 0.1% of output + 1 mV
Output Resistance: 1 kΩ ± 5%
Update rate: once per reading
Span and Offset: Adjustable

Standard Programming Languages

SCPI (IEEE 488.2), Keithley 181

Accessories Included

4 ft low thermal cable with copper spade lugs,
Kelvin clip set, 4-wire shorting plug, user's man-
ual, service manual, test report, contact cleaner,
and power cord.

General Specifications

Front Panel Connection:
Shielded, low thermal, 99% copper contacts.

Power Supply:
100V/120V/220V(230V)/240V +/- 10%.

Power Line Frequency:
45 Hz to 66 Hz and 360 Hz to 440 Hz.
Automatically sensed at power-on.

Power Consumption:
25VA peak (10W average).

Operating Environment:
Full accuracy for 0 °C to 55 °C. Full accuracy
to 80% R.H. up to 30 °C.

Storage Environment:
-40 °C to 75 °C.

Size: 254.4 mm W x 374.0 mm L x 103.6 mm H
(10.02" W x 14.72" L x 4.08" H)

Weight: 3 kg (6.5 lbs).

Safety:
Designed to CSA, UL-1244, IEC-1010.
RFI and ESD: CISPR 11.



Agilent Email Updates

www.agilent.com/find/emailupdates

Get the latest information on the products and applications you select.



www.lxistandard.org

LAN eXtensions for Instruments puts the power of Ethernet and the Web inside your test systems. Agilent is a founding member of the LXI consortium.

Agilent Channel Partners

www.agilent.com/find/channelpartners

Get the best of both worlds: Agilent's measurement expertise and product breadth, combined with channel partner convenience.

Ordering Information

Includes low thermal input cable (34102A), low thermal shorting plug (34103A), Kelvin clip set (11062A), calibration certificate, power cord. Also includes CD with: IntuiLink software, IVI and VXI PnP drivers, user's guide, service guide, and data sheet.

Options

34420A-ABA English localization

34420A-ABD German localization: translated operating manual

34420A-ABF French localization: translated operating manual

34420A-ABJ Japanese localization: translated operating manual

34420A-A6J ANSI Z540 compliant calibration



Agilent Advantage Services is committed to your success throughout your equipment's lifetime. To keep you competitive, we continually invest in tools and processes that speed up calibration and repair and reduce your cost of ownership. You can also use Infoline Web Services to manage equipment and services more effectively. By sharing our measurement and service expertise, we help you create the products that change our world.

www.agilent.com/find/advantageservices



www.agilent.com/quality

Accessories

34102A Low-thermal input cable (four-conductor) with copper spade lugs

34103A Low-thermal shorting plug

34104A Low-thermal input connector

34131A Transit Case

34161A Accessory pouch

34190A Rackmount Kit: designed for use with only one instrument, mounted on either the left or the right side of the rack.

34191A 2U Dual Flange Kit: secures the instrument to the front of the rack. This kit can be used with the 34194A Dual Lock Link Kit to mount two half-width, 2U height instruments side-by-side.

34194A Dual Lock Link Kit: recommended for side-by-side combinations and includes links for instruments of different depths. This kit can be used with the 34191A 2U Dual Flange Kit to mount two half-width, 2U height instruments side-by-side.

For more information on Agilent Technologies' products, applications or services, please contact your local Agilent office. The complete list is available at:

www.agilent.com/find/contactus

Americas

| | |
|---------------|----------------|
| Canada | (877) 894 4414 |
| Brazil | (11) 4197 3500 |
| Mexico | 01800 5064 800 |
| United States | (800) 829 4444 |

Asia Pacific

| | |
|--------------------|----------------|
| Australia | 1 800 629 485 |
| China | 800 810 0189 |
| Hong Kong | 800 938 693 |
| India | 1 800 112 929 |
| Japan | 0120 (421) 345 |
| Korea | 080 769 0800 |
| Malaysia | 1 800 888 848 |
| Singapore | 1 800 375 8100 |
| Taiwan | 0800 047 866 |
| Other AP Countries | (65) 375 8100 |

Europe & Middle East

| | |
|----------------|----------------------|
| Belgium | 32 (0) 2 404 93 40 |
| Denmark | 45 70 13 15 15 |
| Finland | 358 (0) 10 855 2100 |
| France | 0825 010 700* |
| | *0.125 €/minute |
| Germany | 49 (0) 7031 464 6333 |
| Ireland | 1890 924 204 |
| Israel | 972-3-9288-504/544 |
| Italy | 39 02 92 60 8484 |
| Netherlands | 31 (0) 20 547 2111 |
| Spain | 34 (91) 631 3300 |
| Sweden | 0200-88 22 55 |
| United Kingdom | 44 (0) 131 452 0200 |

For other unlisted countries:

www.agilent.com/find/contactus

Revised: June 8, 2011

Product specifications and descriptions in this document subject to change without notice.

© Agilent Technologies, Inc. 2011
Published in USA, October 11, 2011
5968-0161EN

