



Normally closed DIP6-pin economic type with reinforced insulation

PhotoMOS[®]
GU-E 1 Form B
(AQV414E, AQV410EH)



mm inch

FEATURES

1. High cost-performance type of PhotoMOS 1 Form B output
2. 60V type couples high capacity (0.55A) with low on-resistance (typ. 1Ω).
3. Low on-resistance

This has been realized thanks to the built-in MOSFET processed by our proprietary method, DSD (Double-diffused and Selective Doping) method.


5. High sensitivity and low on-resistance

Can control max. 0.55 A load current with 5 mA input current.
Low on-resistance of typ. 1Ω (AQV412EH).

6. Low-level off-state leakage current of max. 1 μA (AQV414E)

7. Reinforced insulation 5,000 V type also available

More than 0.4 mm internal insulation distance between inputs and outputs.
Conforms to EN41003, EN60950 (reinforced insulation).



4. Controls low-level analog signals

PhotoMOS relays feature extremely low closed-circuit offset voltage to enable control of low-level analog signals without distortion.

TYPICAL APPLICATIONS

- Power supply
- Measuring equipment
- Security equipment
- Telephone equipment
- Sensing equipment

TYPES

I/O isolation voltage	Output rating*		Package	Part No.				Packing quantity	
				Through hole terminal		Surface-mount terminal			
	Load voltage	Load current		Tube packing style		Tape and reel packing style		Tube	Tape and reel
AC/DC dual use	1,500 V AC (Standard)	400 V 120 mA	DIP6-pin	AQV414E	AQV414EA	AQV414EAX	AQV414EAZ	1 tube contains: 50 pcs. 1 batch contains: 500 pcs.	1,000 pcs.
	60 V	550 mA		AQV412EH	AQV412EHA	AQV412EHAX	AQV412EHAZ		
	350 V	130 mA		AQV410EH	AQV410EHA	AQV410EHAX	AQV410EHAZ		
	400 V	120 mA		AQV414EH	AQV414EHA	AQV414EHAX	AQV414EHAZ		

*Indicate the peak AC and DC values.

Note: The surface mount terminal shape indicator "A" and the packing style indicator "X" or "Z" are not marked on the relay.

RATING

1. Absolute maximum ratings (Ambient temperature: 25°C 77°F)


Item	Symbol	Type of connection	AQV414E(A)	AQV412EH(A)	AQV410EH(A)	AQV414EH(A)	Remarks			
Input	LED forward current	I _F		50 mA			f = 100 Hz, Duty factor = 0.1%			
	LED reverse voltage	V _R		5 V						
	Peak forward current	I _{FP}		1 A						
	Power dissipation	P _{in}		75 mW						
Output	Load voltage (peak AC)	V _L	400 V	60 V	350 V	400 V				
	Continuous load current	I _L	A	0.12 A	0.55 A	0.13 A	A connection: Peak AC, DC B,C connection: DC			
			B	0.13 A	0.65 A	0.15 A				
			C	0.15 A	0.8 A	0.17 A				
	Peak load current	I _{peak}		0.3 A	1.5 A	0.4 A	0.3 A			
Total power dissipation	Power dissipation	P _{out}	500 mW							
			550 mW							
			1,500 V AC	5,000 V AC						
Temperature limits	Operating	T _{opr}	-40°C to +85°C -40°F to +185°F				Non-condensing at low temperatures			
	Storage	T _{stg}	-40°C to +100°C -40°F to +212°F							

GU-E 1 Form B (AQV414E, AQV410EH)

2. Electrical characteristics (Ambient temperature: 25°C 77°F)

Item			Symbol	Type of connection	AQV414E(A)	AQV412EH(A)	AQV410EH(A)	AQV414EH(A)	Condition
Input	LED operate (OFF) current	Typical	I_{Foff}	—	1.45 mA	1.9 mA			$I_L = \text{Max.}$
		Maximum			3.0 mA				
	LED reverse (ON) current	Minimum	I_{For}	—	0.3 mA	0.4 mA			$I_L = \text{Max.}$
		Typical			1.40 mA	1.8 mA			
Output	LED dropout voltage	Typical	V_F	—	1.25 V (1.14 V at $I_F = 5 \text{ mA}$)				$I_F = 50 \text{ mA}$
		Maximum			1.5 V				
	On resistance	Typical	R_{on}	A	26 Ω	1 Ω	18 Ω	25.2 Ω	$I_F = 0 \text{ mA}$ $I_L = \text{Max.}$ Within 1 s on time
		Maximum			50 Ω	2.5 Ω	35 Ω	50 Ω	
		Typical	R_{on}	B	20 Ω	0.55 Ω	13 Ω	19 Ω	$I_F = 0 \text{ mA}$ $I_L = \text{Max.}$ Within 1 s on time
		Maximum			25 Ω	1.3 Ω	17.5 Ω	25 Ω	
		Typical	R_{on}	C	10 Ω	0.3 Ω	6.5 Ω	10 Ω	$I_F = 0 \text{ mA}$ $I_L = \text{Max.}$ Within 1 s on time
		Maximum			12.5 Ω	0.7 Ω	8.8 Ω	12.5 Ω	
Transfer characteristics	Off state leakage current	Maximum	I_{Leak}	—	1 μA	10 μA			$I_F = 5 \text{ mA}$ $V_L = \text{Max.}$
	Operate (OFF) time*	Typical	T_{off}	—	0.7 ms	3 ms	1.5 ms	1.3 ms	$I_F = 0 \text{ mA} \rightarrow 5 \text{ mA}$ $I_L = \text{Max.}$
		Maximum			2.0 ms	8 ms	3.0 ms		
	Reverse (ON) time*	Typical	T_{on}	—	0.1 ms	0.3 ms			$I_F = 5 \text{ mA} \rightarrow 0 \text{ mA}$ $I_L = \text{Max.}$
		Maximum			1.0 ms	1.5 ms			
I/O capacitance	Typical	C_{iso}	—	0.8 pF				$f = 1 \text{ MHz}$ $V_B = 0 \text{ V}$	
	Maximum			1.5 pF					
Initial I/O isolation resistance	Minimum	R_{iso}	—	1,000 MΩ				500 V DC	

*Operate/Reverse time



RECOMMENDED OPERATING CONDITIONS

Please obey the following conditions to ensure proper relay operation and resetting.

Item	Symbol	Recommended value	Unit
Input LED current	I_F	Standard type: 5 Reinforced type: 5 to 10	mA

Dimensions

Schematic and Wiring Diagrams

Cautions for Use

These products are not designed for automotive use.

If you are considering to use these products for automotive applications, please contact your local Panasonic technical representative.


Please refer to our information on [PhotoMOS Relays for Automotive Applications](#).

REFERENCE DATA

1-(1). Load current vs. ambient temperature characteristics

Allowable ambient temperature: -40°C to $+85^{\circ}\text{C}$
 -40°F to $+185^{\circ}\text{F}$


Type of connection: A



1-(2). Load current vs. ambient temperature characteristics


Allowable ambient temperature: -40°C to $+85^{\circ}\text{C}$
 -40°F to $+185^{\circ}\text{F}$

Type of connection: A




2. On resistance vs. ambient temperature characteristics

Measured portion: between terminals 4 and 6;
LED current: 0 mA; Load voltage: Max. (DC);
Continuous load current: Max. (DC)




3. Operate (OFF) time vs. ambient temperature characteristics

LED current: 5mA; Load voltage: Max. (DC);
Continuous load current: Max. (DC)




4. Reverse (ON) time vs. ambient temperature characteristics

LED current: 5 mA; Load voltage: Max. (DC);
Continuous load current: Max. (DC)




5. LED operate (OFF) current vs. ambient temperature characteristics

Load voltage: Max. (DC);
Continuous load current: Max. (DC)




6. LED reverse (ON) current vs. ambient temperature characteristics

Load voltage: Max. (DC);
Continuous load current: Max. (DC)




7. LED dropout voltage vs. ambient temperature characteristics

Sample: All types;
LED current: 5 to 50 mA



8-(1). Current vs. voltage characteristics of output at MOS portion

Measured portion: between terminals 4 and 6;
Ambient temperature: 25°C 77°F




GU-E 1 Form B (AQV414E, AQV410EH)

8-(2). Current vs. voltage characteristics of output at MOS portion

Measured portion: between terminals 4 and 6;


Ambient temperature: 25°C 77°F



9. Off state leakage current vs. load voltage characteristics

Sample: All types;


Measured portion: between terminals 4 and 6;
LED current: 5 mA; Ambient temperature: 25°C 77°F



10. Operate (OFF) time vs. LED forward current characteristics

Measured portion: between terminals 4 and 6;


Load voltage: Max. (DC); Continuous load current: Max. (DC); Ambient temperature: 25°C 77°F



11. Reverse (ON) time vs. LED forward current characteristics

Measured portion: between terminals 4 and 6;

Load voltage: Max. (DC); Continuous load current: Max. (DC); Ambient temperature: 25°C 77°F



12. Output capacitance vs. applied voltage characteristics

Measured portion: between terminals 4 and 6;

Frequency: 1 MHz;

Ambient temperature: 25°C 77°F

