





TYS40181R0N-10

PHYSICAL DIMENSIONS:

A	4.00 ± 0.20
B	4.00 ± 0.20
C	1.80 MAX.
D	0.95 ± 0.20
E	2.10 ± 0.20




LAND PATTERNS FOR REFLOW SOLDERING



ELECTRICAL SPECIFICATION


	Min	Nom	Max
INDUCTANCE (uH) L @ 100 KHz/1V ± 30%	0.70	1.00	1.30
DCR (Ω)		0.025	0.0325

CHARACTERISTICS OF TEMPERATURE RISE



UNCONTROLLED DOCUMENT

CURRENT VS INDUCTANCE DROP IN RATES



Saturation Current(A)	4.80
SRF (MHz)	80
Temperature Rise Current (A)	2.00

NOTES: UNLESS OTHERWISE SPECIFIED

- OPERATING TEMPERATURE RANGE: -25°C TO +125°C (INCLUDING SELF-HEATING) .
- STORAGE TEMPERATURE RANGE (PACKAGING CONDITIONS): -10°C TO +40°C AND RH 70% (MAX.)
- UNLESS OTHERWISE SPECIFIED, THE STANDARD ATMOSPHERIC CONDITIONS FOR MEASUREMENT/TEST AS:
 - AMBIENT TEMPERATURE: 20±15°C.
 - RELATIVE HUMIDITY: 65%±20%.
- DEFINITION OF SATURATION CURRENT (ISAT): DC CURRENT AT WHICH THE INDUCTANCE DROPS ≤30% FROM ITS VALUE WITHOUT CURRENT.
- DEFINITION OF TEMPERATURE RISE CURRENT (IRMS): DC CURRENT THAT CAUSES THE TEMPERATURE RISE (ΔT ≤40°C) FROM 20°C AMBIENT.

DIMENSIONS ARE IN mm .				This print is the property of Laird Tech. and is loaned in confidence subject to return upon request and with the understanding that no copies shall be made without the written consent of Laird Tech. All rights to design or invention are reserved.		Laird TECHNOLOGIES		
				PROJECT/PART NUMBER: TYS40181R0N-10		REV A	PART TYPE POWER INDUCTOR	DRAWN BY: QIU
				DATE: 05/07/12		SCALE: NTS		SHEET: 2 of 2
A	ORIGINAL DRAFT	05/07/12	QIU	DATE: 05/07/12		SCALE: NTS		SHEET: 2 of 2
REV	DESCRIPTION	DATE	INT	CAD # TYS40181R0N-10-A		TOOL # -		