Feature:

• Design for home appliances, aviation electronics, automobile electronics and computer (PC) peripherals

Specifications:

Series
Connector Type
Pitch Spacing
No. of Rows
No. of Contacts
Gender
Contact Termination
Contact Resistance
Current Rating
Insulation Resistance
Operating Temperature
Voltage Rating
Withstand Voltage


: 2212BR : Board to Board : 2.54mm : 1 : 4 : Receptacle : Solder : 20mΩ : 3A : 1,000MΩ : -40°C to +105°C : 250V AC : 600V


Material and Finish:

Insulator Contact Plating

:	High	Temperature	Plastic	(Nylon	6T)
•				(•••

- : Phosphor Bronze
- : Gold Plated





Α	В
7.62	10.16

nulticomp

Dimensions : Millimetres

Part Number Table

Description	Part Number	
Socket, PCB, R/A, 1 Row, 4 Way	2212BR-04G	

Important Notice : This data sheet and its contents (the "Information") belong to the members of the Premier Farnell group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp is the registered trademark of the Group. © Premier Farnell plc 2012.

www.element14.com www.farnell.com www.newark.com

Dimensions : Millimetres

