

Productname : AMBERGLIDE
Ref.Nr.: UDS000355_3_20120514

Creationdate : 14.05.12 Version : 1.0
Replaces: UK10041

SECTION 1: Identification of the substance/mixture and of the company/undertaking

1.1. Product identifier

AMBERGLIDE
Aerosol

1.2. Relevant identified uses of the substance or mixture and uses advised against

Lubricants

1.3. Details of the supplier of the safety data sheet

CRC Industries UK Ltd.
Ambersil House - Wylds Road
Castlefield Industrial Estate
TA6 4DD Bridgwater Somerset
United Kingdom
Tel.: +44 1278 727200
Fax.: +44 1278 425644
E-mail : hse.uk@crcind.com

1.4. Emergency telephone number

(+44)(0)1278 72 7200

SECTION 2: Hazards identification

2.1. Classification of the substance or mixture

Classification according to 67/548/EEC or 1999/45/EC:

Health:	not classified
Physical:	R12: Extremely flammable. EXTREMELY FLAMMABLE
Environment:	R52/53: Harmful to aquatic organisms, may cause long-term adverse effects in the aquatic environment.

2.2. Label elements

Warning symbol(s) : EXTREMELY FLAMMABLE



Risk-phrase(s) : R12: Extremely flammable.

Ambersil

1 / 9

CRC Industries UK Limited
Ambersil House, Wylds Road, Castlefield Industrial Estate, Bridgwater,
Somerset, TA6 4DD
Tel: +44 (0)1278 727200 Fax: +44 (0)1278 425644 web: www.ambersil.com

Productname : AMBERGLIDE
Ref.Nr.: UDS000355_3_20120514

Creationdate : 14.05.12 Version : 1.0
Replaces: UK10041

Safety-phrase(s) :	R52/53: Harmful to aquatic organisms, may cause long-term adverse effects in the aquatic environment. S2: Keep out of the reach of children. S16: Keep away from sources of ignition - No smoking. S51: Use only in well-ventilated areas.
Extra label elements according to Aerosol Dispenser Directive 75/324/EC:	Pressurised container: protect from sunlight and do not expose to temperatures exceeding 50°C. Do not pierce or burn, even after use. Do not spray on a naked flame or any incandescent material.
Other extra label elements:	Remark: Preparations classified as harmful on the basis of an aspiration hazard need not be labelled as harmful with R65 when placed on the market in aerosol containers or in containers fitted with a sealed spray attachment. (EU-Directive 67/548 Annex VI 9.4)

2.3. Other hazards

None

SECTION 3: Composition/information on ingredients

3.1. Substances

Not applicable.

3.2. Mixtures

Hazardous ingredient	CAS-nr.	EC-nr	w/w %	symbol	R-phrases*	Notes
Hydrocarbons,C3-4-rich, petroleum distillate Petroleumgas (1,3-butadiene < 0.1%)	68512-91-4	270-990-9	30-60	F+	12	K
Hydrocarbons, C11-C14, n-alkanes, isoalkanes, cyclics, < 2% aromatics	-	926-141-6	10-30	Xn	65-66	B
n-butyl acetate	123-86-4	204-658-1	1-5		10-66-67	
(Z)-N-methyl-N-(1-oxo-9-octadecenyl)glycine	110-25-8	203-749-3	0-1	Xi,N	38-41-50/53	
1H-Imidazole-1-ethanol, 2-(8-heptadecenyl)-4,5-dihydro-	95-38-5	202-414-9	0-1	Xn,C,N	R22-R34-R48-R50/53	

Explanation notes

B : substance with national established workplace exposure limit

K : not classified as carcinogen, less than 0.1% w/w 1,3-butadiene (Einecs-nr. 203-450-8)

Hazardous ingredient	Registration number	CAS-nr.	EC-nr	w/w %	Hazard Class and Category	Hazard statement	Notes
Hydrocarbons, C11-C14, n-alkanes, isoalkanes, cyclics, < 2% aromatics	01-2119456620-43	-	926-141-6	10-30	Asp. Tox. 1	H304	B
n-butyl acetate	01-2119485493-29	123-86-4	204-658-1	1-5	Flam. Liq. 3, STOT SE 3	H226,H336	

Explanation notes

B : substance with national established workplace exposure limit

(* Explanation phrases : see chapter 16)

Productname : AMBERGLIDE
Ref.Nr.: UDS000355_3_20120514

Creationdate : 14.05.12 Version : 1.0
Replaces: UK10041

SECTION 4: First aid measures

4.1. Description of first aid measures

Contact with eyes :	If substance has got into eyes, immediately wash out with plenty of water Seek medical attention if irritation persists
Contact with skin :	Wash with water and soap. Seek medical attention if irritation persists
Inhalation :	Fresh air, keep warm and at rest. Seek medical attention if ill effects occur
Ingestion :	If swallowed do not induce vomiting because of risk of aspiration into the lungs. If aspiration is suspected obtain immediate medical attention

4.2. Most important symptoms and effects, both acute and delayed

Inhalation :	Excessive inhalation of solvent vapours may give rise to nausea, headaches and dizziness
Ingestion :	After vomiting of swallowed product aspiration into lungs is likely. Solvents may induce chemical pneumonia. Symptoms : sore throat, abdominal pain, nausea, vomiting
Skin contact :	May cause irritation. Symptoms : redness and pain
Eye contact :	May cause irritation. Symptoms : redness and pain

4.3. Indication of any immediate medical attention and special treatment needed

General Advice :	If you feel unwell, seek medical advice (show the label where possible) If symptoms persist always call a doctor
-------------------------	---

SECTION 5: Firefighting measures

5.1. Extinguishing media

foam, carbon dioxide or dry agent

5.2. Special hazards arising from the substance or mixture

Aerosols may explode if heated above 50°C
Forms hazardous decomposition products
CO,CO2

5.3. Advice for firefighters

Keep container(s) exposed to fire cool, by spraying with water
In case of fire, do not breathe fumes

SECTION 6: Accidental release measures



3 / 9

CRC Industries UK Limited
Ambersil House, Wylds Road, Castlefield Industrial Estate, Bridgwater,
Somerset, TA6 4DD
Tel: +44 (0)1278 727200 Fax: +44 (0)1278 425644 web: www.ambersil.com

Productname : AMBERGLIDE
Ref.Nr.: UDS000355_3_20120514

Creationdate : 14.05.12 Version : 1.0
Replaces: UK10041

6.1. Personal precautions, protective equipment and emergency procedures

Shut off all ignition sources
Ensure adequate ventilation
Wear suitable protective clothing and gloves.

6.2. Environmental precautions

Do not allow to enter public sewers and watercourses
If polluted water reaches drainage systems or water courses, immediately inform appropriate authorities

6.3. Methods and material for containment and cleaning up

Absorb spillage in suitable inert material

6.4. Reference to other sections

For further information see section 8

SECTION 7: Handling and storage

7.1. Precautions for safe handling

Keep away from heat and sources of ignition
Take precautionary measures against static discharges
Equipment should be earthed
Use explosion-proof electrical/ventilating/lighting/.../equipment.
Use only non-sparking tools.
Do not breathe aerosols or vapours.
Ensure adequate ventilation
Avoid contact with skin and eyes.
Wash thoroughly after use
Wear protective gloves/protective clothing/eye protection/face protection.

7.2. Conditions for safe storage, including any incompatibilities

Pressurized container : protect from sunlight and do not expose to temperatures exceeding 50°C.
Keep out of reach of children.

7.3. Specific end use(s)

Lubricants

SECTION 8: Exposure controls/personal protection

8.1. Control parameters

Exposure limits :

Productname : AMBERGLIDE
Ref.Nr.: UDS000355_3_20120514

Creationdate : 14.05.12 Version : 1.0
Replaces: UK10041

Hazardous ingredient	CAS-nr.	method	
National established exposure limits, United Kingdom			
n-butyl acetate	123-86-4	TWA	150 ppm
		STEL	200 ppm

8.2. Exposure controls

Control procedures :	Ensure adequate ventilation Keep away from heat and sources of ignition Take precautionary measures against static discharges
Personal protection :	Take precautions to avoid contact with skin and eyes when handling the product. Ensure adequate ventilation
inhalation :	In case of insufficient ventilation, wear suitable respiratory equipment.
hands and skin :	Wear suitable protective gloves (nitrile)
eyes :	Wear safety goggles.

SECTION 9: Physical and chemical properties

9.1. Information on basic physical and chemical properties

(for aerosols data for the product without propellant)

Apperance : physical state :	Liquid under pressure.
colour :	Amber.
odour :	Solvent.
pH :	Not applicable.
Boiling point/range :	126 °C
Flash point :	23 °C
Evaporation rate :	Not available.
Explosion limits : upper limit :	9.4 %
lower limit :	0.6 %
Vapour pressure :	Not available.
Relative density :	0.875 g/cm ³ (@ 20°C).
Solubility in water :	Insoluble in water
Auto-ignition :	225 °C
Viscosity :	Not available.

9.2. Other information

SECTION 10: Stability and reactivity

10.1. Reactivity

No hazardous reactions known if used for its intended purpose

10.2. Chemical stability



5 / 9

CRC Industries UK Limited
 Ambersil House, Wylds Road, Castlefield Industrial Estate, Bridgwater,
 Somerset, TA6 4DD
 Tel: +44 (0)1278 727200 Fax: +44 (0)1278 425644 web: www.ambersil.com

Productname : AMBERGLIDE
Ref.Nr.: UDS000355_3_20120514

Creationdate : 14.05.12 Version : 1.0
Replaces: UK10041

Stable

10.3. Possibility of hazardous reactions

No hazardous reactions known if used for its intended purpose

10.4. Conditions to avoid

Avoid overheating

10.5. Incompatible materials

Strong oxidising agent

10.6. Hazardous decomposition products

CO,CO2

SECTION 11: Toxicological information

11.1. Information on toxicological effects

Inhalation :	Inhalation of solvent vapours may give rise to nausea, headaches and dizziness
Ingestion :	After vomiting of swallowed product aspiration into lungs is likely. Solvents may induce chemical pneumonia.
Skin contact :	Prolonged skin contact will result in defatting of the skin, leading to irritation, and in some cases, dermatitis Repeated exposure may cause skin dryness or cracking.
Eye contact :	May cause irritation.

Toxicological data :

Hazardous ingredient	CAS-nr.	method	
n-butyl acetate	123-86-4	LD50 oral rat	> 2000 mg/kg
		LC50 inhal.rat	> 20 mg/l

SECTION 12: Ecological information

12.1. Toxicity

R52/53: Harmful to aquatic organisms, may cause long-term adverse effects in the aquatic environment.

Ecotoxicological data:

Hazardous ingredient	CAS-nr.	method	



6 / 9

CRC Industries UK Limited
 Ambersil House, Wylds Road, Castlefield Industrial Estate, Bridgwater,
 Somerset, TA6 4DD
 Tel: +44 (0)1278 727200 Fax: +44 (0)1278 425644 web: www.ambersil.com

Productname : AMBERGLIDE
Ref.Nr.: UDS000355_3_20120514

Creationdate : 14.05.12 Version : 1.0
Replaces: UK10041

n-butyl acetate	123-86-4	IC50 algae	647 mg/l
		LC50 fish	18 mg/l
		EC50 daphnia	44 mg/l

12.2. Persistence and degradability

No information available

12.3. Bioaccumulative potential

No information available

12.4. Mobility in soil

Insoluble in water

12.5. Results of PBT and vPvB assessment

No information available

12.6. Other adverse effects

No information available

SECTION 13: Disposal considerations

13.1. Waste treatment methods

Product : This material and its container must be disposed of in a safe way. Do not discharge into drains or the environment, dispose to an authorised waste collection point.
Contaminated packaging : Disposal should be in accordance with local, state or national legislation

SECTION 14: Transport information

14.1. UN number

UN-number : 1950

14.2. UN proper shipping name

Proper shipping name: AEROSOLS

14.3. Transport hazard class(es)

Class: 2.1
ADR/RID - Classification code: 5F



7 / 9

CRC Industries UK Limited
Ambersil House, Wylds Road, Castlefield Industrial Estate, Bridgwater,
Somerset, TA6 4DD
Tel: +44 (0)1278 727200 Fax: +44 (0)1278 425644 web: www.ambersil.com

Productname : AMBERGLIDE
Ref.Nr.: UDS000355_3_20120514

Creationdate : 14.05.12 Version : 1.0
Replaces: UK10041

14.4. Packing group

Packing group: Not applicable.

14.5. Environmental hazards

ADR/RID - Environmentally
hazardous: No
IMDG - Marine pollutant: No
IATA/ICAO - Environmentally
hazardous: No

14.6. Special precautions for user

ADR/RID - Tunnelcode: (D)
IMDG - Ems: F-D, S-U
IATA/ICAO - PAX: 203
IATA/ICAO - CAO: 203

14.7. Transport in bulk according to Annex II of MARPOL73/78 and the IBC Code

Not applicable.

SECTION 15: Regulatory information

15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture

The Safety Data Sheet is compiled according to the current European requirements.
Dir. 2008/47/EC amendment of the aerosol dispenser directive 75/324/EEC.
EU-directive 99/45/EC
Regulation (EC) No 1907/2006 (REACH)

15.2. Chemical safety assessment

No information available

SECTION 16: Other information

*Explanation risk-phrases:

- R10: Flammable.
- R12: Extremely flammable.
- R38: Irritating to skin.
- R41: Risk of serious damage to eyes.
- R65: Harmful: may cause lung damage if swallowed.
- R66: Repeated exposure may cause skin dryness or cracking.
- R67: Vapours may cause drowsiness and dizziness.
- R50/53: Very toxic to aquatic organisms, may cause long-term adverse effects in the aquatic environment.
- RR22
- RR34
- RR48



Productname : AMBERGLIDE
Ref.Nr.: UDS000355_3_20120514

Creationdate : 14.05.12 Version : 1.0
Replaces: UK10041

RR50/53

*Explanation hazard statements: H226 : Flammable liquid and vapour.
H304 : May be fatal if swallowed and enters airways.
H336 : May cause drowsiness or dizziness.

This product should be stored, handled and used in accordance with good industrial hygiene practices and in conformity with any legal regulation.

The information contained herewith is based on the present state of our knowledge and is intended to describe our products from the point of view of safety requirements. It does not guarantee any specific properties. Apart from any fair dealing for purposes of study, research and review of health, safety and environmental risks, no part of these documents may be reproduced by any process without written permission from CRC.