



## Optocoupler, Photodarlington Output, with Internal RBE (Single, Dual, Quad Channel)





Single Channel



Dual Channel



Quad Channel



### FEATURES

- Internal RBE for high stability
- Four available CTR categories per package type
- $BV_{CEO} > 60\text{ V}$
- Standard DIP packages
- Material categorization: For definitions of compliance please see [www.vishay.com/doc?99912](http://www.vishay.com/doc?99912)



**RoHS**  
COMPLIANT

### DESCRIPTION

IL66, ILD66, and ILQ66 are optically coupled isolators employing gallium arsenide infrared emitters and silicon photodarlington detectors. Switching can be accomplished while maintaining a high degree of isolation between driving and load circuits, with no crosstalk between channels.

### AGENCY APPROVALS

- UL1577, file no. E52744 system code H, double protection
- cUL tested to CSA 22.2 bulletin 5A
- DIN EN 60747-5-5 (VDE 0884) available with option 1
- BSI IEC 60950, IEC 60065

1179015-4

| ORDERING INFORMATION  |                |              |   |              |   |              |              |              |
|---|----------------|--------------|---|--------------|---|--------------|--------------|--------------|
| <div style="display: flex; justify-content: space-around; border: 1px solid black; padding: 2px;"> <span>I</span><span>L</span><span>x</span><span>6</span><span>6</span> </div> <p style="text-align: center;">PART NUMBER</p> <p style="text-align: center;">x = D (Dual) or Q (Quad)</p> |                |              | <div style="display: flex; justify-content: space-around; border: 1px solid black; padding: 2px;"> <span>#</span><span>X</span><span>0</span><span>#</span><span>#</span> </div> <p style="text-align: center;">CTR BIN</p> <p style="text-align: center;">PACKAGE OPTION</p> |              | <div style="display: flex; justify-content: space-around; border: 1px solid black; padding: 2px;"> <span>T</span> </div> <p style="text-align: center;">TAPE AND REEL</p> |              |              |              |
|   |                |              |   |              |   |              |              |              |
| AGENCY CERTIFIED/<br>PACKAGE  | SINGLE CHANNEL |              | DUAL CHANNEL  |              | QUAD CHANNEL  |              |              |              |
|   | CTR (%)        |              |   |              |   |              |              |              |
|   | 2 mA           |              |   |              |   |              |              |              |
|   |                |              |   |              | 0.7 mA  |              | 2 mA         |              |
| <b>UL, cUL, BSI</b>   | <b>≥ 100</b>   | <b>≥ 300</b> | <b>≥ 300</b>  | <b>≥ 500</b> | <b>≥ 100</b>  | <b>≥ 300</b> | <b>≥ 400</b> | <b>≥ 500</b> |
| DIP-6   | IL66-1         | IL66-2       | -   | -            | -   | -            | -            | -            |
| DIP-8   | -              | -            | ILD66-2   | ILD66-4      | -   | -            | -            | -            |
| SMD-8, option 7   | -              | -            | -   | ILD66-4X007T | -   | -            | -            | -            |
| SMD-8, option 9   | -              | -            | -   | ILD66-4X009  | -   | -            | -            | -            |
| DIP-16  | -              | -            | -   | -            | ILQ66-1   | ILQ66-2      | ILQ66-3      | ILQ66-4      |
| SMD-16, option 7  | -              | -            | -   | -            | -   | -            | -            | ILQ66-4X007T |
| SMD-16, option 9  | -              | -            | -   | -            | -   | -            | -            | ILQ66-4X009T |
| <b>VDE, UL, cUL, BSI</b>  | <b>≥ 100</b>   | <b>≥ 300</b> | <b>≥ 300</b>  | <b>≥ 500</b> | <b>≥ 100</b>  | <b>≥ 300</b> | <b>≥ 400</b> | <b>≥ 500</b> |
| DIP-6, 400 mil, option 6  | IL66-1X016     |              |   |              |   |              |              |              |
| DIP-16  |                |              |   |              |   |              |              | ILQ66-4X001  |

**Note**

- Additional option may be possible, please contact sales office.



| <b>ABSOLUTE MAXIMUM RATINGS</b> ( $T_{amb} = 25\text{ }^{\circ}\text{C}$ , unless otherwise specified) |  |       |            |                |           |
|--|--|-------|------------|----------------|-----------|
| PARAMETER  | TEST CONDITION   | PART  | SYMBOL     | VALUE          | UNIT      |
| <b>INPUT</b>   |  |       |            |                |           |
| Peak reverse voltage   |  |       | $V_{RM}$   | 6.0            | V         |
| Forward continuous current   |  |       | $I_F$      | 60             | mA        |
| Power dissipation  |  |       | $P_{diss}$ | 100            | mW        |
| Derate linearly from 25 °C   |  |       |            | 1.33           | mW/°C     |
| <b>OUTPUT</b>  |  |       |            |                |           |
| Power dissipation  |  |       | $P_{diss}$ | 150            | mW        |
| Derate from 25 °C  |  |       |            | 2.0            | mW/°C     |
| <b>COUPLER</b>   |  |       |            |                |           |
| Isolation test voltage   | $t = 1.0\text{ s}$   |       | $V_{ISO}$  | 5300           | $V_{RMS}$ |
| Total package power dissipation  |  | IL66  | $P_{tot}$  | 250            | mW        |
|  |  | ILD66 | $P_{tot}$  | 400            | mW        |
|  |  | ILQ66 | $P_{tot}$  | 500            | mW        |
| Derate linearly from 25 °C   |  | IL66  |            | 3.3            | mW/°C     |
|  |  | ILD66 |            | 5.33           | mW/°C     |
|  |  | ILQ66 |            | 6.67           | mW/°C     |
| Creepage distance  |  |       |            | $\geq 7.0$     | mm        |
| Clearance distance   |  |       |            | $\geq 7.0$     | mm        |
| Comparative tracking index   |  |       | CTI        | 175            |           |
| Isolation resistance   | $V_{IO} = 500\text{ V}, T_{amb} = 25\text{ }^{\circ}\text{C}$  |       | $R_{IO}$   | $\geq 10^{12}$ | $\Omega$  |
|  | $V_{IO} = 500\text{ V}, T_{amb} = 100\text{ }^{\circ}\text{C}$ |       | $R_{IO}$   | $\geq 10^{11}$ | $\Omega$  |
| Storage temperature  |  |       | $T_{stg}$  | - 55 to + 125  | °C        |
| Operating temperature  |  |       | $T_{amb}$  | - 55 to + 100  | °C        |
| Lead soldering time at 260 °C  |  |       |            | 10             | s         |

**Note**

- Stresses in excess of the absolute maximum ratings can cause permanent damage to the device. Functional operation of the device is not implied at these or any other conditions in excess of those given in the operational sections of this document. Exposure to absolute maximum ratings for extended periods of the time can adversely affect reliability.

| <b>ELECTRICAL CHARACTERISTICS</b> ( $T_{amb} = 25\text{ }^{\circ}\text{C}$ , unless otherwise specified) |  |             |      |      |      |               |
|--|--|-------------|------|------|------|---------------|
| PARAMETER  | TEST CONDITION                           | SYMBOL      | MIN. | TYP. | MAX. | UNIT          |
| <b>INPUT</b>   |  |             |      |      |      |               |
| Forward voltage  | $I_F = 20\text{ mA}$                     | $V_F$       |      | 1.25 | 1.5  | V             |
| Reverse current  | $V_R = 6.0\text{ V}$                     | $I_R$       |      | 0.1  | 10   | $\mu\text{A}$ |
| Capacitance  | $V_R = 0\text{ V}$                       | $C_O$       |      | 25   |      | pF            |
| <b>OUTPUT</b>  |  |             |      |      |      |               |
| Collector emitter breakdown voltage  | $I_C = 1.0\text{ mA}, I_F = 0\text{ A}$  | $BV_{CEO}$  | 60   |      |      | V             |
| Collector base breakdown voltage (IL66)  | $I_C = 10\text{ }\mu\text{A}$            | $BV_{CBO}$  | 60   |      |      | V             |
| Collector emitter leakage current  | $V_{CE} = 50\text{ V}, I_F = 0\text{ A}$ | $I_{CEO}$   |      | 1.0  | 100  | nA            |
| Capacitance collector emitter  | $V_{CE} = 10\text{ V}$                   |             |      | 3.4  |      | pF            |
| <b>COUPLER</b>   |  |             |      |      |      |               |
| Saturation voltage, collector emitter  | $I_C = 10\text{ mA}, I_F = 10\text{ mA}$ | $V_{CEsat}$ |      | 0.9  | 1.0  | V             |

**Note**

- Minimum and maximum values are testing requirements. Typical values are characteristics of the device and are the result of engineering evaluation. Typical values are for information only and are not part of the testing requirements.

| <b>CURRENT TRANSFER RATIO</b> ( $T_{amb} = 25\text{ }^{\circ}\text{C}$ , unless otherwise specified) |   |             |        |      |      |      |      |
|--|---|-------------|--------|------|------|------|------|
| PARAMETER  | TEST CONDITION                                  | PART        | SYMBOL | MIN. | TYP. | MAX. | UNIT |
| Current transfer ratio   | $I_F = 2.0\text{ mA}$ , $V_{CE} = 10\text{ V}$  | IL(D,Q)66-1 | CTR    | 100  | 400  |      | %    |
|  |   | IL(D,Q)66-2 | CTR    | 300  | 500  |      | %    |
|  | $I_F = 0.7\text{ mA}$ , $V_{CE} = 10\text{ V}$  | IL(D,Q)66-3 | CTR    | 400  | 500  |      | %    |
|  | $I_F = 2.0\text{ mA}$ , $V_{CE} = 5.0\text{ V}$ | IL(D,Q)66-4 | CTR    | 500  | 750  |      | %    |

| <b>SWITCHING CHARACTERISTICS</b> ( $T_{amb} = 25\text{ }^{\circ}\text{C}$ , unless otherwise specified) |  |        |      |      |      |               |  |
|---|--|--------|------|------|------|---------------|--|
| PARAMETER   | TEST CONDITION   | SYMBOL | MIN. | TYP. | MAX. | UNIT          |  |
| <b>NON SATURATED</b>  |  |        |      |      |      |               |  |
| Rise time -1, -2, -4  | $V_{CC} = 10\text{ V}$ , $I_F = 2.0\text{ mA}$ , $R_L = 100\text{ }\Omega$ | $t_r$  |      |      | 200  | $\mu\text{s}$ |  |
| Fall time -1, -2, -4  | $V_{CC} = 10\text{ V}$ , $I_F = 2.0\text{ mA}$ , $R_L = 100\text{ }\Omega$ | $t_f$  |      |      | 200  | $\mu\text{s}$ |  |
| Rise time -3  | $V_{CC} = 10\text{ V}$ , $I_F = 0.7\text{ mA}$ , $R_L = 100\text{ }\Omega$ | $t_r$  |      |      | 200  | $\mu\text{s}$ |  |
| Fall time -3  | $V_{CC} = 10\text{ V}$ , $I_F = 0.7\text{ mA}$ , $R_L = 100\text{ }\Omega$ | $t_f$  |      |      | 200  | $\mu\text{s}$ |  |


**TYPICAL CHARACTERISTICS** ( $T_{amb} = 25\text{ }^{\circ}\text{C}$ , unless otherwise specified)


Fig. 1 - Forward Voltage vs. Forward Current





 Fig. 3 - Normalized Non-Saturated and Saturated  $CTR_{CE}$  vs. LED Current

 Fig. 2 - Normalized Non-Saturated and Saturated  $CTR_{CE}$  vs. LED Current


Fig. 4 - Non-Saturated and Saturated Collector Emitter Current vs. LED Current




Fig. 5 - Collector Base Photocurrent vs. LED Current




Fig. 8 - High to Low Propagation Delay vs. Collector Load Resistance and LED Current




Fig. 6 - Collector Emitter Current vs. LED Current




Fig. 9 - Low to High Propagation Delay vs. Collector Load Resistance and LED Current




Fig. 7 - Non-Saturated and Saturated  $h_{FE}$  vs. LED Current







Fig. 10 - Switching Waveform




iii66\_11  
Fig. 11 - Switching Schematic

**PACKAGE DIMENSIONS** in millimeters





Weight: ca. 0.50 g  
Creepage distance: > 6 mm  
Air path: > 6 mm  
after mounting on PC board





technical drawings according to DIN specifications




14770-1



ISO method A






i178006



i178007



**Option 7**

**Option 9**



18450-7

**PACKAGE MARKING (example)**



**Notes**

- Only options 1 and 7 reflected in the package marking
- The VDE logo is only marked on option 1 parts
- Tape and reel suffix (T) is not part of the package marking



## Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and/or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.

## Material Category Policy

**Vishay Intertechnology, Inc. hereby certifies that all its products that are identified as RoHS-Compliant fulfill the definitions and restrictions defined under Directive 2011/65/EU of The European Parliament and of the Council of June 8, 2011 on the restriction of the use of certain hazardous substances in electrical and electronic equipment (EEE) - recast, unless otherwise specified as non-compliant.**

**Please note that some Vishay documentation may still make reference to RoHS Directive 2002/95/EC. We confirm that all the products identified as being compliant to Directive 2002/95/EC conform to Directive 2011/65/EU.**

**Vishay Intertechnology, Inc. hereby certifies that all its products that are identified as Halogen-Free follow Halogen-Free requirements as per JEDEC JS709A standards. Please note that some Vishay documentation may still make reference to the IEC 61249-2-21 definition. We confirm that all the products identified as being compliant to IEC 61249-2-21 conform to JEDEC JS709A standards.**