



**Technical**

<b>Battery Charger:</b>	Class 2, Integrated Power Supply
<b>Plug:</b>	Direct Plug-In Matches Local Requirements
<b>Battery Type/Fit:</b>	NiMH: 2 or 4 AA/HR6, NiMH: 2 or 4 AAA/HR03
<b>Typical Weight:</b>	207 g
<b>Input:</b>	100-240V AC, 50-60 Hz, 7w
<b>Output:</b>	AA/HR6: 3.0V DC 360 mA AAA/HR03: 3.0V DC 180 mA
<b>Operating Temp:</b>	0°C - 35°C (32°F - 95°F)
<b>Dimensions:</b>	123 mm (H) x 72 mm (W) x 42 mm (D)

**BENEFITS**

**Great Value, New Sleek & Compact Design, Convenient Wall Plug-In**

**FEATURES**

**Independent Channel Charging**

- Fully Charges cells in 6 hours\*
- Charges both AA and AAA NiMH cells
- Ensures a full charge regardless of charge or battery capacity

**LED Indicates Charge**

- Red = Charging
- Green = Complete
- Flashing Red = Error/Abnormal battery or abnormal temperature

**Maintenance Charge Keeps Cells Fresh**

**International Charge Capability- device can be used worldwide with suitable converter plug**

**SAFETY**

**Microprocessor Controlled**

- Charge termination based on -dV/dt, temperature, and/or built-in timer
- Over-temperature shutoff- prevents overheat of cell
- Primary cell protection- will not charge non-rechargeable batteries
- Low voltage battery protection- prevents overheat and damage to cell
- Power protection circuit- resets whenever a battery is removed

**DURACELL**  
BATTERIES

Berkshire Corporate Park  
Bethel, CT 06801 U.S.A.  
Tel: Toll free 1.800.544.5454  
Web: www.duracell.com

\*Charge rate and time is dependent on cell capacity, discharge state, and operating temperature.

Information and contents in this data sheet are for reference purposes only. They do not constitute any warranty and representation is subject to change without notice. For most current information and further details, please contact Duracell.