

- Weather, water and dust resistant (IP65)
- Vandal resistant (20J BS EN 60068-2-75: 1997)
- Raised "home pip" on the "5" key
- High contrast keytops
- 4, 12 and 16 key formats

2000 SERIES Robust Keypads

Rapid,
responsive
and reliable
keypads for
industrial use




Storm Interface products
include technology protected by
international patents and design
registration. All rights reserved



Storm 2000 Series ruggedized Keypads are ideal for use in harsh industrial environments. They are constructed to survive in exposed, wet or dirty environments. Available in 4, 12 and 16 key configurations, these robust keypads can be fixed to the surface of a host enclosure or located beneath an aperture in a panel. Keys move with a positive "over-centre" action to provide a responsive tactile dynamic and reliable data entry. This excellent tactile response combined with a home pip and high contrast keypad characters make these keypads accessible for those with visual impairment.

Mounting & Connection Details

All dimensions are in mm



Connection Details for 4 Key Keypad

CONTACT CONNECTIONS

5 4 3 2 1
(As viewed from rear of keypad)

A	1
B	2
C	3
D	4

KEY LOCATION
(As viewed from front of keypad)

CONTACT MATRIX	
CONEC. PIN	ROW/COLUMN
1	A
2	B
3	C
4	B
5	A

Connection Details for 12 Key Keypad

CONTACT CONNECTIONS

8 7 6 5 4 3 2 1
(As viewed from rear of keypad)

A	1	2	3
B	4	5	6
C	7	8	-
D	7	-	-

KEY LOCATION
(As viewed from front of keypad)

CONTACT MATRIX	
CONEC. PIN	ROW/COLUMN
1	A
2	B
3	A
4	B
5	C
6	-
7	D
8	C

Connection Details for 16 Key Keypad

CONTACT CONNECTIONS

8 7 6 5 4 3 2 1
(As viewed from rear of keypad)

A	1	2	3	4
B	5	6	7	8
C	6	4	-	-
D	7	-	-	-

KEY LOCATION
(As viewed from front of keypad)

CONTACT MATRIX	
CONEC. PIN	ROW/COLUMN
1	A
2	B
3	A
4	B
5	C
6	A
7	D
8	C

Electrical

Contact Bounce	5ms (max)
Contact Resistance	100 ohms (max)
Insulation Resistance	50 Mohms (min)
Breakdown Voltage	500V AC (max 60 secs.)
Operating Voltage	24V DC (max)
Operating Current	50mA (max)

Mechanical

Operational Life	4 million cycles (min) per key
Keypoint Travel	1.4mm nominal
Actuation Force	180ms nominal
Connector	0.1" pitch, gold plated square pin, male connector

Environmental

Water / Dust Sealed	IP65 (when mounted to suitable enclosure)
Operational Temperature	-25°C to +85°C (Dry)

Material

Casing	General Service Polymer (black)
Keypoints	General Service Polymer (translucent)
Contact Circuit	Gold on Nickel Plated FR4

Part Numbers

2K04110[X]	4 key Pad - Cursor
2K04210[X]	4 Key Pad - Function
2K12010[X]	12 Key Pad - Calculator
2K12701[X]	12 Key Pad - Telephone
2K16010[X]	16 Key Pad - Calculator
2K16710[X]	16 Key Pad - Telephone



www.storm-interface.com

Whilst every effort is made to ensure details are correct at time of press, specifications are subject to change without notice.

Designed & produced by MK Design
mk@mkdesign.co.uk

Storm Interface products include technology protected by international patents and design registration. All rights reserved.

Storm is a trademark of Keymat Technology Ltd
Storm Interface is a trading name of Keymat Technology Ltd



FM 39602