

# XVEC2B5

## ORANGE STEADY LENS INTEGRAL LED

### 24VAC/DC



#### Main

Commercial Status	Commercialised
Range of product	Harmony XVE Optimum
Product or component type	Indicator bank
Beacon or indicator bank unit type	Illuminated unit
Signalling type	Steady
Component name	XVE
Light source	Orange integral LED
Bulb type	LED
[Us] rated supply voltage	24 V AC/DC

#### Complementary

Mounting diameter	2.76 in (70 mm)
Assembly style	Customer assembly
Connections - terminals	Screw clamp terminals: <= 1 x 1.5 mm <sup>2</sup> with cable end
Marking	CE
Overld and short-circuit prot	0.63 A
[Ui] rated insulation voltage	250 V conforming to IEC 60947-1
Nominal voltage limit	0.85...1.1 Un conforming to IEC 60947-5-1
Current consumption	< 25 mA
[Uimp] rated impulse withstand voltage	4 kV conforming to IEC 60947-1
Luminance	74.32 fc (800 cd/m <sup>2</sup> )
CAD overall width	2.76 in (70 mm)
CAD overall height	2.05 in (52 mm)
CAD overall depth	2.76 in (70 mm)
Product weight	0.17 lb(US) (0.077 kg)

#### Environment

Standards	EN/IEC 60947-1 EN/IEC 60947-5-1
Product certifications	CCC CSA UL
Ambient air temperature for storage	-40...158 °F (-40...70 °C)
Ambient air temperature for operation	-13...131 °F (-25...55 °C)
Class of protection against electric shock	Class I plastic tube mounting conforming to IEC 61140 Class I aluminium tube mounting conforming to IEC 61140
Protective treatment	TC
IP degree of protection	IP42 in vertical position conforming to IEC 60529 IP40 in any position except vertical position conforming to IEC 60529

Ordering and shipping details

Category	22616 - XVE OPTIMUM STACKLIGHTS
Discount Schedule	XV
GTIN	00785901869191
Nbr. of units in pkg.	1
Package weight(Lbs)	0.17
Returnability	Y
Country of origin	CZ