Lista Drawer Accessories

























SATISFY YOUR EVERY STORAGE NEED WITH OUR CUSTOMIZED DRAWER STORAGE OPTIONS

Lista Drawer Accessories

How to Order Custom Drawer Partitions and Dividers 118

Partitions 119

Dividers 119

Plastic Boxes 120

Conductive Plastic Boxes 120

Grooved Trays 120

Conductive Grooved Trays

Other Accessories 121-122

Milling Cutter Holders

Corrugated Steel Supports

Holding Pins 121

Slotted Tool Supports 121

Arbor Holders 121

Allen Key Holders

Molded Collet Holders 121

File Drawer Inserts 122

Plastic Angular Supports 122

Drawer Liners 122

Sliding Accessory Tray 122

Foam Drawer Liners 122

Lista drawer partitioning accessories provide complete protection and systematic organization for whatever you need to store - from tools to electronic components to small parts.

Customized compartments

The partitioning slots on the sidewalls of all Lista drawers are ²¹/₃₂" apart, both front to back and side to side, providing for more possible partitioning configurations than any other drawer in the industry. Anything you need to store has its specific compartment, is well protected and easily retrievable.

Solving difficult problems

Our experienced technical support and design team is pleased to review your inventory and assist you in solving any difficult storage problem, free of charge.

These are the basic steps required for ordering custom drawer partitions and dividers from Lista.

EASY-ORDER DRAWER INTERIOR SETS:

Preconfigured drawer interior sets for many popular drawer layouts are available for all sizes of Lista drawers:

NW Width page 17 MP Width page 21 SC Width pages 26-27 MW Width page 31 DW Width page 35 CL Width page 47 ST Width page 51 HS Width page 55

For tool holders, tool trays for drawers, drawer frames and other CNC and machine tool accessories, please see pages 90-91.

The Lista drawer subdivision system

Lista drawers are subdivided using 2 basic accessories: partitions, which divide the drawer into rows, and dividers, which define compartments within those rows.


The part designations for ordering partitions or dividers have 3 components:

- A letter or letters prefix indicating the part. "P" is for slotted drawer partitions, "LP" is for plain drawer partitions, and "D" is for aluminum drawer dividers (for descriptions, see page 119).
- A number indicating the drawer model (height) number, and therefore the height of the partition or divider.
- 3. A number indicating the length of the partition or divider in slots/units.

Drawer slot/unit dimensions are as follows:

NW Width 19 units W x 36 units D
MP Width 27 units W x 36 units D
Standard Width 36 units W x 36 units D
Mid-Width 64 units W x 36 units D
Double Width 78 units W x 36 units D
CL Width 27 units W x 27 units D
ST Width 36 units W x 27 units D
HS Width 54 units W x 27 units D

The examples to the right use an HS Width shallow depth cabinet drawer (40 1/4" wide) which has 54 slots/units side to side and 27 slots/units front to back.



Slotted and Plain Drawer Partitions


Partitions can divide a drawer into either horizontal or vertical rows.

The length of the partitions used in a drawer is determined by the number of slots/units in the drawer, front to back or side to side.



EXAMPLE A: if you want to divide a model HS100F drawer into 3 sections each, running front to back, order 2 slotted drawer partitions **P100-27**.

P = slotted drawer partition 100 = drawer height model number 27 = units front to back




EXAMPLE B: if you want to divide the same drawer into 3 sections running side to side, order 2 slotted partitions **P100-54**.

P = slotted drawer partition 100 = drawer height model number 54 = units side to side



Aluminum Drawer Dividers

To further divide drawers into smaller compartments, order aluminum drawer dividers. To divide each of the 3 sections in the previous examples into 3 smaller sections, you would order 2 drawer dividers for each large section or a total of 6. **To subdivide drawers using dividers, you must specify slotted drawer partitions.**




EXAMPLE A: if you have divided the drawer into 3 equal sections running front to back, each section is 18 slots/ units wide $(54 \div 3 = 18)$. So order 6 **D100-18** dividers.

D = drawer divider

100 = drawer height model number

18 = units wide



EXAMPLE B: if you have divided the drawer into 3 equal rows running side to side, each section is 9 slots/units wide $(27 \div 3 = 9)$. So order 6 **D100-9** dividers.


D = drawer divider

100 = drawer height model number

9 = units wide

Slotted Drawer Partitions

These slotted steel sheet partitions are the basic drawer dividers. They divide drawers into small or large compartments by length and/or width. Partition ends slide easily into drawer sidewall slots and can be bolted to the perforated drawer bottom. Partitions are slotted at ²¹/₃₂" intervals to match the



drawer sidewalls and should be ordered to match particular drawer heights, widths and depths (see chart). Color: gray.

FOR USE WITH DRAWER HEIGHT							
75	100/125	150/175	200/225	250	300/350/400		
		PARTITION	I HEIGHT				
2"	3"	5"	7"	8 ¹⁵ /16"	10 ¹⁵ /16"		
	P	ARTITION PA	RT NUMBER				
P75-27	P100-27	P150-27	P200-27	P250-27	P300-27		
P75-30	P100-30	P150-30	P200-30	-	-		
P75-36	P100-36	P150-36	P200-36	P250-36	P300-36		
P75-54	P100-54	P150-54	P200-54	P250-54	P300-54		
P75-64	P100-64	P150-64	P200-64	P250-64	P300-64		
P75-78	P100-78	P150-78	P200-78	P250-78	P300-78		
	2" P75-27 P75-30 P75-36 P75-54 P75-64	75 100/125 2" 3" P75-27 P100-27 P75-30 P100-30 P75-36 P100-36 P75-54 P100-54 P75-64 P100-64	75 100/125 150/175 PARTITION 2" 3" 5" PARTITION PA P75-27 P100-27 P150-27 P75-30 P100-30 P150-30 P75-36 P100-36 P150-36 P75-54 P100-54 P150-54 P75-64 P100-64 P150-64	75 100/125 150/175 200/225 PARTITION HEIGHT 2" 3" 5" 7" PARTITION PART NUMBER P75-27 P100-27 P150-27 P200-27 P75-30 P100-30 P150-30 P200-30 P75-36 P100-36 P150-36 P200-36 P75-54 P100-54 P150-54 P200-54 P75-64 P100-64 P150-64 P200-64	75 100/125 150/175 200/225 250 PARTITION HEIGHT 2" 3" 5" 7" 8 15/16" PARTITION PART NUMBER P75-27 P100-27 P150-27 P200-27 P250-27 P75-30 P100-30 P150-30 P200-30 - P75-36 P100-36 P150-36 P200-36 P250-36 P75-54 P100-54 P150-54 P200-54 P250-54 P75-64 P100-64 P150-64 P200-64 P250-64		

Plain Drawer Partitions

For use when drawers will not be subdivided using dividers. These non-slotted steel sheet partitions divide drawers into larger compartments either by length or width. Bottom strips can be bolted to the perforated drawer bottom for additional stability, and the ends slide into slots in drawer sidewalls or slotted drawer partitions. Plain parti-



tions should be ordered to match drawer sidewall height. Color: gray.

	FOR USE WITH DRAWER HEIGHT						
	75	100/125	150/175	200/225	250	300/350/400	
			PARTITION	I HEIGHT			
	2"	3"	5"	7"	8 ¹⁵ /16"	10 ¹⁵ /16"	
LENGTH IN							
UNITS/INCHES		P	ARTITION PA	RT NUMBER			
19 / 12 ¹ /2"	LP75-19	LP100-19	LP150-19	LP200-19	LP250-19	LP300-19	
24 / 16"	LP75-24	LP100-24	LP150-24	LP200-24	-	-	
27 / 18"	LP75-27	LP100-27	LP150-27	LP200-27	LP250-27	LP300-27	
30 / 20"	LP75-30	LP100-30	LP150-30	LP200-30	-	-	
36 / 24"	LP75-36	LP100-36	LP150-36	LP200-36	LP250-36	LP300-36	
54 / 36 1/8"	LP75-54	LP100-54	LP150-54	LP200-54	LP250-54	LP300-54	
64 / 42 ¹³ /16"	LP75-64	LP100-64	LP150-64	LP200-64	LP250-64	LP300-64	
78 / 52 ³ /16"	LP75-78	LP100-78	LP150-78	LP200-78	LP250-78	LP300-78	

Drawer Slot Snap-On Label Holders

Clip-on label holders (not included, see to right) can be attached to these durable red plastic holders, which fit all slotted partitions or slotted drawer walls for labeling adjacent drawer contents. Angled for easier reading.





Aluminum Drawer Dividers

Dividers subdivide drawers into smaller compartments for specialized storage. Aluminum dividers come in a variety of lengths and slip into slots in drawer sidewalls and/or slotted drawer partitions. Top edges are rounded and smooth for safety. Full-width angled top can accommodate most text and barcode labels. Dividers can be fastened to



drawer bottom for greater stability (fasteners included). Dividers should be ordered to match drawer sidewall height.

		FOR	USE WITH D	RAWER HEIG	HT	
	75	100/125	150/175	200/225	250	300/350/400
			DIVIDER	HEIGHT		
	2"	3"	5"	7"	8 ¹⁵ /16"	10 ¹⁵ /16"
LENGTH IN						
UNITS/INCHES*			DIVIDER PAR	T NUMBER		
3 / 1 7/8"	D75-3	D100-3	-	-	-	-
4 / 2 1/2 "	D75-4	D100-4	-	-	-	-
5 / 3 1/16"	D75-5	D100-5	-	-	-	-
6 / 3 ⁷ /8"	D75-6	D100-6	D150-6	D200-6	-	-
7 / 41/2"	D75-7	D100-7	D150-7	D200-7	-	-
8 / 5 3/16"	D75-8	D100-8	D150-8	D200-8	-	-
9 / 5 ⁷ /8"	D75-9	D100-9	D150-9	D200-9	D250-9	D300-9
10 / 6 %16"	D75-10	D100-10	D150-10	D200-10	D250-10	D300-10
12 / 7 7/8"	D75-12	D100-12	D150-12	D200-12	D250-12	D300-12
15 / 9 ⁷ /8"	D75-15	D100-15	D150-15	D200-15	D250-15	D300-15
18 / 11 ⁷ /8"	D75-18	D100-18	D150-18	D200-18	D250-18	D300-18

^{*}usable space is 3/8" less

Clip-on Label Holder

Black plastic label holders easily clip onto Lista aluminum drawer dividers, plastic boxes and tray dividers. When labeled using Lista Script software, DLH-1 holders use 18.787 labels; DLH-2 holders use 18.786 labels; DLH-3 holders use 18.785 labels (see page 120 to order label sheets).



FOR USE WITH			
plastic box dividers PB-24D, PB-24ASD			
slotted grooved tray			
dividers STD-2, STD-3, STD-4			
conductive slotted grooved tray dividers STD-3AS, STD-4AS			
grooved tray divider 2GTD			
drawer slot snap-on label holder SLH-1			
drawer slot snap-on label holder SLH-2			
all aluminum drawer dividers			



Plastic Boxes

Made of high impact polystyrene (HIPS) red plastic, these boxes are for storing small parts. Boxes slip in and out of drawers or plastic box rails for easy loading and dispensing and have label holder slots. Boxes should be ordered to match particular drawer height.



PART NO.	FOR DRAWER	LXWXH	MAX.	BOXES F	PER D	RAWER	/HOUSI	NG STY	LE
	NUMBER/HT.		NW	MP/ST	SC	MW	DW	CL	HS
PB-1*		3" x 3" x 1"	36	48	64	112	136	36	72
PB-2		3" x 3" x 1"	36	48	64	112	136	36	72
PB-3		3" x 6" x 1"	16	24	32	56	68	18	36
PB-4		6" x 6" x 1"	8	12	16	28	32	9	18
PB-5	75	3" x 3" x 2"	36	48	64	112	136	36	72
PB-6	75	3" x 6" x 2"	16	24	32	56	68	18	36
PB-7	75	6" x 6" x 2"	8	12	16	28	32	9	18
PB-8	100	3" x 6" x 3"	16	24	32	56	68	18	36
PB-9	100	6" x 6" x 3"	8	12	16	28	32	9	18
PB-24	75	2" x 4" x 2"	36	54	72	126	156	24	81
PB-8D	divider for PB-8	3							
PB-24D	divider for PB-2	24							

^{*}PB-1 box has a fixed center divider that makes 2 compartments - 3" x 1 1/2"

Conductive Plastic Boxes



Made of conductive black high impact polystyrene (HIPS) for storing electrostatically sensitive components or devices. Boxes slip in and out for easy loading and dispensing and have label holder slots. Order to match drawer height.



PART NO.	FOR DRAWER	LXWXH	MAX.	MAX. BOXES PER DRAWER/HOUSING STYLE						
	NUMBER/HT.		NW	MP/ST		MW	DW	CL	HS	
PB-1AS		3" x 3" x 1"	36	48	64	112	136	36	72	
PB-2AS		3" x 3" x 1"	36	48	64	112	136	36	72	
PB-3AS		3" x 6" x 1"	16	24	32	56	68	18	36	
PB-4AS		6" x 6" x 1"	8	12	16	28	32	9	18	
PB-5AS	75	3" x 3" x 2"	36	48	64	112	136	36	72	
PB-6AS	75	3" x 6" x 2"	16	24	32	56	68	18	36	
PB-7AS	75	6" x 6" x 2"	8	12	16	28	32	9	18	
PB-8AS	100	3" x 6" x 3"	16	24	32	56	68	18	36	
PB-9AS	100	6" x 6" x 3"	8	12	16	28	32	9	18	
PB-24AS	75	2" x 4" x 2"	36	54	72	126	156	24	81	
PB-8ASD	divider for PB-8	BAS								
PB-24ASD	divider for PB-2	24AS								

Angled Label **Holders** for Plastic **Boxes**



Fits into slot in plastic boxes. Transparent label protectors included.

PART NO.	FOR USE WITH
X280*	plastic boxes (red)
X280-AS	conductive plastic boxes (black)

*not for use with PB-24 box

Grooved



steel divider fits into slots in grooved tray to separate and label contents.

PART NO.	
2GTD	

Grooved Trays

These high impact red ABS plastic travs are for individual storage of side sensitive tools such as taps and reamers. Tools are held in place by wedge-shaped grooves which prevent side-to-side movement in the drawer. In 2 parts, each part with end tongues to fit slotted partitions or drawer sidewall. Each



2-part tray is 9 units (153mm) wide x 97mm deep. Sectioned off with D-9 drawer dividers. Larger trays in the set are slotted for clip-on label holders (not included, see page 119). Grooved tray dividers (see to left) not included.

PART NO.	FOR MAXIMUM TOOL DIAMETER	NO. OF GROOVES	
PGT-19	5/16" (8mm)	11	
PGT-29	⁹ /16" (14mm)	8	
PGT-39	³ / ₄ " (20mm)	6	

Slotted Grooved Trays

Trays are for storage of drills, gauges, mills, etc. Made of durable high impact polystyrene (HIPS) red plastic with end tongues so units snap together to form a continuous tray. Slotted at 9/16" increments, plastic dividers subdivide individual grooves into smaller compartments. Each 6" x 6" tray can have 2, 3, or 4 grooves. Clip-on label holders not included (see page 119).



PART NO.	FOR MAXIMUM	NO. OF GROOVES	SLOTTED TRAY	AVERAGE QTY.
	TOOL		DIVIDERS	REQUIRED PER
	DIAMETER		PART NO.	SLOTTED TRAY
SGT-4	1 ¹ /4" (33mm)	4	STD-4	5 dividers
SGT-3	1 ³ /4" (45mm)	3	STD-3	4 dividers
SGT-2	2 ³ /4" (70mm)	2	STD-2	3 dividers

Conductive Slotted Grooved Trays



Trays are for storage of electrostatically sensitive components and MOS semiconductor devices. Made of conductive black high impact polystyrene (HIPS). Each groove is slotted at 9/16" intervals with end tongues so units snap together to form a continuous tray. Clip-on label holders (see page 119) not included.



PART NO.	FOR MAXIMUM	NO. OF GROOVES	SLOTTED TRAY	AVERAGE QTY.
	TOOL		DIVIDERS	REQUIRED PER
	DIAMETER		PART NO.	SLOTTED TRAY
SGT-4AS	1 ¹ / ₄ " (33mm)	4	STD-4AS	5 dividers
SGT-3AS	1 ³ / ₄ " (45mm)	3	STD-3AS	4 dividers

Paper Label Sheets

Perforated sheets of label paper allow printing of labels with Lista Script software that fit perfectly into the wide variety of Lista label-holding tabs and covers. One package of 18.784 drawer handle labels is included with each Lista cabinet.

PART NO.	LABEL SIZE	FOR USE WITH	SHEETS/PKG.	LABELS/SHEET
18.784	210mm x 22mm	all hinged drawer handle covers	5 sheets (A4 size)	30
18.785	47mm x 18mm	DLH-3 label holders	2 sheets (A4 size)	52
18.786	47mm x 12mm	X280 and X280-AS label holders	2 sheets (A4 size)	76
		DLH-2 label holders		
18.787	27mm x 12mm	DLH-1 label holders	2 sheets (A4 size)	133
18.932	52.5mm x 18mm	self-adhesive label holders	2 sheets (A4 size)	52



Milling Cutter Holders

Tools with center holes are put over these holders for non-slip stability in the drawer. Red high-impact plastic holders can be fastened together to any required height and are bolted to perforated drawer bottom. Nuts are included.

PART NO.	FOR ARBOR-HOLE SIZE
CH-1	¹ /2" (12mm)
CH-2	⁵ /8" (15.5mm)
CH-3	⁷ /8" (21.5mm)
CH-4	1" (25mm)
CH-8	1 ¹ /16" (26.5mm)
CH-5	1 ¹ / ₄ " (31mm)
CH-6	1 ¹ /2" (37.5mm)
CH-9	1 ⁹ /16" (39.5mm)
CH-7	2" (49.5mm)



Corrugated Steel Supports

For holding arbors, punches, drifts, etc., with 17 recesses. Held with plain partition. Pressed steel sheet, electrophoretically deposited, stoved enamel. Finished in gray.

PART NO.	LENGTH	
X1152	18"	




Holding Pins

Galvanized steel rods with screw bottoms are bolted to perforated drawer bottom for positioning and holding irregularly shaped tools. Nuts included.

PART NO.	DIAMETER	HEIGHT	
HP-1	¹ /4" (6mm)	1" (26mm)	
HP-2	¹ /4" (6mm)	2" (52mm)	
HP-3	1/4" (6mm)	3" (77mm)	





Slotted Tool Supports

These 1/16" thick, 24" long aluminum slotted carriers are perfect for storing wrenches, etc. Bottom strip is bolted to perforated drawer bottom. Fasteners included. Ordered individually.

PART NO.	HEIGHT	SLOT OPENING
X214	1 ¹ /16" (26.5mm)	1/4" (7mm)
X36	1 ¹ / ₁₆ " (26.5mm)	3/16" (5mm)



Arbor Holders

For horizontally storing tools larger than standard grooved trays. Supports are bolted in pairs to perforated drawer bottom. Elongated slots for fastening bolts allow precise positioning for particular tool diameter. Made of durable high impact red plastic. Fasteners included. Comes in pairs.

PART NO.	SIZE
AH	1" W x 3" D x 2" H
	25mm W x 75mm D x 50mm H



Metric Allen Key Holders

Red high impact plastic trays for sets of allen wrenches 1.5mm to 10mm.

PART NO.	SIZE	
AKH	6" wide x 6" deep x 1" high	



Molded Collet Holders

For the storage of standard collets in drawers. Trays sit over partition slots on the sides of the drawer, so the full usable width and depth of the drawer may be used. Each collet holder is 12" wide x 9 1/2" deep x 2" high.

PART NO.	HOLDS
CH-25MM/R8-72	(72) R8 collets/
	25mm straight tools
CH-32MM/C5-42	(42) C5 collets/
	32mm straight tools

Collet Holders Per Drawer	
DRAWER SIZE	MAX. HOLDERS
NW	2
MP	2
SC	4
MW	6
DW	10
ST	2
HS	3



File Drawer Inserts

Fits into a 300 height drawer and converts it into a useable file drawer for either letter- or legal-sized files.

PART NO.	USE	NO. PER	ORIENTA.
	WITH	DRAW.	
FFH19	NW*	1	side-to-side
FFH27	MP	1	side-to-side
	ST	1	front-to-back
	HS	2	front-to-back
FFH36	MP	1	front-to-back
	SC	1	front-to-back
	MW	3	front-to-back
	DW	3	front-to-back


*all NW300N-FFH and NW325N-FFH drawers come with side supports for front-to-back file storage



Plastic Angular Supports

Pairs of supports hold files and small tools. Twelve segments, red only.

PART NO.	SIZE	
X1153	3 ½" W x 17 ½" D x ½" H	
	80mm W x 445mm D x 12mm H	



Drawer Liners

- Non-slip polyester mesh liner protects items from shifting or sliding.
 Protects drawer bottom from scratches and dents. Liner is nontoxic, washable and treated to inhibit mold and mildew.
- Plastic liners are 1/16" thick, clear only.

PART NO.	FOR USE WITH DRAWER
Mesh liner	
NWMDL	NW
MPMDL	MP, ST
SCMDL	SC
MWMDL	MW
DWMDL	DW
CLMDL	CL
HSMDL	HS
Plastic liner	
NWPDL	NW
MPPDL	MP, ST
SCPDL	SC
MWPDL	MW
DWPDL	DW
HSPDL	HS



Sliding Accessory Tray

Tray fits into any 100 height or higher NW or MP Width drawer and can slide forward or back to allow access to the rest of the drawer contents. For use with 1" high plastic boxes (PB-1, PB-2, PB-3 and PB-4). Plastic boxes must be ordered separately – see page 120.

PART NO.	FOR USE WITH
AT19	NW width drawers
AT27	MP width drawers



Foam Drawer Liners

Shadowed foam drawer insert liners protect, identify and control valuable inventory. Using a 2-layer insert system, the upper blue foam liner cushions tools and components in perfectly-shaped cut-outs, while the bottom yellow rigid foam liner makes it easy to spot when a tool is missing from the drawer.

Foam drawer liner kits consist of the following:

- (5) sheets of 1/2" thick royal blue cross linked oil-resistant Tool Control Foam (polyethylene base, standard density 2#) with self-adhesive back
- (1) sheet of 1" thick royal blue cross linked oil-resistant Tool Control Foam (polyethylene base, standard density 2#) with self-adhesive back
- (6) sheets of ¹/₈" thick yellow highdensity cross linked Tool Control Foam (polyethylene base, standard density 2#)
- (6) vellum sheets for tracing your tools
- (1) Exacto[®] knife for cutting blue foam
- (1) 18" ruler for measuring
- (1) instruction booklet


PART NO.	DIMEN.	USE WITH DR.
FDL-18X24/LOK	18" x 24"	MP, ST
FDL-24X24/LOK	24" x 24"	SC
FDL-36X18/LOK	36" x 18"	HS

Foam Drawer Liner Sets for Other Lista Drawer Sizes

Foam liner sets may be ordered individually to fit all Lista drawer dimensions. Each set includes:

- (1) sheet of ½" or 1" thick royal blue cross linked oil-resistant foam with self-adhesive back
- (1) sheet of 1/8" thick yellow highdensity cross linked foam
- (1) instruction booklet

PART NO.	DIMEN.	THICK.	USE
		W	DRAW.
FDL-MP-1/2IN	18" x 24"	1/2"	MP
FDL-SC-1/2IN	24" x 24"	1/2"	SC
FDL-MW-1/2IN	42 ¹³ /16" x 24	" 1/2"	MW
FDL-DW-1/2IN	52 ³/16" x 24"	1/2"	DW
FDL-ST-1/2IN	24" x 18"	1/2"	ST
FDL-HS-1/2IN	36 ½" x 18"	1/2"	HS
FDL-MP-1IN	18" x 24"	1"	MP
FDL-SC-1IN	24" x 24"	1"	SC
FDL-MW-1IN	42 ¹³ /16" x 24	" 1"	MW
FDL-DW-1IN	52 ³/16" x 24"	1"	DW
FDL-ST-1IN	24" x 18"	1"	ST
FDL-HS-1IN	36 ½" x 18"	1"	HS



Other Options

- Foam liners can be custom made to your exact specifications, including designing, cutting and labeling the inserts for your specific tool storage requirements.
- Technical grade foam inserts are available for medical, crime lab or archival storage/ museum applications. This foam does not off-gas, and can be sterilized.
- Contact your Lista representative for details.