


Internal Schematic Diagram



Description:

The 2N5415 are high voltage silicon epitaxial planar PNP transistors in JEDEC TO-39 metal case designed for use in consumer and industrial line-operated applications.

These devices are particularly suited as drivers in high-voltage low current inverters, switching and series regulators.

Feature:

- PNP transistors

Absolute Maximum Ratings

Parameter	Symbol	Value	Unit
Collector-Base Voltage ($I_E = 0$)	V_{CBO}	-200	V
Collector-Emitter Voltage ($I_B = 0$)	V_{CEO}		
Emitter-Base Voltage ($I_C = 0$)	V_{EBO}		
Collector Current	I_C	-1	A
Base Current	I_B	-0.5	
Total Dissipation at $T_C \leq 25^\circ\text{C}$	P_{tot}	10	W
Total Dissipation at $T_a \leq 50^\circ\text{C}$		1	
Storage Temperature	T_{stg}	-65 to 200	$^\circ\text{C}$


Thermal Data

Parameter	Symbol	Value	Unit
Maximum Thermal Resistance Junction-case	$R_{thj-case}$	17.5	°C/W
Maximum Thermal Resistance Junction-ambient	R_{thj-a}	175	

Electrical Characteristics ($T_C = 25^\circ\text{C}$ unless otherwise noted)

Parameter	Test Conditions	Symbol	Min.	Typ.	Max.	Unit
Collector Cut-off Current ($I_E = 0$)	2N5415 $V_{CB} = -175\text{V}$	I_{CBO}	-	-	-50	μA
Collector Cut-off Current ($I_B = 0$)	$V_{CE} = -150\text{V}$	I_{CEO}	-	-	-50	
Emitter Cut-off Current ($I_C = 0$)	2N5415 $V_{EB} = -4\text{V}$	I_{EBO}	-	-	-20	
Collector-Emitter Sustaining Voltage	2N5415 $I_C = -10\text{mA}$	V_{CEO}^* (sus)	-200	-	-	V
Collector-Emitter Saturation Voltage	$I_C = -50\text{mA}$ $I_B = -5\text{mA}$	$V_{CE(sat)}^*$	-	-	-2.5	
Base-Emitter Voltage	$I_C = -50\text{mA}$ $V_{CE} = -10\text{V}$	V_{BE}^*	-	-	1.5	
DC Current Gain	2N5415 $I_C = -50\text{mA}$ $V_{CE} = -10\text{V}$	h_{FE}^*	30	-	150	-
Small Signal Current Gain	$I_C = -5\text{mA}$ $V_{CE} = -10\text{V}$ $f = 1\text{KHz}$	h_{fe}	25	-	-	-
Transition frequency	$I_C = -10\text{mA}$ $V_{CE} = -10\text{V}$ $f = 5\text{MHz}$	f_T	15	-	-	MHz
Collector Base Capacitance	$I_E = 0$ $V_{CB} = -10\text{V}$ $f = 1\text{MHz}$	C_{CBO}	-	-	25	pF

*Pulsed: Pulse Duration = 300ms, Duty Cycle 1.5%.



TO-39 Mechanical Data

Dimension	mm			Inches		
	Min.	Typ.	Max.	Min.	Typ.	Max.
A	12.7	-	-	0.5	-	
B	-	-	0.49	-	-	0.019
D	-	-	6.6	-	-	0.26
E	-	-	8.5	-	-	0.334
F	-	-	9.4	-	-	0.37
G	5.08	-	-	0.2	-	-
H	-	-	1.2	-	-	0.047
I	-	-	0.9	-	-	0.035
L	45° (Typical)					

Part Number Table

Description	Part Number
Transistor	2N5415

Important Notice : This data sheet and its contents (the "Information") belong to the members of the Premier Farnell group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp is the registered trademark of the Group. © Premier Farnell plc 2012.