



Features & Benefits

- Shielded design for improved EMI performance
- Suitable for Gigabit Ethernet applications and beyond
- Ultra-slimline design
- Colour coded for quick and accurate termination
- Interchangeable with all other Euro modules and blanks
- Individually QA tested
- Easy to use shield connection

Specification

Width	25mm
Depth	22mm
Height	50mm
Recommended Back-box Depth	32mm
Material	Polycarbonate/ABS thermoplastic resin, with grade UL94 VO at 1.5mm flame retardancy
Finish	High gloss
IDC Labels	Colour coded labels to T568B
Cable Guide	Integrated earth connection / cable tie position
Sockets	High performance shielded RJ45
IDC Blocks	Industry standard IDC blocks
Conforms to	ANSI/TIA-568-C.2 Category 6 Specification

Ordering Information

Product Description	Part Number
Cat 6 FTP Compact Euro Module	008-000-001-30

The Connectix Category 6 FTP Compact Module provides the performance needed for present and next generation data communications networks and applications, including Gigabit Ethernet, with the added benefit of shielding to minimise the risk of EMI. The use of next generation components and specially designed boards allow a bandwidth of 250MHz to be achieved in a shielded package.

Category 6 compact modules can be fitted into single or dual gang Euro faceplates and can be combined with quarter blanks and/or voice modules to provide the required configuration.

The compact design provides one of the shallowest wall outlets on the market; making them the ideal solution wherever back-box depth is a problem.

The modules are fully compliant with the ANSI/TIA Category 6 standards. When used in conjunction with Connectix Category 6 FTP Patch Panels and FTP Cable the user will get a link performance exceeding Category 6 requirements.

