



**Tripp Lite**  
1111 West 35th Street  
Chicago, IL 60609 USA  
Telephone: +(773) 869 1234  
E-mail: [saleshelp@tripplite.com](mailto:saleshelp@tripplite.com)

## Model #: UL24RA-15

### Waber-by-Tripp Lite Power Strip with 6 Right-Angle Outlets and 15-ft. Cord



#### Highlights

- 6 outlets turned 90 degrees
- 12.5" length
- 15 ft. cord
- Lighted master switch

#### Description

The Waber-by-Tripp Lite UL24RA-15 Power Strip offers a convenient method of power distribution in workbench, wallmount or floor mount applications. Includes 6 NEMA 5-15R output receptacles with 1.625 inch center-to-center spacing, 15 foot AC line cord and keyhole mounting tabs for installation in a wide variety of applications. Right angle outlet orientation better accommodates large transformer plugs. Corded, multi-outlet strip reduces cabling clutter and enables the connection of multiple electrical devices to a single AC wall socket. Unfiltered electrical pass-through makes UL24RA-15 ideal for distributing alternate waveform UPS or generator power. Features rugged all-metal housing, lighted power switch with transparent guard to prevent accidental shutoff, 15 amp resettable circuit breaker and attractive blue/gray color scheme.

PLUG/OUTLETS - Input: NEMA 5-15P/Output: 6 NEMA 5-15R

ELECTRICAL - 120VAC, 50/60Hz, 15A (Requires standard NEMA 5-15R wall receptacle)

FORMAT - Corded power distribution strip

#### Applications

- Offers multiple outlet power distribution in workbench, wallmount or floor mount applications. Unfiltered electrical pass-through makes UL24RA-15 ideal for distributing alternate waveform UPS or generator power to protected equipment.

#### Package Includes

- UL24RA-15 Power Strip
- Warranty information
- Instruction manual

#### Features

- Multi-outlet power strip offers convenient power distribution in workbench, wallmount or floor mount applications
- Includes 6 NEMA 5-15R output receptacles with 1.625 inch center-to-center outlet spacing
- Lighted power switch with transparent snap-over guard to prevent accidental shutoff
- Keyhole mounting tabs support permanent installation on a wide variety of surfaces
- Right angle outlet orientation better accommodates large transformer plugs
- UL1363 (USA), cUL (Canada)
- 15 amp power handling capacity with circuit breaker

- 15 foot AC line cord

## Specifications

<b>OUTPUT</b>	
Frequency compatibility	50 / 60 Hz
Circuit Breaker (amps)	15
Outlet quantity / type	6 Nema 5-15R
Outlet spacing	1.625 in.
Outlet orientation	Single row of 6 arranged with right-angle outlet orientation
<b>INPUT</b>	
Nominal Input Voltage(s) Supported	120V AC
Recommended Electrical Service	15A 120V
Input connection type	Nema 5-15P
Input cord length (ft.)	15
Input cord length (m)	4.572
Input cord gauge, type	14 gauge, SJT
Voltage compatibility (VAC)	120
<b>LEDS ALARMS &amp; SWITCHES</b>	
Switches	Lighted 2 position switch controls power to all outlets
Locking switch cover	Transparent on/off switch cover prevents accidental turn-off
<b>PHYSICAL</b>	
Unit Dimensions (HWD/in)	12.5 x 2.5 x 1.5
Unit Dimensions (HWD/cm)	31.75 x 6.35 x 3.8
Material of construction	Metal
Integrated keyhole mounting tabs	Keyhole mounting tabs enable mounting to a variety of surfaces
Receptacle Color	Black
AC line cord color	Black
Outlets center to center measurement	41.3mm
Keyhole slot center to center measurement	261.92mm
<b>CERTIFICATIONS</b>	
UL1363 (Power Tap)	UL1363
cUL / CSA (Canada)	cUL
<b>WARRANTY</b>	
Product Warranty Period (Worldwide)	Lifetime limited warranty

---

More information, including related products, owner's manuals, and additional technical specifications, can be found online at [www.tripplite.com/en/products/model.cfm?variables.txtModelID=1958](http://www.tripplite.com/en/products/model.cfm?variables.txtModelID=1958).

---

Copyright © 2013 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.