

Cable Multicore

pro-POWER


RoHS
Compliant




Product Description:

Part Number	3313	3314	3315	3316	3317
Application	For Internal or external wiring - Hi Impact Resistant cable.				
Multi-construction	2 Cores	3 Cores	3 Cores	5 Cores	5 Cores
Construction	Bare Copper				
	2 Cores	3 Cores	3 Cores	5 Cores	5 Cores
Construction	1.38	1.38	1.78	1.38	1.78
Stranded Dia.(+/-0.08mm)	1.38	1.38	1.78	1.38	1.78
Insulation	FR-PVC				
Thickness	0.6	0.6	0.75	0.6	0.75
Insulation Dia.(+/-0.1mm)	2.63	2.63	3.32	2.63	3.32
Insulation Colour	Blue & Brown	Green / Yellow, Brown, Blue	Brown, Blue, Green / Yellow	Brown, Blue, Black, Grey, Green / Yellow	Blue, Brown, Grey, Black, Green / Yellow
Filling	Chalk				
Inner Jacket	PVC				
Thickness (mm)	1	1	1	1	1.1
Dia.(+/-0.15mm)	6.95	7.35	8.9	8.8	10.7
Outer Jacket	PVC				
Thickness (mm)	0.8	0.8	1	0.8	1.1
Dia.(+/-0.15mm)	8.65	9.05	11.1	10.5	12.9
Marking	2 × 1.5mm ² PVC/PVC to BS 6500 [Meter Mark]	3 × 1.5mm ² PVC/PVC to BS 6500 [Meter Mark]	3 × 2.5mm ² PVC/PVC to BS 6500 [Meter Mark]	5 × 1.5mm ² PVC/PVC to BS 6500 [Meter Mark]	5 × 2.5mm ² PVC/PVC to BS 6500 [Meter Mark]
Packaging	100m/Reel				
Electrical Characteristics:					
Max.Conductor DC Resistance at 20°C (Ω/Km)	<12.5	<12.5	<7.5	<12.5	<7.5
Rated Temperature (°C)	-20 to +80				
Rated Voltage (V)	300/500				
Min. Insulation DC Resistance at 20°C (MΩ × KM)	>500				


Design:




3313




3314



3315



3316



3317

Part Number Table

Description	Part Number
Multicore, 2 Core, 1.5mm ² , 100m, 500V	3313
Multicore, 3 Core, 1.5mm ² , 100m, 500V	3314
Multicore, 3 Core, 2.5mm ² , 100m, 500V	3315
Multicore, 5 Core, 1.5mm ² , 100m, 500V	3316
Multicore, 5 Core, 2.5mm ² , 100m, 500V	3317

Important Notice : This data sheet and its contents (the "Information") belong to the members of the Premier Farnell group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. pro-POWER is the registered trademark of the Group. © Premier Farnell plc 2012.