



Features & Benefits

Faceplates

- Standard or compact depth
- Single or dual gang option
- Industry standard size

Backboxes

- Tough shatter resistant material
- Designed for ease of use
- Uncluttered internal design

Specification

Dimensions	Faceplate			Back Box			
	Std	Dual	Compact	Sngl	Dual	Dry Line	
						Std	Dual
Width (mm)	87	148	87	87	148	87	148
Height (mm)	87	87	87	87	87	87	87
External Depth (mm)	15	15	9	32	32	34	
Internal Depth (mm)	-	-	-	29.5	29.5	32	

Ordering Information

Product Description	Part Number
Euro Faceplates	
Compact Elite Single Gang Euro Faceplate	008-001-003-70
Standard Elite Single Gang Euro Faceplate	008-001-003-50
Standard Elite Dual Gang Euro Faceplate	008-001-003-60
Euro 1/4 Blank	008-001-004-65
Euro 1/2 Blank	008-001-004-70
Back Boxes	
Dry Lining Single Gang	012-006-001-001
Dry Lining Double Gang	012-006-002-001
CCS 32mm White Single Gang	008-010-001-00
CCS 32mm White Dual Gang	012-007-002-321

Connectix Elite Faceplates are available in standard or compact depth, single and dual gang versions, and have been designed to fit all industry standard modules. The sleek curved Elite plate is available for high end applications.

All Connectix faceplates are supplied with fixing screws and come finished as standard in an attractive high gloss white.

Connectix backboxes are available in single and dual gang with a choice of surface mounted and flush mounted dry lined wall versions. Surface mount boxes feature knock outs for mini trunking adaptors.

Dry lining wall boxes are suitable for mounting into 6-14 mm thick board and can easily cope with irregular shaped aperture sizes. Swivelling snap out clamps will grip any standard thickness of building board tightly.

