


Plug-in unit in kit form for CompacPCI and VME64x applications



Illustration shows front panel
6 U, 4 HP



Dimension 3 / 6 U

Part no.: 20848-598

Features:

- Meets IEEE 1101.10 and IEC 60297-3-102 standards
- Codable to IEC 60297-3-103
- Front panel shielded, without offset
- Suitable for insertion and extraction forces up to 700 N (per pair)
- Designed for fitting of microswitches

Add to basket




Technical information:

Description	Height	Width
Front assembly	6 U	12 HP

Downloads:

3D PDF with CAD data (STEP) ([Log in](#) Required)
 User manual, plug-in unit IEEE ([Log in](#) Required)
 User Manual ([Log in](#) Required)



Product illustrations are exemplary illustrations and can deviate from supplied products.

User manual, coding IEEE ([Log in](#) Required)

To gain access to the additional information you must [Log in](#).
If you do not yet have a user name, you may [Register here](#).

Delivery comprises: kit

Item	Qty	Description
	6 U	
	≥8 HP	
1	1	U front profile, aluminium front: anodised; -rear: pickled
2	1	EMC seal. Core: foam Sleeve: textile cladding with CuNi coating
3	2	IEL handle with integrated alignment pin for perforated strip and guide rail Lever: plastic PC, light grey, RAL 7035 Key: plastic PC, black, RAL 9005
4	-	Printed board bracket, diecast zinc
5	-	Countersunk screw with cross recess, M 2,5 × 8, St nickel-plated
6	2	Sleeve, PA, grey
7	4	Collar screw with cross recess M 2,5 × 12,3, St, nickel-plated
8	2	Countersunk screw with cross recess, M 2,5 × 6, St nickel-plated
9	2	Washer A 2.7, St, nickel-plated
10	2	Countersunk screw with cross recess, M 2,5 × 6, St nickel-plated

Accessories:

Part no.	Description	
20817-606	Microswitch for handles, CompactPCI/VME64x application Qty: 10 pieces	Add to basket