

High capacity all-purpose vacuum cleaner

Standard accessories:

- Suction hose 2.5 m
- Metal suction tube
- 2 x 0.5 m
- Filter bag Paper
- Wet and dry floor tool 300 mm
- Crevice tool
- Cartridge filter
- Drain hose
- Bend
- Safety class II
- Caster with brake

Order no.: 1.428-604.0



Technical data

Air flow rate (l/s)	67
Vacuum (mbar/kPa)	200/20
Container capacity (l)	48
Max. intake performance (W)	max. 1380
Standard nominal size (mm)	35
Length of cord access. (m)	7.5
Sound level (dB(A))	72
Container material	Plastic
Frequency (Hz)	50-60
Voltage (V)	220-240
Weight (kg)	10.5
Dimensions (L x W x H) (mm)	490x390x780

Details

Description

The NT 48/1 is a high-capacity single motor all-purpose vacuum cleaner for picking up large quantities of wet or dry dirt. It is fitted with an automatic cut out facility for when maximum fluid capacity is reached and a drainage hose for the disposal of all liquids in a safe and clean manner. The NT 48/1 is an attractive option for groups within the professional sector, especially targeting contract cleaners, as well as automotive and craft trades.

Features & Benefits

Drain hose

Easily accessible drain hose for convenient liquid disposal.

Cartridge filter with float

Large cartridge filter ensures constant high suction power. The float system interrupts the suction flow after reaching the maximum capacity.

Robust metal latches

The extremely robust metal latches lock more reliably.

Robust bumper

The NT 48/1 has a bumper to protect the vacuum, walls, machines and other items against damage.

Accessories

All-purpose brushes

All-purpose brush

All-purpose brush PPN_Bristle

Order no. 6.900-425.0



Plastic bend

Plastic bend

Plastic bend (DN 35) with C-35 clip system. For all industrial single-motor NT 361 to NT 611 Eco models (except NT Eco M and NT Eco H).

Order no. 5.031-718.0



Suction tubes stainless steel

Suction tube, DN 35

Order no. 6.902-154.0

