

# Wirewound Resistor




RoHS  
Compliant




## Specifications:

Material coating	: Lead free vitreous enamel
Material core	: Tubular ceramic
Terminals	: Tinned lug with hole
Resistance	: 1Ω
Power Rating	: 300W
Resistance Tolerance	: ±10%
Resistor Element Type	: Wirewound
Temperature Coefficient	: ±400ppm/°C
Overload	: 10 times rated wattage for 5 sec
Dielectric withstanding Voltage	: 1,000V AC (Measured from terminal to mounting bracket)
Derating linearly from 100% @ +25°C to 0% @ +400°C	



Dimensions : Inches

Wattage Derating Chart



## Part Number Table

Description	Resistance (Ω) ±10%	Part Number
Wirewound Resistors, Fixed, Vitreous, Edgewound	1	MC14649
	4	MC14651

**Important Notice** : This data sheet and its contents (the "Information") belong to the members of the Premier Farnell group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp is the registered trademark of the Group. © Premier Farnell plc 2012.

www.element14.com  
www.farnell.com  
www.newark.com

