














































▷ ISO 2725-1, DIN 3124, NF ISO 2725-1


▼ Dessins Techniques





Zoom

			S mm	\varnothing d1 mm	\varnothing d2 mm	t mm	L mm	$\Delta\Delta$ g
R.3,2			3,2	5,9	11,2	2,40	22	7,3
R.4			4,0	6,9	11,2	2,60	22	7,7
R.5			5,0	8,2	11,2	4,80	22	8,1
R.5,5			5,5	8,8	11,2	4,80	22	8,4
R.6			6,0	9,4	11,2	5,60	22	8,6
R.7			7,0	11	11	6,00	22	9,2
R.8			8,0	12,0	12,0	6,50	22	11,5
R.9			9,0	13,2	13,2	6,50	22	14,3
R.10			10,0	14,7	14,7	7,80	22	17,7
R.11			11,0	15,8	15,8	9,00	22	19,4
R.12			12,0	17,0	17,0	9,50	22	23,2
R.13			13,0	17,7	17,7	10,00	22	23,7
R.14			14,0	18,7	18,7	10,00	22	26,1
R.5,5E			5,5	8,8	11,2	4,8	22	8,4
R.6E			6,0	9,4	11,2	5,6	22	8,6
R.7E			7,0	11	11	6	22	9,2
R.8E			8,0	12,0	12,0	6,5	22	11,5
R.9E			9,0	13,2	13,2	6,5	22	14,3
R.10E			10,0	14,7	14,7	7,8	22	17,7
R.11E			11,0	15,8	15,8	9	22	19,4

▼ Données Techniques

R.12E  12,0 17,0 17,0 9,5 22 23,2

R.13E  13,0 17,7 17,7 10 22 23,7

R.14E  14,0 18,7 18,7 10 22 26,1