

June 2010

FDC3535

P-Channel Power Trench[®] MOSFET -80 V, -2.1 A, 183 m Ω

Features

- Max $r_{DS(on)}$ = 183 m Ω at V_{GS} = -10 V, I_D = -2.1 A
- Max $r_{DS(on)}$ = 233 m Ω at V_{GS} = -4.5 V, I_D = -1.9 A
- High performance trench technology for extremely low r_{DS(on)}
- High power and current handling capability in a widely used surface mount package
- Fast switching speed
- 100% UIL Tested
- RoHS Compliant





General Description

This P-Channel MOSFET is produced using Fairchild Semiconductor's advanced Power Trench® process that has been optimized for $r_{DS(on)}$, switching performance and ruggedness.

Applications

- Load Switch
- Synchronous Rectifier





MOSFET Maximum Ratings T_A = 25 °C unless otherwise noted

Symbol	Parameter		Ratings	Units
V_{DS}	Drain to Source Voltage		-80	V
V_{GS}	Gate to Source Voltage		±20	V
	Drain Current -Continuous	(Note 1a)	-2.1	۸
ID	-Pulsed		-10	_ A
E _{AS}	Single Pulse Avalanche Energy	(Note 3)	37	mJ
D	Power Dissipation	(Note 1a)	1.6	W
P_{D}	Power Dissipation	(Note 1b)	0.7	VV
T _J , T _{STG}	Operating and Storage Junction Temperature Range		-55 to +150	°C

Thermal Characteristics

			1
$R_{\theta JC}$	Thermal Resistance, Junction to Case	30	°C/W
R _{0,IA}	Thermal Resistance, Junction to Ambient (Note	a) 78	C/VV

Package Marking and Ordering Information

Device Marking	Device	Package	Reel Size	Tape Width	Quantity
.535	FDC3535	SSOT-6	7 "	8 mm	3000 units

Electrical Characteristics $T_J = 25$ °C unless otherwise noted

Parameter

Off Characteristics							
BV _{DSS}	Drain to Source Breakdown Voltage	$I_D = -250 \mu A, V_{GS} = 0 V$	-80			V	
$\frac{\Delta BV_{DSS}}{\Delta T_{J}}$	Breakdown Voltage Temperature Coefficient	I_D = -250 μ A, referenced to 25 °C		-64		mV/°C	
I _{DSS}	Zero Gate Voltage Drain Current	V _{DS} = -64 V, V _{GS} = 0 V			-1	μΑ	
I _{GSS}	Gate to Source Leakage Current	$V_{GS} = \pm 20 \text{ V}, V_{DS} = 0 \text{ V}$			±100	nA	

Test Conditions

Min

Тур

Max

Units

On Characteristics

Symbol

V _{GS(th)}	Gate to Source Threshold Voltage	$V_{GS} = V_{DS}, I_{D} = -250 \mu A$	-1	-1.6	-3	V
$\frac{\Delta V_{GS(th)}}{\Delta T_J}$	Gate to Source Threshold Voltage Temperature Coefficient	I_D = -250 μ A, referenced to 25 °C		5		mV/°C
		$V_{GS} = -10 \text{ V}, I_D = -2.1 \text{ A}$		147	183	
r _{DS(on)} Static Drain to Source On Resistance	$V_{GS} = -4.5 \text{ V}, I_D = -1.9 \text{ A}$		176	233	mΩ	
, ,		$V_{GS} = -10 \text{ V}, I_D = -2.1 \text{ A}, T_J = 125 \text{ °C}$		246	307	1
9 _{FS}	Forward Transconductance	$V_{DD} = -10 \text{ V}, I_D = -2.1 \text{ A}$		6.3		S

Dynamic Characteristics

C _{iss}	Input Capacitance	V 40.V V 0.V	659	880	pF
Coss	Output Capacitance	$V_{DS} = -40 \text{ V}, V_{GS} = 0 \text{ V},$ $f = 1 \text{ MHz}$	49	65	pF
C _{rss}	Reverse Transfer Capacitance	1 - 1 101112	24	40	pF
R _a	Gate Resistance		5.7		Ω

Switching Characteristics

t _{d(on)}	Turn-On Delay Time		6.5	13	ns
t _r	Rise Time	V _{DD} = -40 V, I _D = -2.1 A,	3.1	10	ns
t _{d(off)}	Turn-Off Delay Time	$V_{GS} = -10 \text{ V}, R_{GEN} = 6 \Omega$	23	38	ns
t _f	Fall Time		2.9	10	ns
0	Total Gate Charge	V _{GS} = 0 V to -10 V	14	20	nC
$Q_{g(TOT)}$	Total Gate Charge	$V_{GS} = 0 \text{ V to } -4.5 \text{ V}$ $V_{DD} = -40 \text{ V}$	6.8	10	nC
Q_{gs}	Total Gate Charge	I _D = -2.1 A	1.6		nC
Q_{gd}	Gate to Drain "Miller" Charge		2.7		nC

Drain-Source Diode Characteristics

V_{SD}	Source to Drain Diode Forward Voltage	$V_{GS} = 0 \text{ V}, I_{S} = -2.1 \text{ A}$ (Note 2)		-0.81	-1.3	V
t _{rr}	Reverse Recovery Time	I _F = -2.1 A, di/dt = 100 A/μs		25	40	ns
Q _{rr}	Reverse Recovery Charge			23	38	nC

NOTES:

1. R_{0JA} is the sum of the junction-to-case and case-to-ambient thermal resistance where the case thermal reference is defined as the solder mounting surface of the drain pins. $R_{\theta JC}$ is guaranteed by design while $R_{\theta CA}$ is determined by the user's board design.



a. 78 °C/W when mounted on a 1 in² pad of 2 oz copper



b.175 °C/W when mounted on a minimum pad of 2 oz copper

- 2. Pulse Test: Pulse Width < 300 $\mu s,$ Duty cycle < 2.0 %.
- 3. Starting T $_{J}$ = 25 $^{o}C,\,L$ = 3 mH, I_{AS} = -5 A, V_{DD} = -80 V, V_{GS} = -10 V.

Typical Characteristics T_J = 25 °C unless otherwise noted




Figure 1. On-Region Characteristics




Figure 2. Normalized On-Resistance vs Drain Current and Gate Voltage




Figure 3. Normalized On-Resistance vs Junction Temperature




Figure 4. On-Resistance vs Gate to Source Voltage




Figure 5. Transfer Characteristics




Figure 6. Source to Drain Diode Forward Voltage vs Source Current

Typical Characteristics $T_J = 25$ °C unless otherwise noted




Figure 7. Gate Charge Characteristics




Figure 9. Unclamped Inductive Switching Capability




Figure 11. Forward Bias Safe
Operating Area




Figure 8. Capacitance vs Drain to Source Voltage




Figure 10. Maximum Continuous Drain Current vs Ambient Temperature




Figure 12. Single Pulse Maximum Power Dissipation

Typical Characteristics T_J = 25 °C unless otherwise noted





Figure 13. Junction-to-Ambient Transient Thermal Response Curve







TRADEMARKS

The following includes registered and unregistered trademarks and service marks, owned by Fairchild Semiconductor and/or its global subsidiaries, and is not intended to be an exhaustive list of all such trademarks.

AccuPower™ Auto-SPM™ Build it Now™ CorePLUS™ CorePOWER™ CROSSVOLTTM Current Transfer Logic™ **DEUXPEED®** Dual Cool™ EcoSPARK[®]

ESBC™

Fairchild[®]

EfficentMax™

Fairchild Semiconductor® FACT Quiet Series™ FACT®

FAST® FastvCore™ FETBench™ FlashWriter® 7 Green FPS™ Green FPS™ e-Series™ Gmax™ GTO™ IntelliMAX™ ISOPLANAR™ MegaBuck™ MICROCOUPLER™ MicroFET™ MicroPak™

Global Power ResourceSM

F-PFS™

FRFET®

MicroPak2™ MillerDrive™ MotionMax™ Motion-SPM™ OptiHiT™ OPTOLOGIC® OPTOPLANAR®

PDP SPM™

Power-SPM™ PowerTrench® PowerXS™

Programmable Active Droop™

OFET QSTM Quiet Series™ RapidConfigure™

Saving our world, 1mW/W/kW at a time™ SignalWise™

SmartMax™ SMART START™ SPM® STEALTH™ SuperFET™

SuperSOT™-3 SuperSOT™-6 SuperSOT™-8 SupreMOS™ SyncFET™ Sync-Lock™

SYSTEM^{3*}
GENERAL
The Power Franchise[®]

wer franchise TinyBoost™ TinyBuck™ TinyCalc™ TinyLogic[®] TINYOPTO™ TinyPower™ TinyPWM™ TinyWire™ TriFault Detect™ TRUECURRENT*** μSerDes™

UHC® Ultra FRFET™ UniFET™ VCX™ VisualMax™ XSTN

*Trademarks of System General Corporation, used under license by Fairchild Semiconductor.

FAIRCHILD SEMICONDUCTOR RESERVES THE RIGHT TO MAKE CHANGES WITHOUT FURTHER NOTICE TO ANY PRODUCTS HEREIN TO IMPROVE RELIABILITY, FUNCTION, OR DESIGN. FAIRCHILD DOES NOT ASSUME ANY LIABILITY ARISING OUT OF THE APPLICATION OR USE OF ANY PRODUCT OR CIRCUIT DESCRIBED HEREIN; NEITHER DOES IT CONVEY ANY LICENSE UNDER ITS PATENT RIGHTS, NOR THE RIGHTS OF OTHERS. THESE SPECIFICATIONS DO NOT EXPAND THE TERMS OF FAIRCHILD'S WORLDWIDE TERMS AND CONDITIONS, SPECIFICALLY THE WARRANTY THEREIN, WHICH COVERS THESE PRODUCTS.

LIFE SUPPORT POLICY
FAIRCHILD'S PRODUCTS ARE NOT AUTHORIZED FOR USE AS CRITICAL COMPONENTS IN LIFE SUPPORT DEVICES OR SYSTEMS WITHOUT THE EXPRESS WRITTEN APPROVAL OF FAIRCHILD SEMICONDUCTOR CORPORATION.

- Life support devices or systems are devices or systems which, (a) are intended for surgical implant into the body or (b) support or sustain life, and (c) whose failure to perform when properly used in accordance with instructions for use provided in the labeling, can be reasonably expected to result in a significant injury of the user.
- A critical component in any component of a life support, device, or system whose failure to perform can be reasonably expected to cause the failure of the life support device or system, or to affect its safety or effectiveness.

ANTI-COUNTERFEITING POLICY

Fairchild Semiconductor Corporation's Anti-Counterfeiting Policy. Fairchild's Anti-Counterfeiting Policy is also stated on our external website, www.Fairchildsemi.com, under Sales Support.

Counterfeiting of semiconductor parts is a growing problem in the industry. All manufactures of semiconductor products are experiencing counterfeiting of their parts. Customers who inadvertently purchase counterfeit parts experience many problems such as loss of brand reputation, substandard performance, failed application, and increased cost of production and manufacturing delays. Fairchild is taking strong measures to protect ourselves and our customers from the proliferation of counterfeit parts. Fairchild strongly encourages customers to purchase Fairchild parts either directly from Fairchild or from Authorized Fairchild Distributors who are listed by country on our web page cited above. Products customers buy either from Fairchild directly or from Authorized Fairchild Distributors are genuine parts, have full traceability, meet Fairchild's quality standards for handing and storage and provide access to Fairchild's full range of up-to-date technical and product information. Fairchild and our Authorized Distributors will stand behind all warranties and will appropriately address and warranty issues that may arise. Fairchild will not provide any warranty coverage or other assistance for parts bought from Unauthorized Sources. Fairchild is committed to combat this global problem and encourage our customers to do their part in stopping this practice by buying direct or from authorized distributors.

PRODUCT STATUS DEFINITIONS **Definition of Terms**

Datasheet Identification	Product Status	Definition
Advance Information	Formative / In Design	Datasheet contains the design specifications for product development. Specifications may change in any manner without notice.
Preliminary	First Production	Datasheet contains preliminary data; supplementary data will be published at a later date. Fairchild Semiconductor reserves the right to make changes at any time without notice to improve design.
No Identification Needed	Full Production	Datasheet contains final specifications. Fairchild Semiconductor reserves the right to make changes at any time without notice to improve the design.
Obsolete	Not In Production	Datasheet contains specifications on a product that is discontinued by Fairchild Semiconductor. The datasheet is for reference information only.
		Rev. 14:

www.fairchildsemi.com