

# HellermannTyton

## Product Safety Data Sheet

### 1. IDENTIFICATION OF THE SUBSTANCE/PREPARATION & COMPANY/UNDERTAKING

---

PRODUCT NAME: **Hellerine M Lubricant**

---

Address/Phone No: Hellermann Tyton  
International Medical and Technology Park  
William Prance Road  
Plymouth  
Devon  
PL6 5WR  
(01752) 701261

---

### 2. HAZARDOUS IDENTIFICATION

Low Hazard. Material can form flammable mixtures or can burn only on heating to temperatures at or above the flash point. Toxic gases will form on combustion.

---

### 3. COMPOSITION/INFORMATION OF INGREDIENTS

PRODUCT DESCRIPTION: Lubricant for rubber sleeves  
None

---

### 4. FIRST-AID MEASURES

Inhalation: Using approved respiratory protection, immediately remove the affected person from exposure. Seek medical attention.

Skin Contact: First aid is not normally required. If grossly contaminated remove clothing and launder before re-use.

Eye Contact: Flush eyes with large amounts of water until irritation subsides. If it persists, seek medical attention.

Ingestion: Do not induce vomiting.

---

### 5. FIRE-FIGHTING MEASURES

Extinguishing Media: Use foam, dry chemical or water spray to extinguish fire.

Fire Fighting Protective Equipment: Respiratory and eye protection required for fire fighting personnel.

---

---

PRODUCT NAME:

**Hellerine M Lubricant**

---

**6. ACCIDENTAL RELEASE MEASURES**

Contain spilled liquid with sand or earth.

---

**7. HANDLING & STORAGE**

**7.1 HANDLING**

Handle and open containers with care.

A high standard of personal hygiene is required.

**7.2 Storage**

Storage temperature: 40°C maximum

Store in cool well ventilated place away from direct sunlight.

Avoid contamination.

---

**8. EXPOSURE CONTROLS / PERSONAL PROTECTION**

**Occupational Exposure Limits**

1.	Substance	8 Hr. TWA	STEL	Source/Other Information
2.	Mineral Oil (see Oil mist, mineral)	5mg/m <sup>3</sup>	10mg/ m <sup>3</sup>	EH40
3.	Engineering Control Measures:	None		

Personal Protective Equipment: Avoid skin and eye contact. In case of repeated or prolonged contact wear impervious gloves (eg of PVC). Change contaminated clothing and clean before re-use

**HAZARDOUS INGREDIENT(S)**

None

---

---

PRODUCT NAME:

**Hellerine M Lubricant**

---

**9. PHYSICAL & CHEMICAL PROPERTIES**

Form	:	Liquid
Odour	:	Aromatic
Density (g/ml)	:	0.88
Solubility (Water)	:	Negligible
Solubility (Other)	:	In most organic solvents
Flash Point (°C)	:	165°C

---

**10. STABILITY & REACTIVITY**

Hazardous Reactions : Avoid strong oxidising agents.

Hazardous Decomposition Product(s) :

---

**11. TOXICOLOGICAL INFORMATION**

Inhalation :Negligible at ambient temperatures. Avoid breathing vapours and mists.

Skin Contact :May cause some dermatological problems if exposed to long term use.

Eye Contact :Slight irritation.

Ingestion :Minimal toxicity. May have a laxative effect.

Long Term Exposure :See skin contact.

---

**12. ECOLOGICAL INFORMATION**

Ecotoxicological data: Not available.

---

**13. DISPOSAL CONSIDERATIONS**

Care should be taken to ensure compliance with EC, National and Local Regulations.

---

---

PRODUCT NAME:

**Hellerine M Lubricant**

---

#### **14. TRANSPORT INFORMATION**

No special requirements. Not a hazardous good as defined within international regulations.

---

#### **15. REGULATORY INFORMATION**

Not defined as hazardous as per 67/548/EEC and 1999/45/EC.

Product is compliant with EU Directives

2002/95/EC (RoHS)

2002/96/EC (WEEE)

2003/11/EC (pentabromodiphenyl ether, octabromodiphenyl ether)

2006/122/EC (PFOS)

---

#### **16. OTHER INFORMATION**

This data sheet was prepared in accordance with Regulation (EC) No 1907/2006 (REACH)

Use: Lubricant

For other technical information, contact the address in Section 1.

---

Information in this publication is believed to be accurate and is given in good faith, but it is for the Customer to satisfy itself of the suitability for its own particular purpose. Accordingly, HellermannTyton gives no warranty to the fitness of the Product for any particular purpose and any implied warranty or condition (statutory or otherwise) is excluded except to the extent that such exclusion is prevented by law. Freedom under Patent, Copyright and Designs cannot be assumed.

---