## **SWITCHMODE Power Rectifier**

#### **DPAK Surface Mount Package**

These state-of-the-art devices are designed for use in switching power supplies, inverters and as free wheeling diodes.

#### **Features**

- Ultrafast 35 Nanosecond Recovery Time
- Low Forward Voltage Drop
- Low Leakage
- ESD Rating:
  - ◆ Human Body Model = 3B (> 8 kV)
  - ◆ Machine Model = C (> 400 V)
- NRVUD Prefix for Automotive and Other Applications Requiring Unique Site and Control Change Requirements; AEC-Q101 Qualified and PPAP Capable
- These Devices are Pb-Free and are RoHS Compliant\*

#### **Mechanical Characteristics:**

- Case: Epoxy, Molded
- Weight: 0.4 Gram (Approximately)
- Finish: All External Surfaces Corrosion Resistant and Terminal Leads are Readily Solderable
- Lead and Mounting Surface Temperature for Soldering Purposes: 260°C Max. for 10 Seconds




#### ON Semiconductor®

http://onsemi.com

# ULTRAFAST RECTIFIER 6.0 AMPERES 200 VOLTS



DPAK CASE 369C



#### **MARKING DIAGRAM**



A = Assembly Location

Y = Year
WW = Work Week
U620T = Device Code
G = Pb-Free Package

#### ORDERING INFORMATION

Device	Package	Shipping <sup>†</sup>
MURD620CTG	DPAK (Pb-Free)	75 Units / Rail
NRVUD620CTG	DPAK (Pb-Free)	75 Units / Rail
MURD620CTT4G	DPAK (Pb-Free)	2,500 / Tape & Reel
NRVUD620CTT4G	DPAK (Pb-Free)	2,500 / Tape & Reel

<sup>†</sup>For information on tape and reel specifications, including part orientation and tape sizes, please refer to our Tape and Reel Packaging Specifications Brochure, BRD8011/D.

<sup>\*</sup>For additional information on our Pb-Free strategy and soldering details, please download the ON Semiconductor Soldering and Mounting Techniques Reference Manual, SOLDERRM/D.

#### **MAXIMUM RATINGS**

Rating	Symbol	Value	Unit
Peak Repetitive Reverse Voltage Working Peak Reverse Voltage DC Blocking Voltage	$egin{array}{c} V_{RRM} \ V_{RWM} \ V_{R} \end{array}$	200	V
Average Rectified Forward Current (Rated V <sub>R</sub> , T <sub>C</sub> = 140°C) Per Diode Per Device	I <sub>F(AV)</sub>	3.0 6.0	Α
Peak Repetitive Forward Current (Rated V <sub>R</sub> , Square Wave, 20 kHz, T <sub>C</sub> = 145°C) Per Diode	I <sub>F</sub>	6.0	А
Non-Repetitive Peak Surge Current (Surge Applied at Rated Load Conditions Halfwave, 60 Hz)	I <sub>FSM</sub>	50	Α
Operating Junction and Storage Temperature Range	T <sub>J</sub> , T <sub>stg</sub>	-65 to +175	°C

Stresses exceeding Maximum Ratings may damage the device. Maximum Ratings are stress ratings only. Functional operation above the Recommended Operating Conditions is not implied. Extended exposure to stresses above the Recommended Operating Conditions may affect device reliability.

#### THERMAL CHARACTERISTICS (Per Diode)

Characteristic	Symbol	Value	Unit
Thermal Resistance, Junction-to-Case	$R_{ heta JC}$	9	°C/W
Thermal Resistance, Junction-to-Ambient (Note 1)	$R_{ heta JA}$	80	°C/W

<sup>1.</sup> Rating applies when surface mounted on the minimum pad sizes recommended.

#### **ELECTRICAL CHARACTERISTICS** (Per Diode)

Characteristic	Symbol	Value	Unit
$\label{eq:maximum Instantaneous Forward Voltage Drop (Note 2)} \begin{tabular}{ll} (i_F = 3 \text{ Amps, } T_C = 25^\circ C) \\ (i_F = 3 \text{ Amps, } T_C = 125^\circ C) \\ (i_F = 6 \text{ Amps, } T_C = 25^\circ C) \\ (i_F = 6 \text{ Amps, } T_C = 125^\circ C) \\ \end{tabular}$	VF	1 0.96 1.2 1.13	V
Maximum Instantaneous Reverse Current (Note 2) (T <sub>J</sub> = 25°C, Rated dc Voltage) (T <sub>J</sub> = 125°C, Rated dc Voltage)	i <sub>R</sub>	5 250	μΑ
Maximum Reverse Recovery Time ( $I_F=1$ Amp, $di/dt=50$ Amps/ $\mu$ s, $V_R=30$ V, $T_J=25$ °C) ( $I_F=0.5$ Amp, $I_R=1$ Amp, $I_{REC}=0.25$ A, $V_R=30$ V, $T_J=25$ °C)	t <sub>rr</sub>	35 25	ns

<sup>2.</sup> Pulse Test: Pulse Width = 300  $\mu s, \ Duty \ Cycle \leq 2.0\%.$ 




Figure 4. Current Derating, Case (Per Leg)

Figure 5. Current Derating, Ambient (Per Leg)





Figure 6. Typical Capacitance (Per Leg)

#### PACKAGE DIMENSIONS

#### **DPAK (SINGLE GAUGE)**


CASE 369C ISSUE D



- 1. DIMENSIONING AND TOLERANCING PER ASME Y14.5M, 1994
- 2. CONTROLLING DIMENSION: INCHES.
  3. THERMAL PAD CONTOUR OPTIONAL WITHIN DI-MENSIONS b3, L3 and Z.
  4. DIMENSIONS D AND E DO NOT INCLUDE MOLD
- FLASH, PROTRUSIONS, OR BURRS. MOLD FLASH, PROTRUSIONS, OR GATE BURRS SHALL NOT EXCEED 0.006 INCHES PER SIDE.
  5. DIMENSIONS D AND E ARE DETERMINED AT THE
- OUTERMOST EXTREMES OF THE PLASTIC BODY.
- 6. DATUMS A AND B ARE DETERMINED AT DATUM

	INCHES		MILLIMETERS	
DIM	MIN	MAX	MIN	MAX
Α	0.086	0.094	2.18	2.38
A1	0.000	0.005	0.00	0.13
b	0.025	0.035	0.63	0.89
b2	0.030	0.045	0.76	1.14
b3	0.180	0.215	4.57	5.46
С	0.018	0.024	0.46	0.61
c2	0.018	0.024	0.46	0.61
D	0.235	0.245	5.97	6.22
E	0.250	0.265	6.35	6.73
е	0.090	BSC	2.29	BSC
Н	0.370	0.410	9.40	10.41
L	0.055	0.070	1.40	1.78
L1	0.108 REF		2.74 REF	
L2	0.020	BSC	0.51	BSC
L3	0.035	0.050	0.89	1.27
L4		0.040		1.01
Z	0.155		3.93	

#### **SOLDERING FOOTPRINT\***



\*For additional information on our Pb-Free strategy and soldering details, please download the ON Semiconductor Soldering and Mounting Techniques Reference Manual, SOLDERRM/D.

ON Semiconductor and un are registered trademarks of Semiconductor Components Industries, LLC (SCILLC). SCILLC reserves the right to make changes without further notice to any products herein. SCILLC makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does SCILLC assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. "Typical" parameters which may be provided in SCILLC data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. SCILLC does not convey any license under its patent rights nor the rights of others. SCILLC products are not designed, intended, or authorized for use as components in systems intended for surgical implant into the body, or other applications intended to support or sustain life, or for any other application in which the failure of the SCILLC product could create a situation where personal injury or death may occur. Should Buyer purchase or use SCILLC products for any such unintended or unauthorized application, Buyer shall indemnify and hold SCILLC and its officers, employees, subsidiaries, affiliates, and distributors harmless against all claims, costs, damages, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized use, even if such claim alleges that SCILLC was negligent regarding the design or manufacture of the part. SCILLC is an Equal Opportunity/Affirmative Action Employer. This literature is subject to all applicable copyright laws and is not for resale in any manner.

#### **PUBLICATION ORDERING INFORMATION**

#### LITERATURE FULFILLMENT:

Literature Distribution Center for ON Semiconductor P.O. Box 5163, Denver, Colorado 80217 USA Phone: 303-675-2175 or 800-344-3860 Toll Free USA/Canada

Fax: 303-675-2176 or 800-344-3867 Toll Free USA/Canada Email: orderlit@onsemi.com

N. American Technical Support: 800-282-9855 Toll Free USA/Canada

Europe, Middle East and Africa Technical Support: Phone: 421 33 790 2910

Japan Customer Focus Center Phone: 81-3-5817-1050

ON Semiconductor Website: www.onsemi.com

Order Literature: http://www.onsemi.com/orderlit

For additional information, please contact your local Sales Representative