

Multilayer Ceramic Capacitors

Ultra-Small Series



RoHS
Compliant



Description:

MLCC consists of a conducting material and electrodes. To manufacture a chip-type SMT and achieve miniaturization, high density and high efficiency, ceramic condensers are used. 0201 MLCC is performed by high precision technology achieve high capacitance in unit size and ensure the stability and reliability of products.

Features:

- High capacitance in unit size
- High precision dimensional tolerances
- Suitable used in high-accuracy automatic mounting machine

Applications:

- Miniature microwave module.
- Portable equipments (ex. Mobile phone, PDA)
- High frequency circuits

External Dimensions:




Fig. 1 The outline of MLCC

Size Inch (mm)	L (mm)	W (mm)	T (mm)/Symbol	MB (mm)	
0201 (0603)	0.6 ±0.03	0.3 ±0.03	0.3 ±0.03	L	0.15±0.05
	0.6 ±0.05 ^{#1}	0.3 ±0.05 ^{#1}	0.3 ±0.05 ^{#1}		

Reflow soldering only.

^{#1} For 0201/Cap ≥0.68uF



Multilayer Ceramic Capacitors

Ultra-Small Series



General Electrical Data:

Size	0201		
Dielectric	NP0	X7R	X5R
Capacitance*	0.3pF to 100pF	100pF to 10nF	100pF to 1μF
Capacitance tolerance**	Cap≤5pF: B (±0.1pF), C (±0.25pF) 5pF<Cap<10pF: C (±0.25pF),D(±0.5pF) Cap≥10pF: F (±1%), G (±2%), J (±5%), K (±10%)	J (±5%), K (±10%), M (±20%)	J (±5%),K (±10%), M (±20%)
Rated voltage (WV DC)	16V, 25V, 50V	6.3V, 10V, 16V, 25V, 50V	6.3V, 10V, 16V, 25V, 50V
Tan δ / Q*	Cap<30pF, Q≥400+20C Cap≥30pF, Q≥1000	Note 1	
Insulation resistance at Ur	≥10GΩ	≥10GΩ or RxC≥500ΩxF whichever is less	
Operating temperature	-55 to +125°C	-55 to +85°C	
Capacitance change	±30ppm	±15%	
Termination	Ni/Sn (lead-free termination)		

* Measured at 30% ~ 70% related humidity.

NP0: Apply 1.0±0.2Vrms, 1.0MHz±10% at the condition of 25°C ambient temperature.

X7R, X5R: Apply 1.0±0.2Vrms, 1.0kHz±10%(0201/6.3V,Cap≥224 : 0.5±0.2Vrms, 1.0kHz±10%) at the condition of 25°C ambient temperature.

** Preconditioning for Class II MLCC: Perform a heat treatment at 150±10°C for 1 hour, then leave in ambient condition for 24±2 hours before measurement.

Note 1:

X7R/X5R

Rated vol.	D.F.	Exception of D.F.	
≥50V	≤3%	---	
25V	≤3.5%	≤5%	0201≥0.01uF
16V	≤3.5%	≤5%	0201≥0.01uF
10V	≤5%	≤10%	0201≥0.012uF
		≤15%	0201≥0.1uF
6.3V	≤10%	≤15%	0201≥0.1uF

Packaging Dimension And Quantity:

Size	Thickness (mm)/Symbol		Paper Tape	
			7" reel	13" reel
0201 (0603)	0.3 ±0.03	L	15,000	70,000
	0.3 ±0.05 ^{#1}		15,000	-

#1 For 0201/Cap≥0.68uF



Multilayer Ceramic Capacitors

Ultra-Small Series



Capacitance Range:

Size	0201		
Dielectric	NP0		
Rated Voltage (V DC)	16	25	50
0.3pF (0R3)	L^	L^	L^
0.4pF (0R4)	L^	L^	L^
0.5pF (0R5)	L^	L^	L^
1.0pF (1R0)	L^	L^	L^
1.2pF (1R2)	L^	L^	L^
1.5pF (1R5)	L^	L^	L^
1.8pF (1R8)	L^	L^	L^
2.2pF (2R2)	L^	L^	L^
2.7pF (2R7)	L^	L^	L^
3.0pF (3R0)	L^	L^	L^
3.3pF (3R3)	L^	L^	L^
3.9pF (3R9)	L^	L^	L^
4.0pF (4R0)	L^	L^	L^
4.7pF (4R7)	L^	L^	L^
5.6pF (5R6)	L^	L^	L^
6.8pF (6R8)	L^	L^	L^
8.2pF (8R2)	L^	L^	L^
10pF (100)	L^	L^	L^
12pF (120)	L^	L^	L^
15pF (150)	L^	L^	L^
18pF (180)	L^	L^	L^
22pF (220)	L^	L^	L^
27pF (270)	L^	L^	L^
33pF (330)	L^	L^	L^
39pF (390)	L^	L^	L^
47pF (470)	L^	L^	L^
56pF (560)	L^	L^	L
68pF (680)	L^	L^	L
82pF (820)	L^	L^	L
100pF (101)	L^	L^	L

Size	0201									
Dielectric	X7R					X5R				
Rated Voltage (V DC)	6.3	10	16	25	50	6.3	10	16	25	50
100pF (101)			L	L	L			L	L	L
120pF (121)			L	L	L			L	L	L
150pF (151)			L	L	L			L	L	L
180pF (181)			L	L	L			L	L	L
220pF (221)			L	L	L			L	L	L
270pF (271)			L	L	L			L	L	L
330pF (331)			L	L	L			L	L	L
390pF (391)			L	L	L			L	L	L
470pF (471)			L	L	L			L	L	L
560pF (561)			L	L	L			L	L	L
680pF (681)			L	L	L			L	L	L
820pF (821)			L	L	L			L	L	L
1,000pF (102)	L	L	L	L	L		L	L	L	L
1,200pF (122)	L	L	L	L			L	L		
1,500pF (152)	L	L	L	L			L	L		
2,200pF (222)	L	L	L				L	L		
3,300pF (332)	L	L	L				L	L		
4,700pF (472)	L	L	L				L	L		
6,800pF (682)	L	L					L			
8,200pF (822)	L	L					L			
0.010µF (103)	L	L	L				L	L		
0.015µF (153)							L	L		
0.022µF (223)							L	L		
0.033µF (333)							L	L		
0.047µF (473)							L	L		
0.068µF (683)							L	L		
0.082µF (823)							L	L		
0.10µF (104)							L	L		
0.22µF (224)							L			
0.47µF (474)							L			
1.0µF (105)							L			

1. The letter in cell is expressed the symbol of product thickness.
2. The letter in cell with "A" mark is expressed product with Ag/Ni/Sn terminations.



Multilayer Ceramic Capacitors

Ultra-Small Series



Reliability Test Conditions and Requirements:

No	Item	Test Condition	Requirements																									
1	Visual and Mechanical	-	No remarkable defect. Dimensions to conform to individual specification sheet.																									
2	Capacitance	Class I: NP0 Cap \leq 1,000pF, 1.0 \pm 0.2Vrms, 1MHz \pm 10% Cap $>$ 1,000pF, 1.0 \pm 0.2Vrms, 1kHz \pm 10% Class II: X7R, X5R 1 \pm 0.2Vrms, 1kHz \pm 10% 0.5 \pm 0.2Vrms, 1.0kHz \pm 10% : 0201 \geq 0.22 uF(6.3V)	Shall not exceed the limits given in the detailed spec.																									
3	Q/ D.F. (Dissipation Factor)		<table border="1"> <thead> <tr> <th>Rated Vol.</th> <th>D.F.</th> <th colspan="2">Exception of D.F.</th> </tr> </thead> <tbody> <tr> <td>\geq50V</td> <td>\leq3%</td> <td>---</td> <td></td> </tr> <tr> <td>25V</td> <td>\leq3.5%</td> <td>\leq5%</td> <td>0201\geq0.01uF</td> </tr> <tr> <td>16V</td> <td>\leq3.5%</td> <td>\leq5%</td> <td>0201\geq0.01uF</td> </tr> <tr> <td rowspan="2">10V</td> <td rowspan="2">\leq5%</td> <td>\leq10%</td> <td>0201\geq0.012uF</td> </tr> <tr> <td>\leq15%</td> <td>0201\geq0.1uF</td> </tr> <tr> <td>6.3V</td> <td>\leq10%</td> <td>\leq15%</td> <td>0201\geq0.1uF</td> </tr> </tbody> </table>	Rated Vol.	D.F.	Exception of D.F.		\geq 50V	\leq 3%	---		25V	\leq 3.5%	\leq 5%	0201 \geq 0.01uF	16V	\leq 3.5%	\leq 5%	0201 \geq 0.01uF	10V	\leq 5%	\leq 10%	0201 \geq 0.012uF	\leq 15%	0201 \geq 0.1uF	6.3V	\leq 10%	\leq 15%
Rated Vol.	D.F.	Exception of D.F.																										
\geq 50V	\leq 3%	---																										
25V	\leq 3.5%	\leq 5%	0201 \geq 0.01uF																									
16V	\leq 3.5%	\leq 5%	0201 \geq 0.01uF																									
10V	\leq 5%	\leq 10%	0201 \geq 0.012uF																									
		\leq 15%	0201 \geq 0.1uF																									
6.3V	\leq 10%	\leq 15%	0201 \geq 0.1uF																									
4a	Dielectric Strength	To apply voltage (\leq 100V) 250%. Duration: 1 to 5 sec. Charge and discharge current less than 50mA.	No evidence of damage or flash over during test.																									
5	Insulation Resistance	To apply rated voltage for max. 120 sec.	\geq 10G Ω or Rx $C \geq$ 500 Ω -F whichever is smaller. Class II (X5R, X7R) <table border="1"> <thead> <tr> <th>Related Voltage</th> <th>Insulation Resistance</th> </tr> </thead> <tbody> <tr> <td>6.3V; 10V:0201\geq47nF</td> <td>\geq100Ω-F</td> </tr> </tbody> </table>	Related Voltage	Insulation Resistance	6.3V; 10V:0201 \geq 47nF	\geq 100 Ω -F																					
Related Voltage	Insulation Resistance																											
6.3V; 10V:0201 \geq 47nF	\geq 100 Ω -F																											
6	Temperature Coefficient	With no electrical load. <table border="1"> <thead> <tr> <th>T.C.</th> <th>Operating Temperature</th> </tr> </thead> <tbody> <tr> <td>NP0 (C0G)</td> <td>55~125°C at 25°C</td> </tr> <tr> <td>X7R</td> <td>-55~125°C at 25°C</td> </tr> <tr> <td>X5R</td> <td>-55~85°C at 25°C</td> </tr> </tbody> </table>	T.C.	Operating Temperature	NP0 (C0G)	55~125°C at 25°C	X7R	-55~125°C at 25°C	X5R	-55~85°C at 25°C	<table border="1"> <thead> <tr> <th>T.C.</th> <th>Capacitance Change</th> </tr> </thead> <tbody> <tr> <td>NP0 (C0G)</td> <td>Within \pm30ppm/$^{\circ}$C</td> </tr> <tr> <td>X7R</td> <td>Within \pm15%</td> </tr> <tr> <td>X5R</td> <td>Within \pm15%</td> </tr> </tbody> </table>	T.C.	Capacitance Change	NP0 (C0G)	Within \pm 30ppm/ $^{\circ}$ C	X7R	Within \pm 15%	X5R	Within \pm 15%									
T.C.	Operating Temperature																											
NP0 (C0G)	55~125°C at 25°C																											
X7R	-55~125°C at 25°C																											
X5R	-55~85°C at 25°C																											
T.C.	Capacitance Change																											
NP0 (C0G)	Within \pm 30ppm/ $^{\circ}$ C																											
X7R	Within \pm 15%																											
X5R	Within \pm 15%																											
7	Adhesive Strength of Termination	Pressurizing force: 2N Test time: 10 \pm 1 sec.	No remarkable damage or removal of the terminations.																									

Multilayer Ceramic Capacitors

Ultra-Small Series



Reliability Test Conditions and Requirements:

No	Item	Test Condition	Requirements															
8	Vibration Resistance	Vibration frequency: 10~55 Hz/min. Total amplitude: 1.5mm Test time: 6 hrs. (Two hrs each in three mutually perpendicular directions.) Measurement to be made after keeping at room temp. for 24±2 hrs.	No remarkable damage. Cap change and Q/D.F.: To meet initial spec.															
9	Solderability	Solder temperature: 235±5°C	95% min. coverage of all metalized area.															
10	Bending Test	The middle part of substrate shall be pressurized by means of the pressurizing rod at a rate of about 1 mm per second until the deflection becomes 1mm and then the pressure shall be maintained for 5±1 sec. Measurement to be made after keeping at room temp. for 24±2 hrs.	No remarkable damage. Cap change: NP0: within ±5.0% or ±0.5pF whichever is larger. X7R, X5R: within ±12.5% (This capacitance change means the change of capacitance under specified flexure of substrate from the capacitance measured before the test.)															
11	Resistance to Soldering Heat	Solder temperature: 260±5°C Dipping time: 10±1 sec Preheating: 120 to 150°C for 1 minute before immerse the capacitor in a eutectic solder. Before initial measurement (Class II only): Perform 150+0/-10°C for 1 hr and then set for 24±2 hrs at room temp Measurement to be made after keeping at room temp. for 24±2 hrs.	No remarkable damage. Cap change: NP0: within ±2.5% or ±0.25pF whichever is larger. X7R, X5R: within ±7.5% Q/D.F., I.R. and dielectric strength: To meet initial requirements. 25% max. leaching on each edge.															
12	Temperature Cycle	Conduct the five cycles according to the temperatures and time. <table border="1" style="margin-left: 20px;"> <thead> <tr> <th>Step</th> <th>Temp. (°C)</th> <th>Time (Min.)</th> </tr> </thead> <tbody> <tr> <td>1</td> <td>Min. operating temp. +0/-3</td> <td>30±3</td> </tr> <tr> <td>2</td> <td>Room temp.</td> <td>2~3</td> </tr> <tr> <td>3</td> <td>Max. operating temp. +3/-0</td> <td>30±3</td> </tr> <tr> <td>4</td> <td>Room temp.</td> <td>2~3</td> </tr> </tbody> </table> Before initial measurement (Class II only): Perform 150+0/-10°C for 1 hour and then set for 24±2 hrs at room temp. Measurement to be made after keeping at room temp. for 24±2 hrs.	Step	Temp. (°C)	Time (Min.)	1	Min. operating temp. +0/-3	30±3	2	Room temp.	2~3	3	Max. operating temp. +3/-0	30±3	4	Room temp.	2~3	No remarkable damage. Cap change: NP0: within ±2.5% or ±0.25pF whichever is larger. X7R, X5R: within ±7.5% Q/D.F., I.R. and dielectric strength: To meet initial requirements.
Step	Temp. (°C)	Time (Min.)																
1	Min. operating temp. +0/-3	30±3																
2	Room temp.	2~3																
3	Max. operating temp. +3/-0	30±3																
4	Room temp.	2~3																

Multilayer Ceramic Capacitors

Ultra-Small Series



Reliability Test Conditions and Requirements:

No	Item	Test Condition	Requirements																										
13	Humidity (Steady State)	<p>Test temp.: 40±2°C Humidity: 90~95% RH Test time: 500+24/-0hrs. Before initial measurement (Class II only): Perform 150+0/-10°C for 1 hr and then set for 24±2 hrs at room temp. Measurement to be made after keeping at room temp. for 24±2 hrs.</p>	<p>No remarkable damage. Cap change: NP0: within ±5.0% or ±0.5pF whichever is larger. X7R, X5R: ≥10V, within ±12.5%, 10V^{0.1}μF, within ±25%; 6.3V, within ±25% Y5V: ≥10V, within ±30% 6.3V, within +30/-40% Q/D.F. value: NP0: Cap≥30pF, Q≥350; 10pF≤Cap<30pF, Q≥275+2.5C Cap<10pF; Q≥200+10C X7R, X5R:</p> <table border="1"> <thead> <tr> <th>Rated Vol.</th> <th>D.F.</th> <th colspan="2">Exception of D.F.</th> </tr> </thead> <tbody> <tr> <td>≥50V</td> <td>≤6%</td> <td>-</td> <td></td> </tr> <tr> <td>25V</td> <td>≤5%</td> <td>≤10%</td> <td>0201≥0.01uF</td> </tr> <tr> <td>16V</td> <td>≤5%</td> <td>≤15%</td> <td>0201≥0.01uF</td> </tr> <tr> <td rowspan="2">10V</td> <td rowspan="2">≤7.5%</td> <td>≤15%</td> <td>0201≥0.012uF</td> </tr> <tr> <td>≤20%</td> <td>0201≥0.1uF</td> </tr> <tr> <td>6.3V</td> <td>≤15%</td> <td>≤30%</td> <td>0201≥0.1uF</td> </tr> </tbody> </table> <p>I.R.: ≥10V, ≥1GΩ or RxC≥50Ω-F whichever is smaller. 6.3V; 10V:0201≥47nF, RxC≥10Ω-F</p>	Rated Vol.	D.F.	Exception of D.F.		≥50V	≤6%	-		25V	≤5%	≤10%	0201≥0.01uF	16V	≤5%	≤15%	0201≥0.01uF	10V	≤7.5%	≤15%	0201≥0.012uF	≤20%	0201≥0.1uF	6.3V	≤15%	≤30%	0201≥0.1uF
Rated Vol.	D.F.	Exception of D.F.																											
≥50V	≤6%	-																											
25V	≤5%	≤10%	0201≥0.01uF																										
16V	≤5%	≤15%	0201≥0.01uF																										
10V	≤7.5%	≤15%	0201≥0.012uF																										
		≤20%	0201≥0.1uF																										
6.3V	≤15%	≤30%	0201≥0.1uF																										
14	Humidity Load (Damp Heat)	<p>Test temp.: 40±2°C Humidity: 90~95%RH Test time: 500+24/-0 hrs. To apply voltage: rated voltage. Before initial measurement (Class II only): To apply test voltage for 1hr at 40°C and then set for 24±2 hrs at room temp. Measurement to be made after keeping at room temp. for 24±2 hrs.</p>	<p>No remarkable damage. Cap change: NP0: within ±7.5% or ±0.75pF whichever is larger. X7R, X5R: ≥10V, within ±12.5%, 10V^{0.1}μF, within ±25%; 6.3V, within ±25% Y5V: ≥10V, within ±30% 6.3V, within +30/-40% Q/D.F. value: NP0: Cap≥30pF, Q≥200; Cap<30pF, Q≥100+10/3C X7R, X5R:</p> <table border="1"> <thead> <tr> <th>Rated Vol.</th> <th>D.F.</th> <th colspan="2">Exception of D.F.</th> </tr> </thead> <tbody> <tr> <td>≥50V</td> <td>≤6%</td> <td>-</td> <td></td> </tr> <tr> <td>25V</td> <td>≤5%</td> <td>≤10%</td> <td>0201≥0.01uF</td> </tr> <tr> <td>16V</td> <td>≤5%</td> <td>≤15%</td> <td>0201≥0.01uF</td> </tr> <tr> <td rowspan="2">10V</td> <td rowspan="2">≤7.5%</td> <td>≤15%</td> <td>0201≥0.012uF</td> </tr> <tr> <td>≤20%</td> <td>0201≥0.1uF</td> </tr> <tr> <td>6.3V</td> <td>≤15%</td> <td>≤30%</td> <td>0201≥0.1uF</td> </tr> </tbody> </table> <p>I.R.: ≥10V, 500M or RxC≥25-F whichever is smaller. 6.3V; 10V:0201≥47nF, RxC≥5-F</p>	Rated Vol.	D.F.	Exception of D.F.		≥50V	≤6%	-		25V	≤5%	≤10%	0201≥0.01uF	16V	≤5%	≤15%	0201≥0.01uF	10V	≤7.5%	≤15%	0201≥0.012uF	≤20%	0201≥0.1uF	6.3V	≤15%	≤30%	0201≥0.1uF
Rated Vol.	D.F.	Exception of D.F.																											
≥50V	≤6%	-																											
25V	≤5%	≤10%	0201≥0.01uF																										
16V	≤5%	≤15%	0201≥0.01uF																										
10V	≤7.5%	≤15%	0201≥0.012uF																										
		≤20%	0201≥0.1uF																										
6.3V	≤15%	≤30%	0201≥0.1uF																										



Multilayer Ceramic Capacitors

Ultra-Small Series




Reliability Test Conditions and Requirements:

No	Item	Test Condition	Requirements																								
15	High Temperature Load (Endurance)	<p>Test temp.: NP0, X7R: 125±3°C X5R, Y5V: 85±3°C To apply voltage: (1) Cap.≥0.1uF : 100% of rated voltage (2) 6.3V: 150% of rated voltage. (3) >6.3V: 200% of rated voltage. Test time: 1000+24/-0 hrs. Before initial measurement (Class II only): To apply test voltage for 1hr at test temp. and then set for 24±2 hrs at room temp. Measurement to be made after keeping at room temp. for 24±2 hrs</p>	<p>No remarkable damage. Cap change: NP0: within ±3.0% or ±0.3pF whichever is larger. X7R, X5R: ≥10V, within ±12.5%, 10V≥0.1μF, within ±25%; 6.3V, within ±25% Y5V: ≥10V, within ±30% 6.3V, within +30/-40% Q/D.F. value: NP0: Cap≥30pF, Q≥350; 10pF≤Cap<30pF, Q≥275+2.5C Cap<10pF; Q≥200+10C X7R, X5R:</p> <table border="1"> <thead> <tr> <th>Rated Vol.</th> <th>D.F.</th> <th colspan="2">Exception of D.F.</th> </tr> </thead> <tbody> <tr> <td>≥50V</td> <td>≤6%</td> <td>-</td> <td></td> </tr> <tr> <td>25V</td> <td>≤5%</td> <td>≤10%</td> <td>0201≥0.01uF</td> </tr> <tr> <td>16V</td> <td>≤5%</td> <td>≤15%</td> <td>0201≥0.01uF</td> </tr> <tr> <td>10V</td> <td>≤7.5%</td> <td>≤20%</td> <td>0201≥0.1uF</td> </tr> <tr> <td>6.3V</td> <td>≤15%</td> <td>≤30%</td> <td>0201≥0.1uF</td> </tr> </tbody> </table> <p>I.R.: ≥10V, ≥1G or RxC≥50-F whichever is smaller. 6.3V; 10V:0201≥47nF, RxC≥10-F</p>	Rated Vol.	D.F.	Exception of D.F.		≥50V	≤6%	-		25V	≤5%	≤10%	0201≥0.01uF	16V	≤5%	≤15%	0201≥0.01uF	10V	≤7.5%	≤20%	0201≥0.1uF	6.3V	≤15%	≤30%	0201≥0.1uF
Rated Vol.	D.F.	Exception of D.F.																									
≥50V	≤6%	-																									
25V	≤5%	≤10%	0201≥0.01uF																								
16V	≤5%	≤15%	0201≥0.01uF																								
10V	≤7.5%	≤20%	0201≥0.1uF																								
6.3V	≤15%	≤30%	0201≥0.1uF																								

Appendixes

Tape & Reel Dimensions




The dimension of paper tape

Size	0201
Thickness	L
A ₀	0.38 ±0.05
B ₀	0.68 ±0.05
T	0.42 ±0.05
K ₀	-
W	8 ±0.1
P ₀	4 ±0.1
10xP ₀	40 ±0.1
P ₁	2 ±0.05
P ₂	2 ±0.05
D ₀	1.55 ±0.05
D ₁	-
E	1.75 ±0.05
F	3.5 ±0.05



Multilayer Ceramic Capacitors


Ultra-Small Series



Size	0201	
Reel size	7"	13"
C	13+0.5/-0.2	13+0.5/-0.2
W ₁	8.4+1.5/-0	8.4+1.5/-0
A	178±0.1	330±1
N	60+1/-0	100±1

The dimension of reel

Constructions:



No.	Name	NP0	NP0, X7R, X5R
1	Ceramic material	BaTiO ₃ based	
2	Inner electrode	AgPd alloy	Ni
3	Inner layer	Ag	Cu
4	Middle layer	Ni	
5	Outer layer	Sn (Matt)	

Storage and handling conditions

- (1) To store products at 5 to 40°C ambient temperature and 20 to 70% related humidity conditions.
- (2) The product is recommended to be used within one year after shipment. Check solderability in case of shelf life extension is needed.

Cautions:

- a. The corrosive gas reacts on the terminal electrodes of capacitors, and results in the poor solderability. Do not store the capacitors in the ambience of corrosive gas (e.g., hydrogen sulfide, sulfur dioxide, chlorine, ammonia gas etc.)
- b. In corrosive atmosphere, solderability might be degraded, and silver migration might occur to cause low reliability.
- c. Due to the dewing by rapid humidity change, or the photochemical change of the terminal electrode by direct sunlight, the solderability and electrical performance may deteriorate. Do not store capacitors under direct sunlight or dewing condition. To store products on the shelf and avoid exposure to moisture.




Multilayer Ceramic Capacitors Ultra-Small Series




Recommended Soldering Conditions:

The lead-free termination MLCCs are not only to be used on SMT against lead-free solder paste, but also suitable against lead-containing solder paste. If the optimized solder joint is requested, increasing soldering time, temperature and concentration of N₂ within oven are recommended.



Recommended reflow soldering profile for SMT process with SnAgCu series solder paste.



Recommended wave soldering profile for SMT process with SnAgCu series solder.

Multilayer Ceramic Capacitors

Ultra-Small Series



Part Number Table

Description	Partnumber
Cap, MLCC, 100PF, 25V, NP0, 0201, Reel	MC000359
Cap, MLCC, 100NF, 6.3V, X5R, 0201, Reel	MC000360
Cap, MLCC, 1NF, 16V, X7R, 0201, Reel	MC000361
Cap, MLCC, 10NF, 10V, X7R, 0201, Reel	MC000362
Cap, MLCC, 4.7NF, 10V, X7R, 0201, Reel	MC000363
Cap, MLCC, 10NF, 10V, X5R, 0201, Reel	MC000364

Important Notice : This data sheet and its contents (the "Information") belong to the members of the Premier Farnell group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp is the registered trademark of the Group. © Premier Farnell plc 2012.

www.element14.com
www.farnell.com
www.newark.com

