

SAFETY DATA SHEET

RX439N/NC

Page: 1

Compilation date: 27/01/2012

Revision No: 1

Section 1: Identification of the substance/mixture and of the company/undertaking

1.1. Product identifier

Product name: RX439N/NC

1.2. Relevant identified uses of the substance or mixture and uses advised against

1.3. Details of the supplier of the safety data sheet

Company name: Robnor Resins Ltd
Hunts Rise
South Marston Park
Swindon
Wiltshire
SN3 4TE
United Kingdom

Tel: +44(0)1793 823741

Fax: +44(0)1793 827033

Email: support@robnor.co.uk

1.4. Emergency telephone number

Emergency tel: +44(0)1793 823741
(office hours only)

Section 2: Hazards identification

2.1. Classification of the substance or mixture

Classification under CHIP: Xi: R36/38; Sens.: R43; N: R51/53

Most important adverse effects: Irritating to eyes and skin. May cause sensitisation by skin contact. Toxic to aquatic organisms, may cause long-term adverse effects in the aquatic environment.

2.2. Label elements

Label elements under CHIP:

Hazard symbols: Irritant.
Dangerous for the environment.



Risk phrases: R36/38: Irritating to eyes and skin.
R43: May cause sensitisation by skin contact.
R51/53: Toxic to aquatic organisms, may cause long-term adverse effects in the aquatic environment.

Safety phrases: S24: Avoid contact with skin.
S37: Wear suitable gloves.
S61: Avoid release to the environment. Refer to special instructions / safety data sheets.

SAFETY DATA SHEET

RX439N/NC

Page: 2

2.3. Other hazards

PBT: This substance is not identified as a PBT substance.

Section 3: Composition/information on ingredients

3.2. Mixtures

Hazardous ingredients:

ZINC OXIDE

EINECS	CAS	CHIP Classification	CLP Classification	Percent
-	1314-13-2	N: R50/53	-	10-30%

BISPHENOL A-(EPICHLORHYDRIN) {REACTION PRODUCT}

500-033-5	25068-38-6	Xi: R36/38; Sens.: R43; N: R51/53	-	10-30%
-----------	------------	-----------------------------------	---	--------

1,4-BIS(2,3-EPOXYPROPOXY) BUTANE

219-371-7	2425-79-8	Xn: R20/21; Xi: R36/38; Sens.: R43	-	1-10%
-----------	-----------	------------------------------------	---	-------

2,3-EPOXYPROPYL NEODECANOATE

247-979-2	26761-45-5	Sens.: R43; N: R51/53	-	1-10%
-----------	------------	-----------------------	---	-------

Section 4: First aid measures

4.1. Description of first aid measures

Skin contact: Remove all contaminated clothes and footwear immediately unless stuck to skin. Wash immediately with plenty of soap and water.

Eye contact: Bathe the eye with running water for 15 minutes. Consult a doctor.

Ingestion: Wash out mouth with water. Consult a doctor.

Inhalation: Remove casualty from exposure ensuring one's own safety whilst doing so. Consult a doctor.

4.2. Most important symptoms and effects, both acute and delayed

Skin contact: There may be irritation and redness at the site of contact.

Eye contact: There may be irritation and redness. The eyes may water profusely.

Ingestion: There may be soreness and redness of the mouth and throat.

Inhalation: There may be irritation of the throat with a feeling of tightness in the chest. Exposure may cause coughing or wheezing.

Delayed / immediate effects: Delayed effects can be expected after long-term exposure.

4.3. Indication of any immediate medical attention and special treatment needed

Immediate / special treatment: Eye bathing equipment should be available on the premises.

Section 5: Fire-fighting measures

5.1. Extinguishing media

Extinguishing media: Suitable extinguishing media for the surrounding fire should be used. Use water spray to cool containers.

5.2. Special hazards arising from the substance or mixture

Exposure hazards: In combustion emits toxic fumes.

5.3. Advice for fire-fighters

Advice for fire-fighters: Wear self-contained breathing apparatus. Wear protective clothing to prevent contact with skin and eyes.

[cont...]

SAFETY DATA SHEET

RX439N/NC

Page: 3

Section 6: Accidental release measures

6.1. Personal precautions, protective equipment and emergency procedures

Personal precautions: Refer to section 8 of SDS for personal protection details. If outside do not approach from downwind. If outside keep bystanders upwind and away from danger point. Mark out the contaminated area with signs and prevent access to unauthorised personnel. Turn leaking containers leak-side up to prevent the escape of liquid.

6.2. Environmental precautions

Environmental precautions: Do not discharge into drains or rivers. Contain the spillage using bunding.

6.3. Methods and material for containment and cleaning up

Clean-up procedures: Absorb into dry earth or sand. Transfer to a closable, labelled salvage container for disposal by an appropriate method.

6.4. Reference to other sections

Reference to other sections: Refer to section 8 of SDS.

Section 7: Handling and storage

7.1. Precautions for safe handling

Handling requirements: Avoid direct contact with the substance. Ensure there is sufficient ventilation of the area. Do not handle in a confined space. Avoid the formation or spread of mists in the air.

7.2. Conditions for safe storage, including any incompatibilities

Storage conditions: Store in cool, well ventilated area. Keep container tightly closed. The floor of the storage room must be impermeable to prevent the escape of liquids.

Suitable packaging: Must only be kept in original packaging.

7.3. Specific end use(s)

Specific end use(s): No data available.

Section 8: Exposure controls/personal protection

8.1. Control parameters

Hazardous ingredients:

ZINC OXIDE

Workplace exposure limits:

Respirable dust

State	8 hour TWA	15 min. STEL	8 hour TWA	15 min. STEL
UK	5 mg/m ³	10 mg/m ³	-	-

8.2. Exposure controls

Engineering measures: Ensure there is sufficient ventilation of the area. The floor of the storage room must be impermeable to prevent the escape of liquids.

Respiratory protection: Self-contained breathing apparatus must be available in case of emergency.

Hand protection: Protective gloves.

Eye protection: Safety glasses. Ensure eye bath is to hand.

Skin protection: Protective clothing.

Environmental: Prevent from entering in public sewers or the immediate environment.

[cont...]

SAFETY DATA SHEET

RX439N/NC

Page: 4

Section 9: Physical and chemical properties

9.1. Information on basic physical and chemical properties

State: Liquid
Colour: Off-white
Odour: Barely perceptible odour
Relative density: 2.05

9.2. Other information

Other information: Not applicable.

Section 10: Stability and reactivity

10.1. Reactivity

Reactivity: Stable under recommended transport or storage conditions.

10.2. Chemical stability

Chemical stability: Stable under normal conditions.

10.3. Possibility of hazardous reactions

Hazardous reactions: Hazardous reactions will not occur under normal transport or storage conditions.
Decomposition may occur on exposure to conditions or materials listed below.

10.4. Conditions to avoid

Conditions to avoid: Heat. Direct sunlight.

10.5. Incompatible materials

Materials to avoid: Strong oxidising agents. Strong acids.

10.6. Hazardous decomposition products

Haz. decomp. products: In combustion emits toxic fumes.

Section 11: Toxicological information

11.1. Information on toxicological effects

Relevant effects for mixture:

Effect	Route	Basis
Irritation	OPT DRM	Hazardous: calculated
Sensitisation	DRM	Hazardous: calculated

Symptoms / routes of exposure

Skin contact: There may be irritation and redness at the site of contact.
Eye contact: There may be irritation and redness. The eyes may water profusely.
Ingestion: There may be soreness and redness of the mouth and throat.
Inhalation: There may be irritation of the throat with a feeling of tightness in the chest. Exposure may cause coughing or wheezing.

Delayed / immediate effects: Delayed effects can be expected after long-term exposure.

Section 12: Ecological information

12.1. Toxicity

Ecotoxicity values: Not applicable.

[cont...]

SAFETY DATA SHEET

RX439N/NC

Page: 5

12.2. Persistence and degradability

Persistence and degradability: Not biodegradable.

12.3. Bioaccumulative potential

Bioaccumulative potential: Bioaccumulation potential.

12.4. Mobility in soil

Mobility: Readily absorbed into soil.

12.5. Results of PBT and vPvB assessment

PBT identification: This substance is not identified as a PBT substance.

12.6. Other adverse effects

Other adverse effects: Toxic to aquatic organisms. Toxic to soil organisms.

Section 13: Disposal considerations

13.1. Waste treatment methods

Disposal operations: Transfer to a suitable container and arrange for collection by specialised disposal company.

NB: The user's attention is drawn to the possible existence of regional or national regulations regarding disposal.

Section 14: Transport information

14.1. UN number

UN number: UN3082

14.2. UN proper shipping name

Shipping name: ENVIRONMENTALLY HAZARDOUS SUBSTANCE, LIQUID, N.O.S.
(BISPHENOL A-(EPICHLORHYDRIN) {REACTION PRODUCT}); ZINC OXIDE

14.3. Transport hazard class(es)

Transport class: 9

14.4. Packing group

Packing group: III

14.5. Environmental hazards

Environmentally hazardous: Yes

Marine pollutant: No

14.6. Special precautions for user

Special precautions: No special precautions.

Tunnel code: E

Transport category: 3

Section 15: Regulatory information

15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture

15.2. Chemical Safety Assessment

Chemical safety assessment: A chemical safety assessment has not been carried out for the substance or the mixture by the supplier.

[cont...]

SAFETY DATA SHEET

RX439N/NC

Page: 6

Section 16: Other information

Other information

Other information: This safety data sheet is prepared in accordance with Commission Regulation (EU) No 453/2010.

* indicates text in the SDS which has changed since the last revision.

Phrases used in s.2 and 3: R20/21: Harmful by inhalation and in contact with skin.

R36/38: Irritating to eyes and skin.

R43: May cause sensitisation by skin contact.

R50/53: Very toxic to aquatic organisms, may cause long-term adverse effects in the aquatic environment.

R51/53: Toxic to aquatic organisms, may cause long-term adverse effects in the aquatic environment.

Legal disclaimer: The above information is believed to be correct but does not purport to be all inclusive and shall be used only as a guide. This company shall not be held liable for any damage resulting from handling or from contact with the above product.