



Micro Commercial Components

Micro Commercial Components  
 20736 Marilla Street Chatsworth  
 CA 91311  
 Phone: (818) 701-4933  
 Fax: (818) 701-4939

# MMDT5551

## Features

- Case Material: Molded Plastic. UL Flammability Classification Rating 94-0 and MSL Rating 1
- Marking: K4N
- Surface Mount SOT-363 Package
- Capable of 200mWatts of Power Dissipation
- Ideal for Medium Power Amplification and Switching
- Operating and Storage Junction Temperatures: -55°C to 150°C

## Plastic-Encapsulate Transistors

### Electrical Characteristics @ 25°C Unless Otherwise Specified

Symbol	Parameter	Min	Max	Units
$V_{(BR)CEO}$	Collector-Emitter Breakdown Voltage ( $I_C=1\text{ mAdc}$ , $I_B=0$ )	160		Vdc
$V_{(BR)CBO}$	Collector-Base Breakdown Voltage ( $I_C=100\mu\text{A}$ , $I_E=0$ )	180		Vdc
$V_{(BR)EBO}$	Emitter-Base Breakdown Voltage ( $I_E=10\mu\text{Adc}$ , $I_C=0$ )	6.0		Vdc
$I_{EBO}$	Emitter Cutoff Current ( $V_{EB}=4\text{Vdc}$ , $I_C=0$ )		50	nAdc
$I_{CBO}$	Collector Cutoff Current ( $V_{CB}=120\text{Vdc}$ , $I_E=0$ )		50	nAdc
$I_C$	Collector Current-Continuous		200	mA
$R_{\theta JA}$	Thermal Resistance, Junction to Ambient		625	K/W


### ON CHARACTERISTICS

$h_{FE}$	DC Current Gain* ( $I_C=1\text{mAdc}$ , $V_{CE}=5.0\text{Vdc}$ ) ( $I_C=10\text{mAdc}$ , $V_{CE}=5.0\text{Vdc}$ )	80 80	250	
$V_{CE(sat)}$	Collector-Emitter Saturation Voltage ( $I_C=10\text{mAdc}$ , $I_B=1.0\text{mAdc}$ )		0.15	Vdc
$V_{BE(sat)}$	Base-Emitter Saturation Voltage ( $I_C=10\text{mAdc}$ , $I_B=1.0\text{mAdc}$ )		1.0	Vdc

### SMALL-SIGNAL CHARACTERISTICS

$f_T$	Current Gain-Bandwidth Product ( $I_C=10\text{mAdc}$ , $V_{CE}=20\text{Vdc}$ , $f=100\text{MHz}$ )	100	300	MHz
$C_{obo}$	Output Capacitance ( $V_{CB}=5.0\text{Vdec}$ , $I_E=0$ , $f=1.0\text{MHz}$ )		6.0	pF
Noise figure	$R_g=1\text{kohm}$ $V_{CE}=5.0\text{Vdec}$ , $I_C=200\mu\text{A}$ , $f=1.0\text{KHz}$		8.0	NF

### SOT-363



DIM	DIMENSIONS				NOTE
	INCHES		MM		
A	.006	.014	0.15	0.35	
B	.045	.053	1.15	1.35	
C	.085	.096	2.15	2.45	
D	.026		0.65Nominal		
G	.047	.055	1.20	1.40	
H	.071	.087	1.80	2.20	
J	---	.004	---	0.10	
K	.035	.043	0.90	1.10	
L	.010	.018	0.26	0.46	
M	.003	.006	0.08	0.15	



Micro Commercial Components

## Ordering Information

Device (Part Number)-TP	Packing Tape&Reel;3Kpcs/Reel
----------------------------	---------------------------------

### \*\*\*IMPORTANT NOTICE\*\*\*

*Micro Commercial Components Corp.* reserves the right to make changes without further notice to any product herein to make corrections, modifications, enhancements, improvements, or other changes. *Micro Commercial Components Corp.* does not assume any liability arising out of the application or use of any product described herein; neither does it convey any license under its patent rights, nor the rights of others. The user of products in such applications shall assume all risks of such use and will agree to hold *Micro Commercial Components Corp.* and all the companies whose products are represented on our website, harmless against all damages.

### \*\*\*APPLICATIONS DISCLAIMER\*\*\*

Products offer by *Micro Commercial Components Corp.* are not intended for use in Medical, Aerospace or Military Applications.