

Product data sheet

Characteristics

XVBC21

INDICATING BANK ACCESSORIES 70MM

+OPTIONS

Price*: 61.00 USD



Main

Commercial Status	Commercialised
Range of product	Harmony XVB Universal
Product or component type	Base unit with cover
Component name	XVBC
Indicator bank base type	Standard
Material	Polycarbonate cover unit Glass reinforced polyamide base unit

Complementary

Fixing mode	Direct or tube fixing
Mounting diameter	2.76 in (70 mm)
Product destination	Banks without flash discharge tube unit
Cable entry	Bottom or side entry
Assembly style	Customer assembly, up to 5 units
Terminals description ISO n°1	(COM-1)PW (COM-2)PW (COM-3)PW (COM-4)PW (COM-5)PW (GND)GROUND
Product weight	0.42 lb(US) (0.19 kg)

Environment

Product certifications	CCC CSA C22-2 No 14 GOST UL 508
Standards	EN/IEC 60947-5-1
Protective treatment	TC
Ambient air temperature for storage	-40...158 °F (-40...70 °C)
NEMA degree of protection	NEMA 4X indoor UL 508

Ordering and shipping details

Category	22611 - XVB-STACKLIGHTS
Discount Schedule	XV
GTIN	00785901845027
Nbr. of units in pkg.	1
Package weight(Lbs)	0.45
Returnability	Y
Country of origin	ID