

# LC1D12P7

TeSys D contactor - 3P(3 NO) - AC-3 -  $\leq 440$   
V 12 A - 230 V AC coil



## Main

|   |   |
|---|---|
| Commercial Status                           | Commercialised  |
| Range of product                            | TeSys D   |
| Product or component type                   | Contacteur  |
| Device short name                           | LC1D  |
| Contacteur application                      | Motor control<br>Resistive load   |
| Utilisation category                        | AC-1<br>AC-3  |
| Poles description                           | 3P  |
| Power pole contact composition              | 3 NO  |
| [Ue] rated operational voltage              | $\leq 300$ V DC for power circuit<br>$\leq 690$ V AC 25...400 Hz for power circuit  |
| [Ie] rated operational current              | 25 A ( $\leq 60$ °C) at $\leq 440$ V AC AC-1 for power circuit<br>12 A ( $\leq 60$ °C) at $\leq 440$ V AC AC-3 for power circuit  |
| Motor power kW                              | 7.5 kW at 660...690 V AC 50/60 Hz<br>7.5 kW at 500 V AC 50/60 Hz<br>5.5 kW at 415...440 V AC 50/60 Hz<br>5.5 kW at 380...400 V AC 50/60 Hz<br>3 kW at 220...230 V AC 50/60 Hz   |
| Motor power HP (UL / CSA)                   | 10 hp at 575/600 V AC 50/60 Hz for 3 phases motors<br>7.5 hp at 460/480 V AC 50/60 Hz for 3 phases motors<br>3 hp at 230/240 V AC 50/60 Hz for 3 phases motors<br>3 hp at 200/208 V AC 50/60 Hz for 3 phases motors<br>2 hp at 230/240 V AC 50/60 Hz for 1 phase motors<br>1 hp at 115 V AC 50/60 Hz for 1 phase motors |
| Control circuit type                        | AC 50/60 Hz   |
| Control circuit voltage                     | 230 V AC 50/60 Hz   |
| Auxiliary contact composition               | 1 NO + 1 NC   |
| [Uimp] rated impulse withstand voltage      | 6 kV conforming to IEC 60947  |
| Overvoltage category                        | III   |
| [Ith] conventional free air thermal current | 10 A at $\leq 60$ °C for signalling circuit<br>25 A at $\leq 60$ °C for power circuit   |
| Irms rated making capacity                  | 250 A DC for signalling circuit conforming to IEC 60947-5-1<br>140 A AC for signalling circuit conforming to IEC 60947-5-1<br>250 A at 440 V for power circuit conforming to IEC 60947  |
| Rated breaking capacity                     | 250 A at 440 V for power circuit conforming to IEC 60947  |
| [Icw] rated short-time withstand current    | 61 A $\leq 40$ °C 1 min power circuit<br>30 A $\leq 40$ °C 10 min power circuit<br>140 A 100 ms signalling circuit<br>120 A 500 ms signalling circuit<br>100 A 1 s signalling circuit<br>210 A $\leq 40$ °C 1 s power circuit<br>105 A $\leq 40$ °C 10 s power circuit  |

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

|                               |  |
|-------------------------------|--|
| Associated fuse rating        | 10 A gG for signalling circuit conforming to IEC 60947-5-1<br>25 A gG at ≤ 690 V coordination type 2 for power circuit<br>40 A gG at ≤ 690 V coordination type 1 for power circuit   |
| Average impedance             | 2.5 mOhm at 50 Hz - Ith 25 A for power circuit   |
| [Ui] rated insulation voltage | 600 V for signalling circuit certifications UL<br>600 V for signalling circuit certifications CSA<br>690 V for signalling circuit conforming to IEC 60947-1<br>600 V for power circuit certifications UL<br>600 V for power circuit certifications CSA<br>690 V for power circuit conforming to IEC 60947-4-1  |
| Electrical durability         | 0.8 Mcycles 25 A AC-1 at Ue ≤ 440 V<br>2 Mcycles 12 A AC-3 at Ue ≤ 440 V   |
| Power dissipation per pole    | 1.56 W AC-1<br>0.36 W AC-3   |
| Safety cover                  | With   |
| Mounting support              | Plate<br>Rail  |
| Standards                     | EN 60947-4-1<br>EN 60947-5-1<br>IEC 60947-4-1<br>IEC 60947-5-1<br>UL 508<br>CSA C22.2 No 14  |
| Product certifications        | BV<br>CCC<br>CSA<br>DNV<br>GL<br>GOST<br>RINA<br>UL<br>LROS  |
| Connections - terminals       | Control circuit: screw clamp terminals 2 cable(s)<br>1...4 mm <sup>2</sup> - cable stiffness: solid - without cable end<br>Control circuit: screw clamp terminals 1 cable(s)<br>1...4 mm <sup>2</sup> - cable stiffness: solid - without cable end<br>Control circuit: screw clamp terminals 2 cable(s)<br>1...2.5 mm <sup>2</sup> - cable stiffness: flexible - with cable end<br>Control circuit: screw clamp terminals 1 cable(s)<br>1...4 mm <sup>2</sup> - cable stiffness: flexible - with cable end<br>Control circuit: screw clamp terminals 2 cable(s)<br>1...4 mm <sup>2</sup> - cable stiffness: flexible - without cable end<br>Control circuit: screw clamp terminals 1 cable(s)<br>1...4 mm <sup>2</sup> - cable stiffness: flexible - without cable end<br>Power circuit: screw clamp terminals 2 cable(s) 1...4 mm <sup>2</sup> - cable stiffness: solid - without cable end<br>Power circuit: screw clamp terminals 1 cable(s) 1...4 mm <sup>2</sup> - cable stiffness: solid - without cable end<br>Power circuit: screw clamp terminals 2 cable(s) 1...2.5 mm <sup>2</sup> - cable stiffness: flexible - with cable end<br>Power circuit: screw clamp terminals 1 cable(s) 1...4 mm <sup>2</sup> - cable stiffness: flexible - with cable end<br>Power circuit: screw clamp terminals 2 cable(s) 1...4 mm <sup>2</sup> - cable stiffness: flexible - without cable end<br>Power circuit: screw clamp terminals 1 cable(s) 1...4 mm <sup>2</sup> - cable stiffness: flexible - without cable end |
| Tightening torque             | Control circuit: 1.7 N.m - on screw clamp terminals - with screwdriver Philips No 2<br>Control circuit: 1.7 N.m - on screw clamp terminals - with screwdriver flat Ø 6 mm<br>Power circuit: 1.7 N.m - on screw clamp terminals - with screwdriver Philips No 2<br>Power circuit: 1.7 N.m - on screw clamp terminals - with screwdriver flat Ø 6 mm   |
| Operating time                | 4...19 ms opening<br>12...22 ms closing  |

|                          |   |
|--------------------------|---|
| Safety reliability level | B10d = 2000000 cycles contactor with mechanical load conforming to EN/ISO 13849-1<br>B10d = 1369863 cycles contactor with nominal load conforming to EN/ISO 13849-1 |
| Mechanical durability    | 15 Mcycles  |
| Operating rate           | 3600 cyc/h at $\leq 60\text{ }^{\circ}\text{C}$   |

## Complementary

|                                 |  |
|---------------------------------|--|
| Coil technology                 | Without built-in suppressor module   |
| Control circuit voltage limits  | 0.85...1.1 $U_c$ at $60\text{ }^{\circ}\text{C}$ operational 60 Hz<br>0.8...1.1 $U_c$ at $60\text{ }^{\circ}\text{C}$ operational 50 Hz<br>0.3...0.6 $U_c$ at $60\text{ }^{\circ}\text{C}$ drop-out 50/60 Hz |
| Inrush power in VA              | 70 VA at $20\text{ }^{\circ}\text{C}$ ( $\cos \phi$ 0.75) 50 Hz<br>70 VA at $20\text{ }^{\circ}\text{C}$ ( $\cos \phi$ 0.75) 60 Hz   |
| Hold-in power consumption in VA | 7 VA at $20\text{ }^{\circ}\text{C}$ ( $\cos \phi$ 0.3) 50 Hz<br>7.5 VA at $20\text{ }^{\circ}\text{C}$ ( $\cos \phi$ 0.3) 60 Hz   |
| Heat dissipation                | 2...3 W at 50/60 Hz  |
| Auxiliary contacts type         | Type mirror contact (1 NC) conforming to IEC 60947-4-1<br>Type mechanically linked (1 NO + 1 NC) conforming to IEC 60947-5-1   |
| Signalling circuit frequency    | 25...400 Hz  |
| Minimum switching current       | 5 mA for signalling circuit  |
| Minimum switching voltage       | 17 V for signalling circuit  |
| Non-overlap time                | 1.5 ms on energisation (between NC and NO contact)<br>1.5 ms on de-energisation (between NC and NO contact)  |
| Insulation resistance           | > 10 MOhm for signalling circuit   |

## Environment

|   |  |
|---|--|
| IP degree of protection                               | IP2x front face conforming to IEC 60529  |
| Protective treatment                                  | TH conforming to IEC 60068-2-30  |
| Pollution degree                                      | 3  |
| Ambient air temperature for operation                 | -5...60 $^{\circ}\text{C}$   |
| Ambient air temperature for storage                   | -60...80 $^{\circ}\text{C}$  |
| Permissible ambient air temperature around the device | -40...70 $^{\circ}\text{C}$ at $U_c$   |
| Operating altitude                                    | 3000 m without derating in temperature   |
| Fire resistance                                       | 850 $^{\circ}\text{C}$ conforming to IEC 60695-2-1   |
| Flame retardance                                      | V1 conforming to UL 94   |
| Mechanical robustness                                 | Shocks contactor closed 15 Gn for 11 ms<br>Shocks contactor open 10 Gn for 11 ms<br>Vibrations contactor closed 4 Gn, 5...300 Hz<br>Vibrations contactor open 2 Gn, 5...300 Hz |
| Height  | 77 mm  |
| Width   | 45 mm  |
| Depth   | 86 mm  |
| Product weight  | 0.325 kg   |

## RoHS compliance

|                                   |           |
|-----------------------------------|-----------|
| RoHS EUR status                   | Compliant |
| RoHS EUR conformity date(Y Y W W) | 0627      |

## Contractual warranty

|        |           |
|--------|-----------|
| Period | 18 months |
|--------|-----------|