

Productname : Kontakt ipa
Ref.Nr.: BDS000792_3_20130325

Creationdate : 25.03.13 Version : 1.1
Replaces: BDS000792_20111110

SECTION 1: Identification of the substance/mixture and of the company/undertaking

1.1. Product identifier

Kontakt ipa
Aerosol

1.2. Relevant identified uses of the substance or mixture and uses advised against

Cleaners - Precision

1.3. Details of the supplier of the safety data sheet

CRC Industries Europe bvba
Touwslagerstraat 1
9240 Zele
Belgium
Tel.: +32(0)52/45.60.11
Fax.: +32(0)52/45.00.34
E-mail : hse@crcind.com

Subsidiaries		Tel	Fax
CRC Industries Finland Oy	Asemanrinne 13, 08500 Lohja	+358/(19)32.921	+358/(19)383.676
CRC Industries France	6, avenue du marais, C.S. 90028, 95102 Argenteuil Cedex	01.34.11.20.00	01.34.11.09.96
CRC Industries Deutschland GmbH	Südring 9, D-76473 Iffezheim	(07229) 303.0	(07229)30 32 66
CRC INDUSTRIES IBERIA S.L.U.	GREMIO DEL CUERO-PARC.96, POLIGONO INDUSTRI. DE HONTORIA, 40195 SEGOVIA	0034/921.427.546	0034/921.436.270
CRC Industries Sweden	Kryptogatan 14, 431 53 Mölndal	0046/31 706 84 80	0046/31 27 39 91

1.4. Emergency telephone number

CRC Industries Europe, Belgium: Tel.: +32(0)52/45.60.11 (office hours)

SECTION 2: Hazards identification

2.1. Classification of the substance or mixture

Classification according to 67/548/EEC or 1999/45/EC:

Health: R36: Irritating to eyes.
R67: Vapours may cause drowsiness and dizziness.



CRC Industries Europe bvba

Touwslagerstraat 1, 9240 Zele – Belgium
Tel (+32) (0) 52 / 45 60 11 – Fax (+32) (0) 52 / 45 00 34 – www.crcind.com

1 / 9

Safety Data Sheet

Regulation EC No 1907/2006 Art.31

Productname : Kontakt ipa
Ref.Nr.: BDS000792_3_20130325

Creationdate : 25.03.13 Version : 1.1
Replaces: BDS000792_20111110

Physical: EXTREMELY FLAMMABLE
Environment: not classified

2.2. Label elements

Warning symbol(s) : EXTREMELY FLAMMABLE



Xi : IRRITANT



Risk-phrase(s) : R36: Irritating to eyes.
R67: Vapours may cause drowsiness and dizziness.

Safety-phrase(s) : S2: Keep out of the reach of children.
S16: Keep away from sources of ignition - No smoking.
S23: Do not breathe vapours/spray.
S35: This material and its container must be disposed of in a safe way.
S51: Use only in well-ventilated areas.

Extra label elements according to Aerosol Dispenser Directive 75/324/EC:

Pressurised container: protect from sunlight and do not expose to temperatures exceeding 50°C. Do not pierce or burn, even after use. Do not spray on a naked flame or any incandescent material.

Without adequate ventilation formation of explosive mixtures may be possible.

2.3. Other hazards

None

SECTION 3: Composition/information on ingredients

3.1. Substances

Not applicable.

3.2. Mixtures

Hazardous ingredient	CAS-nr.	EC-nr	w/w %	symbol	R-phrases*	Notes
propan-2-ol; isopropyl alcohol ;isopropanol	67-63-0	200-661-7	75-100	F,Xi	11-36-67	B
carbon dioxide	124-38-9	204-696-9	1-5	-	-	A,G
Explanation notes						
A : substance with Community workplace exposure limit						
B : substance with national established workplace exposure limit						
G : exempted from the obligation to register in accordance with art.2(7)(a)of REACH Regulation No 1907/2006						



CRC Industries Europe bvba

Touwslagerstraat 1, 9240 Zele – Belgium
Tel (+32) (0) 52 / 45 60 11 – Fax (+32) (0) 52 / 45 00 34 – www.crcind.com

2 / 9

Productname : Kontakt ipa
Ref.Nr.: BDS000792_3_20130325

Creationdate : 25.03.13 Version : 1.1
Replaces: BDS000792_20111110

Hazardous ingredient	Registration number	CAS-nr.	EC-nr	w/w %	Hazard Class and Category	Hazard statement	Notes
propan-2-ol; isopropyl alcohol ;isopropanol	01-2119457558-25	67-63-0	200-661-7	75-100	Flam. Liq. 2, Eye Irrit. 2, STOT SE 3	H225,H319,H336	B
carbon dioxide		124-38-9	204-696-9	1-5	Press. Gas	H280	A,G

Explanation notes

A : substance with Community workplace exposure limit
B : substance with national established workplace exposure limit
G : exempted from the obligation to register in accordance with art.2(7)(a)of REACH Regulation No 1907/2006

(* Explanation phrases : see chapter 16)

SECTION 4: First aid measures

4.1. Description of first aid measures

Contact with eyes :	If substance has got into eyes, immediately wash out with water for at least 15 minutes Seek medical advice
Contact with skin :	Remove contaminated clothing immediately and drench affected skin with plenty of water. Then wash with soap and water Seek medical attention if irritation persists
Inhalation :	Remove patient to fresh air Keep warm and at rest, in a half upright position. Loosen clothing Seek medical attention if ill effects occur
Ingestion :	If swallowed accidentally, do not induce vomiting and seek medical advice.

4.2. Most important symptoms and effects, both acute and delayed

Inhalation :	Excessive inhalation of solvent vapours may give rise to nausea, headaches and dizziness
Ingestion :	May cause gastrointestinal disturbances Symptoms : sore throat, abdominal pain, nausea, vomiting
Skin contact :	May cause irritation. Symptoms : redness and pain
Eye contact :	Irritating to eyes Symptoms : redness and pain

4.3. Indication of any immediate medical attention and special treatment needed

General Advice :	If you feel unwell, seek medical advice (show the label where possible) If symptoms persist always call a doctor
-------------------------	---------------------------------------------------------------------------------------------------------------------

SECTION 5: Firefighting measures

5.1. Extinguishing media



CRC Industries Europe bvba

Touwslagerstraat 1, 9240 Zele – Belgium
Tel (+32) (0) 52 / 45 60 11 – Fax (+32) (0) 52 / 45 00 34 – www.crcind.com

3 / 9

Productname : Kontakt ipa
Ref.Nr.: BDS000792_3_20130325

Creationdate : 25.03.13 Version : 1.1
Replaces: BDS000792_20111110

foam, carbon dioxide or dry agent

5.2. Special hazards arising from the substance or mixture

Aerosols may explode if heated above 50°C
Forms hazardous decomposition products
CO,CO2

5.3. Advice for firefighters

Keep container(s) exposed to fire cool, by spraying with water
In case of fire, do not breathe fumes

SECTION 6: Accidental release measures

6.1. Personal precautions, protective equipment and emergency procedures

Shut off all ignition sources
Ensure adequate ventilation
Wear suitable protective clothing and gloves.

6.2. Environmental precautions

Do not allow to enter public sewers and watercourses
If polluted water reaches drainage systems or water courses, immediately inform appropriate authorities

6.3. Methods and material for containment and cleaning up

Absorb spillage in suitable inert material
Place in appropriate container

6.4. Reference to other sections

For further information see section 8

SECTION 7: Handling and storage

7.1. Precautions for safe handling

Keep away from heat and sources of ignition
Take precautionary measures against static discharges
Equipment should be earthed
Use explosion-proof electrical/ventilating/lighting/.../equipment.
Use only non-sparking tools.
Do not breathe aerosols or vapours.
Ensure adequate ventilation



Productname : Kontakt ipa
Ref.Nr.: BDS000792_3_20130325
Creationdate : 25.03.13 Version : 1.1
Replaces: BDS000792_20111110

Avoid contact with skin and eyes.
 Wash thoroughly after use
 Wear protective gloves/protective clothing/eye protection/face protection.
 Eyewash bottles should be available

7.2. Conditions for safe storage, including any incompatibilities

Pressurized container : protect from sunlight and do not expose to temperatures exceeding 50°C.
 Keep out of reach of children.

7.3. Specific end use(s)

Cleaners - Precision

SECTION 8: Exposure controls/personal protection

8.1. Control parameters

Exposure limits :

Hazardous ingredient	CAS-nr.	method	
EU established exposure limits:			
carbon dioxide	124-38-9	TWA	5000 ppm
propan-2-ol; isopropyl alcohol ;isopropanol	67-63-0	TWA	400 ppm
		STEL	500 ppm
National established exposure limits, United Kingdom			
carbon dioxide	124-38-9	TWA	5000 ppm
		STEL	15000 ppm

8.2. Exposure controls

Control procedures :	Ensure adequate ventilation Keep away from heat and sources of ignition Take precautionary measures against static discharges
Personal protection :	Take precautions to avoid contact with skin and eyes when handling the product. Ensure adequate ventilation
inhalation :	In case of insufficient ventilation, wear suitable respiratory equipment. Air purifying respirator equipped with organic gas/vapor cartridge (type A or AX)
hands and skin :	Wear suitable protective gloves against chemicals (neoprene)
eyes :	Wear safety goggles.

Productname : Kontakt ipa
Ref.Nr.: BDS000792_3_20130325

Creationdate : 25.03.13 Version : 1.1
Replaces: BDS000792_20111110

SECTION 9: Physical and chemical properties

9.1. Information on basic physical and chemical properties

(for aerosols data for the product without propellant)

Apperance : physical state : CO2 propelled liquid.
colour : Colorless.
odour : Alcohol.
pH : Not applicable.
Boiling point/range : 82 °C
Flash point : 12 °C (Closed Cup)
Explosion limits : upper limit : 12 %
lower limit : 2 %
Vapour pressure : 43 mbar (@ 20°C)
Relative density : 0.8
Solubility in water : Soluble in water
Auto-ignition : 425 °C

9.2. Other information

VOC: 760 g/l

SECTION 10: Stability and reactivity

10.1. Reactivity

No hazardous reactions known if used for its intended purpose

10.2. Chemical stability

Stable

10.3. Possibility of hazardous reactions

No hazardous reactions known if used for its intended purpose

10.4. Conditions to avoid

Avoid overheating

10.5. Incompatible materials

Strong oxidising agent

10.6. Hazardous decomposition products



Productname : Kontakt ipa
Ref.Nr.: BDS000792_3_20130325

Creationdate : 25.03.13 Version : 1.1
Replaces: BDS000792_20111110

CO,CO2

SECTION 11: Toxicological information

11.1. Information on toxicological effects

Inhalation : Inhalation of solvent vapours may give rise to nausea, headaches and dizziness
Ingestion : May cause gastrointestinal disturbances
Skin contact : May cause irritation.
Eye contact : Irritating to eyes

Toxicological data :

Hazardous ingredient	CAS-nr.	method	
propan-2-ol; isopropyl alcohol ;isopropanol	67-63-0	LD50 oral rat	> 5000 mg/kg
		LC50 inhal.rat	> 20 mg/l
		LD50 derm.rabit	> 5000 mg/kg

SECTION 12: Ecological information

12.1. Toxicity

not classified

Ecotoxicological data:

Hazardous ingredient	CAS-nr.	method	
propan-2-ol; isopropyl alcohol ;isopropanol	67-63-0	IC50 algae	> 1000 mg/l
		LC50 fish	9640 mg/l
		EC50 daphnia	> 1000 mg/l

12.2. Persistence and degradability

No experimental data available

12.3. Bioaccumulative potential

No experimental data available

12.4. Mobility in soil



Productname : Kontakt ipa
Ref.Nr.: BDS000792_3_20130325

Creationdate : 25.03.13 Version : 1.1
Replaces: BDS000792_20111110

Soluble in water

12.5. Results of PBT and vPvB assessment

No information available

12.6. Other adverse effects

SECTION 13: Disposal considerations

13.1. Waste treatment methods

Product : This material and its container must be disposed of in a safe way.
Do not discharge into drains or the environment, dispose to an authorised waste collection point.

Contaminated packaging : Disposal should be in accordance with local, state or national legislation

SECTION 14: Transport information

14.1. UN number

UN-number : 1950

14.2. UN proper shipping name

Proper shipping name: AEROSOLS

14.3. Transport hazard class(es)

Class: 2.1
ADR/RID - Classification code: 5F

14.4. Packing group

Packing group: Not applicable.

14.5. Environmental hazards

ADR/RID - Environmentally hazardous: No
IMDG - Marine pollutant: No
IATA/ICAO - Environmentally hazardous: No

14.6. Special precautions for user



