

Miniature PCB Relay SDT

- 10A contact rating
- UL TV-5 rating
- 1 form A contact arrangement
- Flux proof, wash tight version available

Typical applications Appliances, HVAC, cable TV, monitor, emergency lighting





Approvals

UL E58304, TUV R50137358, CQC03001002917

Technical data of approved types on request

Contact Data				
Contact arrangement	1 Form A (NO)			
Rated voltage	250VAC, 24VDC			
Max. switching voltage	250VAC, 24VDC			
Rated current	10A			
Contact material	AgSnOlnO			
Min. recommended contact load	100mA at 5VDC			
Frequency of operation	800 ops./h			
Operate/release time max.	15/8ms			
Electrical endurance				
10A 250VAC/24VDC resistive, -30°C to +60°C 100x10 ³ ops.				
TV_{-5} 120VAC 25x10 ³ ons				

TV-5 120VAC, 25x10³ ops.

Mechanical endurance, DC coil 10x10⁶ operations

Coil Data		
Coil voltage range	3 to 48VDC	
Operative range, IEC 61810	1	
Coil insulation system according UL	Class E	


Coil Data (continued)


Coil versions, DC coil, D type			
Coil	Rated	Operate	Re
code	voltage	voltage	VO
	VDC	VDC	1


Coil	Rated	Operate	Release	Release Coil	
code	voltage	voltage	voltage	resistance	power
	VDC	VDC	VDC	Ω±10%	mW
003	3	2.25	0.30	16.7	540
005	5	3.75	0.50	46.3	540
006	6	4.50	0.60	66.7	540
009	9	6.75	0.90	150	540
012	12	9.00	1.20	267	540
018	18	13.50	1.80	600	540
024	24	18.00	2.40	1067	540
048	48	36.00	4.80	4267	540

All figures are given for coil without pre-energization, at ambient temperature +23°C

Insulation Data		
Initial dielectric strength		
between open contacts	900V _{rms}	
between contact and coil	4000V _{rms}	
Clearance/creepage		
between contact and coil	>1.6/3.2mm	









Miniature PCB Relay SDT (Continued)

Other Data Material compliance: EU RoHS/ELV, China RoHS, REACH, Halogen content refer to the Product Compliance Support Center at www.te.com/customersupport/rohssupportcenter Ambient temperature -30°C to +60°C Category of environmental protection RTII - flux proof, IEC 61810 RTIII - wash tight Shock resistance (functional) 10g 100g Shock resistance (destructive) Weight 11g Resistance to soldering heat THT IEC 60068-2-20 RTII: 270°C/10s RTIII: 260°C/5s Packaging/unit tube/25 pcs., carton box/1000 pcs.

Terminal assignment


Bottom view on solder pins




tray/100 pcs., carton box/1000 pcs.


PCB layout

Bottom view on solder pins



Dimensions





Product code	Enclosure	Coil voltage	Coil input	Arrangement	Suffix	Part number
SDT-SH-112DM,000	Wash tight	12VDC	Standard	1 form A (NO)	Standard	1419126-5
SDT-SH-124DM,000		24VDC				1-1419126-0
SDT-SS-105DM,000	Flux proof	5VDC				1-1419126-2
SDT-SS-109DM,000		9VDC				1-1419126-5
SDT-SS-112DM,000		12VDC				1-1419126-8
SDT-SS-124DM,000		24VDC				2-1419126-5