

For more Information
please call

1-800-Belden1



General Description:

18 AWG solid bare copper-covered steel conductor, foam polyethylene insulation, Duobond® IV Quad Shield (100% coverage), PVC Jacket.

Physical Characteristics (Overall)

Conductor

AWG:

# Coax	AWG	Stranding	Conductor Material	Dia. (mm)
1	18	Solid	BCCS - Bare Copper Covered Steel	1.016

Total Number of Conductors: 1

Insulation

Insulation Material:

Insulation Material	Dia. (mm)
Gas-injected FPE - Foam Polyethylene	4.572

Outer Shield

Outer Shield Material:

Layer #	Outer Shield Trade Name	Type	Outer Shield Material	Coverage (%)
1	Bonded Duofoil®	Tape	Bonded Aluminum Foil-Polyester Tape-Aluminum Foil	100
2		Braid	AL - Aluminum	60
3	Duofoil®	Tape	Aluminum Foil-Polyester Tape-Aluminum Foil	100
4		Braid	AL - Aluminum	40

Outer Jacket

Outer Jacket Material:

Outer Jacket Material
PVC - Polyvinyl Chloride

Overall Cable

Overall Nominal Diameter: 7.569 mm

Mechanical Characteristics (Overall)

Operating Temperature Range: -30°C To +75°C

Bulk Cable Weight: 49.111 Kg/Km

Max. Recommended Pulling Tension: 720.608 N

Min. Bend Radius/Minor Axis: 76.200 mm

Applicable Specifications and Agency Compliance (Overall)

Applicable Standards & Environmental Programs

NEC/(UL) Specification: CL2R, CMG, CMR

CEC/C(UL) Specification: CMG

EU Directive 2011/65/EU (ROHS II): Yes

EU CE Mark: Yes

EU Directive 2000/53/EC (ELV): Yes

EU Directive 2002/95/EC (RoHS): Yes

EU RoHS Compliance Date (mm/dd/yyyy):	01/01/2004
EU Directive 2002/96/EC (WEEE):	Yes
EU Directive 2003/11/EC (BFR):	Yes
CA Prop 65 (CJ for Wire & Cable):	Yes
MII Order #39 (China RoHS):	Yes
RG Type:	6/U

Flame Test

UL Flame Test:	UL1666 Vertical Shaft
----------------	-----------------------

Suitability

Sunlight Resistance:	Yes
----------------------	-----

Electrical Characteristics (Overall)

Nom. Characteristic Impedance:

Impedance (Ohm)

75

Nom. Inductance:

Inductance (µH/m)

0.318257

Nom. Capacitance Conductor to Shield:

Capacitance (pF/m)

53.1522

Nominal Velocity of Propagation:

VP (%)

82

Nominal Delay:

Delay (ns/m)

4.19968

Nom. Conductor DC Resistance:

DCR @ 20°C (Ohm/km)

91.868

Nominal Outer Shield DC Resistance:

DCR @ 20°C (Ohm/km)

11.8116

Nom. Attenuation:

Freq. (MHz) Attenuation (dB/100m)

1	1.14835
2	1.24678
5	1.47645
10	1.93579
20	2.82166
50	4.49497
100	6.46357
200	9.25242
300	11.4179
400	13.2552

Max. Operating Voltage - UL:

Voltage

300 V rms

Minimum Structural Return Loss:

Description Freq. (MHz) Start Freq. (MHz) Stop Freq. (MHz) Min. SRL (dB)

		5	50	23
--	--	---	----	----

Notes (Overall)

Notes: CPE jacket or LSZH jacket also available as special products.

Put Ups and Colors:

Item #	Putup	Ship Weight	Color	Notes	Item Desc
3092A X7E1000	305 MT	18.597 KG	BLUE X7E	C	#18 GIFHDLDPPE DBSH PVC
3092A X7E2000	610 MT	37.195 KG	BLUE X7E	C	#18 GIFHDLDPPE DBSH PVC
3092A X7E500	152 MT	9.299 KG	BLUE X7E		#18 GIFHDLDPPE DBSH PVC
3092A X7E5000	1,524 MT	92.987 KG	BLUE X7E		#18 GIFHDLDPPE DBSH PVC
3092A 0021000	305 MT	18.597 KG	RED	C	#18 GIFHDLDPPE DBSH PVC
3092A 0101000	305 MT	18.597 KG	BLACK	C	#18 GIFHDLDPPE DBSH PVC
3092A 01010000	3,048 MT	195.046 KG	BLACK		#18 GIFHDLDPPE DBSH PVC
3092A 0102000	610 MT	37.195 KG	BLACK	C	#18 GIFHDLDPPE DBSH PVC
3092A 0102500	762 MT	45.359 KG	BLACK	C	#18 GIFHDLDPPE DBSH PVC
3092A 010500	152 MT	9.299 KG	BLACK		#18 GIFHDLDPPE DBSH PVC
3092A 0105000	1,524 MT	92.987 KG	BLACK		#18 GIFHDLDPPE DBSH PVC

Notes:

C = CRATE REEL PUT-UP.

Revision Number: 3 Revision Date: 07-16-2012

© 2013 Belden, Inc
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

Belden declares this product to be in compliance with EU LVD (Low Voltage Directive 73/23/EEC), as amended by directive 93/68/EEC.