DFN1010




SINGLE SCHMITT-TRIGGER INVERETER

Description

The 74LVC1G14 is a single 1-input Schmitt-trigger inverter with a standard push-pull output. The device is designed for operation with a power supply range of 1.65V to 5.5V. The inputs are tolerant to 5.5V allowing this device to be used in a mixed voltage environment. The device is fully specified for partial power down applications using IOFF. The IOFF circuitry disables the output preventing damaging current backflow when the device is powered down. The gate performs the positive Boolean function:

$$Y = \overline{A}$$

Pin Assignments



Features

- Wide Supply Voltage Range from 1.65V to 5.5V
- ± 24mA Output Drive at 3.3V
- CMOS low power consumption
- IOFF Supports Partial-Power-Down Mode Operation
- Inputs accept up to 5.5V
- ESD Protection Exceeds JESD 22
 - o 200-V Machine Model (A115-A)
 - o 2000-V Human Body Model (A114-A)
- Latch-Up Exceeds 100mA per JESD 78, Class II
- Range of Package Options
- SOT25, SOT353, DFN1410, and DFN1010: Available in "Green" Molding Compound (no Br, Sb)
- Lead Free Finish/ RoHS Compliant (Note 1)

Applications

- Voltage Level Shifting
- General Purpose Logic
- · Power Down Signal Isolation
- Wide array of products such as:
 - o PCs, networking, notebooks, netbooks, PDAs
 - Computer peripherals, hard drives, CD/DVD ROM
 - o TV, DVD, DVR, set top box
 - Cell Phones, Personal Navigation / GPS
 - o MP3 players ,Cameras, Video Recorders


Notes: 1. EU Directive 2002/95/EC (RoHS). All applicable RoHS exemptions applied. Please visit our website at http://www.diodes.com/products/lead_free.html.



Pin Descriptions

Pin Name	Description
Α	Data Input
GND	Ground
Y	Data Output
V _{CC}	Supply Voltage

Logic Diagram



Function Table

Inputs	Output
Α	Υ
Н	L
L	Н



Absolute Maximum Ratings (Note 2)

Symbol	Description	Rating	Unit
ESD HBM	Human Body Model ESD Protection	2	KV
ESD MM	Machine Model ESD Protection	200	V
V _{CC}	Supply Voltage Range	-0.5 to 6.5	V
VI	Input Voltage Range	-0.5 to 6.5	V
Vo	Voltage applied to output in high impedance or I _{OFF} state	-0.5 to 6.5	V
Vo	Voltage applied to output in high or low state	-0.3 to V _{CC} +0.5	V
I _{IK}	Input Clamp Current V _I <0	-50	mA
l _{OK}	Output Clamp Current	-50	mA
Io	Continuous output current	±50	mA
	Continuous current through Vdd or GND	±100	mA
T_J	Operating Junction Temperature	-40 to 150	°C
T _{STG}	Storage Temperature	-65 to 150	°C

Notes: 2. Stresses beyond the absolute maximum may result in immediate failure or reduced reliability. These are stress values and device operation should be within recommend values.

Recommended Operating Conditions (Note 3)

Symbol		Parameter	Min	Max	Unit
\/	Operating Voltage	Operating	1.65	5.5	V
V _{CC}	Operating Voltage	Data retention only	1.5		V
V_{I}	Input Voltage		0	5.5	V
Vo	Output Voltage		0	V _{CC}	V
		V _{CC} = 1.65V		-4	
		V _{CC} = 2.3V		-8	
I_{OH}	High-level output current	V 2V		-16	mA
		V _{CC} = 3V		-24	
		V _{CC} = 4.5V		-32	
		V _{CC} = 1.65V		4	
		V _{CC} = 2.3V		8	
I_{OL}	Low-level output current	V 2V		16	mA
		V _{CC} = 3V		24	
		V _{CC} = 4.5V		32	
		$V_{CC} = 1.8V \pm 0.15V, 2.5V \pm 0.2V$		20	
Δt/ΔV	Input transition rise or fall	$V_{CC} = 3.3V \pm 0.3V$		10	ns/V
	rate	$V_{CC} = 5V \pm 0.5V$		5	1
T _A	Operating free-air temperature		-40	125	°C

Notes: 3. Unused inputs should be held at $V_{\mbox{CC}}$ or Ground.



Electrical Characteristics $T_A = -40$ °C to 85°C (All typical values are at $V_{CC} = 3.3$ V, $T_A = 25$ °C)

Symbol	Parameter	Test Conditions	V _{CC}	Min	Тур.	Max	Unit
			1.65V	0.70		1.20	
	Desitive mains innut		2.3V	1.11		1.60	
V_{T+}	Positive-going input threshold voltage		3V	1.50		2.00	
	Threshold voltage		4.5V	2.16		2.74	
			5.5V	2.61		3.33	
			1.65V	0.30		0.72	
	Mogative going input		2.3V	0.58		1.00	
V_{T-}	Negative-going input threshold voltage		3V	0.80		1.30	
	tinoonoid voitago		4.5V	1.21		1.95	
			5.5V	1.45		2.35	
			1.65V	0.30		0.62	
	Hysteresis		2.3V	0.40		0.80	
ΔV_T	(V _{T+} - V _{T-)}		3V	0.35		1.00	
	(*1+ *1-)		4.5V	0.55		1.10	
			5.5V	0.60		1.20	
		I _{OH} = -100μA	1.65V to 5.5V	V _{CC} – 0.1			
		I _{OH} = -4mA	1.65V	1.2			
V _{OH}	High Level Output Voltage	$I_{OH} = -8mA$	2.3V	1.9			V
VOH	High Level Output voltage	I _{OH} = -16mA	3V	2.4			V
		$I_{OH} = -24mA$	30	2.3			
		$I_{OH} = -32mA$	4.5V	3.8			
		I _{OL} = 100μA	1.65V to 5.5V			0.1	
		I _{OL} = 4mA	1.65V			0.45	
.,		I _{OL} = 8mA	2.3V			0.3	1 ,,
V _{OL}	High-level Input Voltage	I _{OL} = 16mA				0.4	V
		I _{OL} = 24mA	3V			0.55	
		I _{OL} = 32mA	4.5			0.55	1
II	Input Current	V _I = 5.5 V or GND	0 to 5.5V			± 5	μA
I _{OFF}	Power Down Leakage Current	V_I or $V_O = 5.5V$	0			± 10	μA
Icc	Supply Current	$V_I = 5.5V$ of GND $I_O=0$	1.65V to 5.5V			10	μA
ΔI _{CC}	Additional Supply Current	Input at V _{CC} –0.6V	3V to 5.5V			500	μΑ



Electrical Characteristics $T_A = -40$ °C to 125°C (All typical values are at $V_{CC} = 3.3V$, $T_A = 25$ °C)

Symbol	Parameter	Test Conditions	V _{CC}	Min	Тур.	Max	Unit
			1.65V	0.70		1.20	
	Decitive mains inner		2.3V	1.11		1.60	
V_{T+}	Positive-going input threshold voltage		3V	1.50		2.00	
	tilleshold voltage		4.5V	2.16		2.74	
			5.5V	2.61		3.33	
			1.65V	0.30		0.75	
	Negative-going input		2.3V	0.58		1.03	
V_{T-}	threshold voltage		3V	0.80		1.33	
	linoonoid voitago		4.5V	1.21		1.95	
			5.5V	1.45		2.35	
			1.65V	0.30		0.62	
	Hysteresis		2.3V	0.37		0.80	
ΔV_{T}	(V _{T+} - V _{T-)}		3V	0.32		1.00	
	(*1+ *1-)		4.5V	0.50		1.20	
			5.5V	0.55		1.40	
		$I_{OH} = -100 \mu A$	1.65V to 5.5V	V _{CC} – 0.1			
		I _{OH} = -4mA	1.65V	0.95			
V_{OH}	High Level Output Voltage	I _{OH} = -8mA	2.3V	1.7			V
		I _{OH} = -16mA	0)/	1.9			
		I _{OH} = -24mA	3V	2.0			
		I _{OH} = -32mA	4.5V	3.4			
		I _{OL} = 100μA	1.65V to 5.5V			0.1	
		I _{OL} = 4mA	1.65V			0.7	
\ /		I _{OL} = 8mA	2.3V			0.45	
V_{OL}	High-level Input Voltage	I _{OL} = 16mA	0) /			0.6	V
		I _{OL} = 24mA	3V			0.8	
		I _{OL} = 32mA	4.5V			0.8	
I _I	Input Current	$V_I = 5.5V$ or GND	0 to 5.5V			± 100	μA
I _{OFF}	Power Down Leakage Current	V_I or $V_O = 5.5V$	0			± 200	μΑ
I _{CC}	Supply Current	$V_I = 5.5V$ of GND $I_O=0$	1.65V to 5.5V			200	μA
Δl _{CC}	Additional Supply Current	Input at V _{CC} –0.6V	3V to 5.5V			5000	μA



Package Characteristics (All typical values are at Vcc = 3.3V, T_A = 25°C)

Symbol	Parameter	Test Conditions	V _{CC}	Min	Тур.	Max	Unit
CI	Input Capacitance	$V_I = V_{CC} - \text{or GND}$	3.3		3.5		рF
		SOT25			204		
	Thermal Resistance	SOT353	(1)		371		0000
θ_{JA}	Junction-to-Ambient	DFN1410	(Note 4)		430		°C/W
		DFN1010			510		
		SOT25			52		
	Thermal Resistance	SOT353	(1)		143		0000
θ_{JC}	Junction-to-Case	DFN1410	(Note 4)		190		°C/W
		DFN1010			250		

Notes: 4. Test condition for SOT26, SOT363, DFN1410 and DFN1010 : Device mounted on FR-4 substrate PC board, 2oz copper, with minimum recommended pad layout.

Switching Characteristics

 $T_A = -40$ °C to 85°C, $C_L = 15$ pF as noted (see Figure 1)

Parameter	From (Input)	TO (OUTPUT)	V _{CC} = 1.8V ± 0.15V		V _{CC} = 2.5V ± 0.2V		V _{CC} = 3.3V ± 0.3V		V _{CC} = 5V ± 0.5V		Unit
		(iliput) (OOTFOT)	Min	Max	Min	Max	Min	Max	Min	Max	
t _{pd}	A	Y	1.0	9.9	0.7	5.5	0.7	4.6	0.7	4.4	ns

$T_A = -40$ °C to 85°C, $C_L = 30$ or 50pF as noted (see Figure 2)

Parameter	neter From TO ± 0.15			V _{CC} = 2.5V ± 0.2V		V _{CC} = 3.3V ± 0.3V		V _{CC} = 5V ± 0.5V		Unit	
	(input)	input) (OOTPOT)	Min	Max	Min	Max	Min	Max	Min	Max	
t _{pd}	A	Y	1.0	11	0.7	6.5	0.7	5.5	0.7	5	ns

$T_A = -40$ °C to 125°C, $C_L = 15$ pF as noted (see Figure 1)

Parameter	From (Input)	TO (OUTPUT)		: 1.8V .15V	V _{CC} = ± 0	: 2.5V .2V	V _{CC} = ± 0	: 3.3V .3V		= 5V .5V	Unit
	(input)	input) (OOTPOT)	Min	Max	Min	Max	Min	Max	Min	Max	
t _{pd}	Α	Υ	1.0	12.5	0.7	7.5	0.7	6.5	0.7	5.5	ns

$T_A = -40$ °C to 125°C, $C_L = 30$ or 50pF as noted (see Figure 2)

	Parameter	From (Input)		V _{CC} = ± 0.	: 1.8V .15V	V _{CC} = ± 0	: 2.5V .2V	V _{CC} = 3.3V ± 0.3V			= 5V 0.5V	Unit
				Min	Max	Min	Max	Min	Max	Min	Max	
	t _{pd}	A	Y	1.0	14.0	0.7	8.5	0.7	7.0	0.7	6.5	ns




Operating Characteristics


 $T_A = 25$ °C


	Parameter Test Conditions		V _{CC} = 1.8V Typ.	V _{CC} = 2.5V Typ.	V _{CC} = 3.3V Typ.	V _{CC} = 5V Typ.	Unit
C _{pd}	Power dissipation capacitance	f = 10 MHz	20	21	22	25	pF

Parameter Measurement Information



V _{CC}	Inputs		V _M	CL	RL
	VI	t _r /t _f	₹ IVI	OL.	IVL.
1.8V±0.15V	V _{CC}	≤2ns	V _{CC} /2	15pF	1ΜΩ
2.5V±0.2V	V _{CC}	≤2ns	V _{CC} /2	15pF	1ΜΩ
3.3V±0.3V	3V	≤2.5ns	1.5V	15pF	1ΜΩ
5V±0.5V	V _{CC}	≤2.5ns	V _{CC} /2	15pF	1ΜΩ





Voltage Waveform Propagation Delay Times Inverting and Non Inverting Outputs


Figure 1. Load Circuit and Voltage Waveforms

Notes: A. Includes test lead and test apparatus capacitance.


- B. All pulses are supplied at pulse repetition rate \leq 10 MHz.
- C. Inputs are measured separately one transition per measurement.
- D. t_{PLH} and t_{PHL} are the same as t_{PD.}




Parameter Measurement Information (cont.)



V _{CC}	Inputs		V	C	В
	VI	t _r /t _f	V _M	C _L	R _L
1.8V±0.15V	V _{CC}	≤2ns	V _{CC} /2	30pF	1ΚΩ
2.5V±0.2V	V _{CC}	≤2ns	V _{CC} /2	30pF	500Ω
3.3V±0.3V	3V	≤2.5ns	1.5V	50pF	500Ω
5V±0.5V	V _{CC}	≤2.5ns	V _{CC} /2	50pF	500Ω





Voltage Waveform Propagation Delay Times Inverting and Non Inverting Outputs

Figure 2. Load Circuit and Voltage Waveforms

Notes: A. Includes test lead and test apparatus capacitance.

- B. All pulses are supplied at pulse repetition rate ≤ 10 MHz.
- C. Inputs are measured separately one transition per measurement.
- D. t_{PLH} and t_{PHL} are the same as t_{PD}.

Packing

7: Tape & Reel



LVC: 1.65 to 5.5V

SINGLE SCHMITT-TRIGGER INVERETER

Ordering Information

74LVC1G 14 XXX - 7

Logic Device Function
74 : Logic Prefix 14 : 1-Input

14 : 1-Input Schmitt-Trigger Inverter

Family 1G : One gate Package W5 : SOT25

SE: SOT353 FW4: DFN1010 FZ4: DFN1410

7" Tape and Reel **Package Packaging Device** Code (Note 7) Quantity **Part Number Suffix** 74LVC1G14W5-7 W5 SOT25 3000/Tape & Reel -7 (B) (B) 74LVC1G14SE-7 SE **SOT353** 3000/Tape & Reel -7 74LVC1G14FW4-7 FW4 **DFN1010** 5000/Tape & Reel -7 -7 74LVC1G14FZ4-7 FZ4 **DFN1410** 5000/Tape & Reel

Notes: 5. Pad layout as shown on Diodes Inc. suggested pad layout document AP02001, which can be found on our website at http://www.diodes.com/datasheets/ap02001.pdf.

6. The taping orientation is located on our website at http://www.diodes.com/datasheets/ap02007.pdf



Marking Information

(1) SOT25, SOT353

(Top View)

2

 \underline{XX} : Identification Code

 $\overline{\underline{Y}}$: Year 0~9

 $\overline{\underline{W}}$: Week: A~Z: 1~26 week; a~z: 27~52 week;

z represents 52 and 53 week

X: A~Z: Internal Code

Part Number	Package	Identification Code
74LVC1G14W5-7	SOT25	UP
74LVC1G14SE-7	SOT353	UP

(2) DFN1010,DFN1410

(Top View)

<u>XX</u> Y <u>W</u> X XX: Identification Code

_____ <u>Y</u> : Year 0~9

 $\underline{\underline{W}}$: Week: A~Z: 1~26 week; a~z: 27~52 week; z represents 52 and 53 week


 \underline{X} : A~Z: Internal Code

Part Number	Package	Identification Code
74LVC1G14FW4-7	DFN1010	UP
74LVC1G14FZ4-7	DFN1410	UP




Package Outline Dimensions (All Dimensions in mm)

(1) Package Type: SOT25




(2) Package Type: SOT353






Package Outline Dimensions (cont.) (All Dimensions in mm)

(3) Package Type: DFN1010



(4) Package Type DFN1410





IMPORTANT NOTICE

DIODES INCORPORATED MAKES NO WARRANTY OF ANY KIND, EXPRESS OR IMPLIED, WITH REGARDS TO THIS DOCUMENT, INCLUDING, BUT NOT LIMITED TO, THE IMPLIED WARRANTIES OF MERCHANTABILITY AND FITNESS FOR A PARTICULAR PURPOSE (AND THEIR EQUIVALENTS UNDER THE LAWS OF ANY JURISDICTION).

Diodes Incorporated and its subsidiaries reserve the right to make modifications, enhancements, improvements, corrections or other changes without further notice to this document and any product described herein. Diodes Incorporated does not assume any liability arising out of the application or use of this document or any product described herein; neither does Diodes Incorporated convey any license under its patent or trademark rights, nor the rights of others. Any Customer or user of this document or products described herein in such applications shall assume all risks of such use and will agree to hold Diodes Incorporated and all the companies whose products are represented on Diodes Incorporated website, harmless against all damages.

Diodes Incorporated does not warrant or accept any liability whatsoever in respect of any products purchased through unauthorized sales channel.

Should Customers purchase or use Diodes Incorporated products for any unintended or unauthorized application, Customers shall indemnify and hold Diodes Incorporated and its representatives harmless against all claims, damages, expenses, and attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized application.

Products described herein may be covered by one or more United States, international or foreign patents pending. Product names and markings noted herein may also be covered by one or more United States, international or foreign trademarks.

LIFE SUPPORT

Diodes Incorporated products are specifically not authorized for use as critical components in life support devices or systems without the express written approval of the Chief Executive Officer of Diodes Incorporated. As used herein:

- A. Life support devices or systems are devices or systems which:
 - 1. are intended to implant into the body, or
 - 2. support or sustain life and whose failure to perform when properly used in accordance with instructions for use provided in the labeling can be reasonably expected to result in significant injury to the user.
- B. A critical component is any component in a life support device or system whose failure to perform can be reasonably expected to cause the failure of the life support device or to affect its safety or effectiveness.

Customers represent that they have all necessary expertise in the safety and regulatory ramifications of their life support devices or systems, and acknowledge and agree that they are solely responsible for all legal, regulatory and safety-related requirements concerning their products and any use of Diodes Incorporated products in such safety-critical, life support devices or systems, notwithstanding any devices- or systems-related information or support that may be provided by Diodes Incorporated. Further, Customers must fully indemnify Diodes Incorporated and its representatives against any damages arising out of the use of Diodes Incorporated products in such safety-critical, life support devices or systems.

Copyright © 2011, Diodes Incorporated

www.diodes.com