

CC1101-CC1190EMK Quick Start Guide

Opening the box and using the modules with SmartRF04EB

1. Kit Contents



2 x CC1101-CC1190EM 2 x Antennas Documentation

The picture above shows the 869 MHz version of the kit.

4a. Apply Power


The EB can be powered from different sources: USB, Battery or an External Power Supply

The voltage regulator on the EB supplies 3.3 V to the assembly, but it can only source up to 150 mA. It *cannot* supply the CC1101-CC1190EM since it can consume more than 300 mA. <u>An external power</u> supply is therefore required for powering the EM.

It is possible to have separate power sources for the EB and for the EM. This is controlled with the strap between I_OUT and I_IN on P5 (the screw terminal). Remove it to allow separate power supplies.



4d. Optional: Same Power Supply for both EB and EM



Connect a 3.3 V voltage source between the 3.3 V and 0 V terminals. 3.3 V is the middle terminal.

In this case, the on-board voltage regulator will be bypassed. Note that the strap on P5 should not be removed.

2. How to Use the Modules

The CC1101-CC1190 Evaluation Module (EM) boards can be plugged into the SmartRF04EB (EB), which is included in the CC11xxDK. This board lets you control the devices from SmartRF[™] Studio and it can also be used as a development platform.

This Quick Start Guide describes how to properly power an EB with a CC1101-CC1190EM and how to control the combo from SmartRF Studio.

3. Plug EM into SmartRF04EB



Insert the EM into the EB. The connectors will only fit in one position, so that the EM cannot be inserted the wrong way.

Handle the EM with care. Observe precautions for handling electrostatic sensitive devices.

4c. Power the EM



As noted in 4a, remove the strap on P5 and connect the external power supply as shown in the picture above. The red wire is the positive supply and the black wire is GND.

This will power the EM directly from the external power supply, whereas the rest of the EB will be powered from USB or the battery.

The power supply range should be within 3.0 to 3.6 V.

5. Set Power Switch



If EB and EM are powered from different sources as described in 4a-4c, the switch should be set to the rightmost position.

If EB and EM are powered from the same external supply as described in 4d, the switch should be set to the leftmost position.

This switch can be used to turn off the EB by switching it to the opposite position of that used to turn it on.

6. External Power Supply Range

With the test setup in 4a-4c, the EB is connected to a 3.3 V supply through the on-board voltage regulator and the EM is powered by the external supply. Since the EB is powered through a regulated 3.3 V supply the signals going from CC1101-CC1190 to the EB (and vice versa) need to be within 3.0 V to 3.6 V. The external supply connected to the EM when using the setup in 4a-4c is therefore limited to 3.0 V to 3.6 V.

With the setup in 4d the supply range is limited 2.7 V to 3.6 V.

4b. Power the EB



Connect the EB to a USB port on a PC.



Alternatively, connect a 9 V battery (not included in the kit) to the battery connector on the bottom side of the board.

Note that if multiple power sources are connected, the source with the highest voltage will power the EB. This means that you should disconnect any attached battery when using USB power; otherwise the battery will be drained.



SmartRF[™] Studio

1. Download and Install SmartRF Studio

Before connecting the EB to your PC, download SmartRF™ Studio from <u>www.ti.com/smartrfstudio</u>. Install the program and follow the instructions in the wizard.

Connect the EB with a CC1101-CC1190EM to the PC using the USB cable and install the USB driver as described in the manual.

2. Launch SmartRF Studio



Launch SmartRF Studio and double click on the highlighted CC1101 device icon to get complete control of the device from the PC.

You can now configure the radio, run tests, export register settings and run link tests with another CC1101-CC1190EM on a SmartRF04EB connected to the PC.

3. Configure the Radio

CC1101 - Device Control Panel (offline)		
e <u>S</u> ettings <u>V</u> iew <u>E</u> valuation Board <u>H</u> elp		
E Easy Mode Expert Mode Regis	ster View 🔽 RF Parameters 🛛	Register reset
Typical settings		
Data rate: 10 kBaud, Dev.: 19 kHz, Data rate: 38.4 kBaud, Dev.: 20 kHz, Data rate: 38.4 kBaud, Dev.: 20 kHz, Data rate: 38.4 kBaud, Dev.: 20 kHz, Data rate: 76.8 kBaud, Dev.: 32 kHz, Data rate: 76.8 kBaud, Dev.: 32 kHz, Data rate: 100 kBaud, Dev.: 47 kHz, Data rate: 100 kBaud, Dev.: 47 kHz, Data rate: 250 kBaud, Dev.: 127 kHz,	Mod.: GFSK, RX BW: 540 kHz, Opt	imized for sensitivity imized for current consumption imized for sensitivity imized for current consumption imized for sensitivity imized for current consumption imized for current consumption
Base frequency	Channel number	Channel spacing
869.524750 MHz	0 🗢	199.813843 kHz
Xtal frequency	Data rate	RX filter BW
27.000000 💌 MHz	38.4178 kBaud	105.468750 kHz
Modulation format	Deviation	TX power
GFSK	19.775391 kHz	18 💌 dBm
Range Extender CC1190 💽 🗹 High Gain Mode(RX)	EM Revisions CC1101-CC1190EM 868Mhz	v

In order to control the CC1190 select CC1190 as "Range Extender" and select the appropriate "EM Revisions" as shown. You can now use all the features in Studio as for a standalone EM. Test the performance of the radio using some of these features

- Continuous TX: Output power, spectrum
- Continuous RX: Received signal strength, synchronous/asynchronous serial RX mode
- Packet TX/RX: Link and sensitivity testing

References

Please visit

- www.ti.com
- http://focus.ti.com/docs/prod/folders/print/cc1190.html
- http://focus.ti.com/docs/toolsw/folders/print/cc1101emk868-915.html
- <u>http://www.ti.com/lit/swra356</u> (Using the CC1190 Front End with CC1101 under EN 300 220)
- http://www.ti.com/lit/swra361 (Using the CC1190 Front End with CC1101 under FCC 15.247)

Download the SmartRF™ Studio software, as well as datasheets, reference designs and application notes.

You will also find a lot of information on the TI E2E forum at http://e2e.ti.com

We hope you will enjoy working with the CC1101 and CC1190 devices.

IMPORTANT NOTICE

Texas Instruments Incorporated and its subsidiaries (TI) reserve the right to make corrections, modifications, enhancements, improvements, and other changes to its products and services at any time and to discontinue any product or service without notice. Customers should obtain the latest relevant information before placing orders and should verify that such information is current and complete. All products are sold subject to TI's terms and conditions of sale supplied at the time of order acknowledgment.

TI warrants performance of its hardware products to the specifications applicable at the time of sale in accordance with TI's standard warranty. Testing and other quality control techniques are used to the extent TI deems necessary to support this warranty. Except where mandated by government requirements, testing of all parameters of each product is not necessarily performed.

TI assumes no liability for applications assistance or customer product design. Customers are responsible for their products and applications using TI components. To minimize the risks associated with customer products and applications, customers should provide adequate design and operating safeguards.

TI does not warrant or represent that any license, either express or implied, is granted under any TI patent right, copyright, mask work right, or other TI intellectual property right relating to any combination, machine, or process in which TI products or services are used. Information published by TI regarding third-party products or services does not constitute a license from TI to use such products or services or a warranty or endorsement thereof. Use of such information may require a license from a third party under the patents or other intellectual property of the third party, or a license from TI under the patents or other intellectual property of TI.

Reproduction of TI information in TI data books or data sheets is permissible only if reproduction is without alteration and is accompanied by all associated warranties, conditions, limitations, and notices. Reproduction of this information with alteration is an unfair and deceptive business practice. TI is not responsible or liable for such altered documentation. Information of third parties may be subject to additional restrictions.

Resale of TI products or services with statements different from or beyond the parameters stated by TI for that product or service voids all express and any implied warranties for the associated TI product or service and is an unfair and deceptive business practice. TI is not responsible or liable for any such statements.

TI products are not authorized for use in safety-critical applications (such as life support) where a failure of the TI product would reasonably be expected to cause severe personal injury or death, unless officers of the parties have executed an agreement specifically governing such use. Buyers represent that they have all necessary expertise in the safety and regulatory ramifications of their applications, and acknowledge and agree that they are solely responsible for all legal, regulatory and safety-related requirements concerning their products and any use of TI products in such safety-critical applications, notwithstanding any applications-related information or support that may be provided by TI. Further, Buyers must fully indemnify TI and its representatives against any damages arising out of the use of TI products in such safety-critical applications.

TI products are neither designed nor intended for use in military/aerospace applications or environments unless the TI products are specifically designated by TI as military-grade or "enhanced plastic." Only products designated by TI as military-grade meet military specifications. Buyers acknowledge and agree that any such use of TI products which TI has not designated as military-grade is solely at the Buyer's risk, and that they are solely responsible for compliance with all legal and regulatory requirements in connection with such use.

TI products are neither designed nor intended for use in automotive applications or environments unless the specific TI products are designated by TI as compliant with ISO/TS 16949 requirements. Buyers acknowledge and agree that, if they use any non-designated products in automotive applications, TI will not be responsible for any failure to meet such requirements.

Following are URLs where you can obtain information on other Texas Instruments products and application solutions:

Products		Applications	
Audio	www.ti.com/audio	Communications and Telecom	www.ti.com/communications
Amplifiers	amplifier.ti.com	Computers and Peripherals	www.ti.com/computers
Data Converters	dataconverter.ti.com	Consumer Electronics	www.ti.com/consumer-apps
DLP® Products	www.dlp.com	Energy and Lighting	www.ti.com/energy
DSP	dsp.ti.com	Industrial	www.ti.com/industrial
Clocks and Timers	www.ti.com/clocks	Medical	www.ti.com/medical
Interface	interface.ti.com	Security	www.ti.com/security
Logic	logic.ti.com	Space, Avionics and Defense	www.ti.com/space-avionics-defense
Power Mgmt	power.ti.com	Transportation and Automotive	www.ti.com/automotive
Microcontrollers	microcontroller.ti.com	Video and Imaging	www.ti.com/video
RFID	www.ti-rfid.com	Wireless	www.ti.com/wireless-apps
RF/IF and ZigBee® Solutions	www.ti.com/lprf		

TI E2E Community Home Page

e2e.ti.com

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265 Copyright © 2011, Texas Instruments Incorporated