400 MICRO-TECH® TOOLS

WITH DEDICATED FEATURES

- to optimize gripping, cutting or handling small components.
- Efficient storage for instant selection of the correct tool.
- Antistatic tools providing electrostatic discharge protection (ESD).



ACCORDING TO CUT The Facom range offers three types. Choose the one best suited to your needs.

CUTTING EDGES	ILLUSTRATION	FEATURES	WIRE	TYPE	OPERATION	APPLICATION
			Си	YES		
		Cutting edges are treated to achieve maximum	Cu-Ni alloy	YES	- Production work.	Customer service (hi-fi)
AXIAL CUT		strength and precision cutting of a wide range of materials,	Mild steel 30 HRc	YES	- Day-to-day use.	Machine-tools Automotive
		from piano wire to copper.	Hard steel 50 HRc	YES	- Hard materials.	Domestic appliances
			Piano wire			
SEMI-FLUSH CUT		Micro-chamfered cutting edges ensure high cutting capacity with clean finish. Precision is maintained throughout a long service life even in intensive use. Suitable for semi-hard wire.	Си	YES	– Clean cut	Computers Telephone exchanges Video and laser Micro-engineering (hi-fi, labs)
			Cu-Ni alloy	YES	 – Wiring. – Batch electronics. – Semi-hard materials. 	
			Mild steel 30 HRc	YES		
			Hard steel 50 HRc	NO		
			Piano wire			
			Си	YES	– High-frequency apparatus.	Defence Aerospace Aviation Laboratory
FLUSH CUT		This range is designed to give a through-cut without crushing the wire. Clean-cut ends allow reliable soldering, without damage to electronic components from arcing. Suitable for soft wire only.	Cu-Ni alloy	YES	Maximum precision equipment. Cut-back before soldering.	
			Mild steel 30 HRc	NO		
			Hard steel 50 HRc	NO	- Electrostatically sensitive	
			Piano wire		components.	







■ ACCORDING TO PROFILE*

	Г	~		
NOSE DESIGN	₹0	Ø Cu wire (mm) 0 0,5 1 1,5 2	Ø max Fe wire 30 HRc	Ø max piano wire
		1 7 6 7 7 7	TO WITC SO TIME	pidno wire
Bullet nose for strength	405.8 MT-C-E 405.MT-C-E 405.10 MT-C-E 405.12MT-C-E 405.RMT-C-E	$0.2 \longrightarrow 1$ $0.3 \longrightarrow 1.3$ $0.3 \longrightarrow 1.4$ $0.4 \longrightarrow 2.0$ $0.3 \longrightarrow 1.1$	0,5 0,7 0,8 1,0 0,7	0,4 0,5 0,8 0,4
	405.10 RMT-RC-RE	0,3 -> 1,2	0,8	0,5
• End nose for reach	405.12 RMT-RC-RE* 408.MT	0,4 — > 1,5 0,4 — > 1,5	0,5	0,6
Bullet nose for strength	406.8-MT-C-E 406.MT-C-E 435.MT-C-E 436.MT-E 415.MT-C-E 406.RMT-RC-RE* 435.RMT-RC-RE*	0,1 -> 1 $0,1 -> 1,3$ $0,1 -> 1,3$ $0,1 -> 1,2$ $0,3 -> 2,0$ $0,1 -> 1,1$ $0,1 -> 1,1$ $0,3 -> 1,5$	0,7 0,7 0,7 1,0 0,7 0,7	STOP
Pointed nose for control	416.MT-C-E 416.PMT-C-E 416.12 MT-C-E 416.RMT-RC*	0.1 -> 1.0 $0.1 -> 0.8$ $0.3 -> 1.6$ $0.1 -> 0.9$	0,5 0,4 0,7 0,5	
Bullet nose for strength	407.8 MT-C-E 407.MT-C-E 425.MT-C-E 426.MT-E	0.1 -> 0.8 $0.1 -> 1.3$ $0.1 -> 1.3$ $0.1 -> 1.3$		
Pointed nose for control	417.PMT-C-E	0,1> 0,8	STOP	STOP
• Angled nose for accuracy	427.MT-C-E 429.MT-C-E 430.MT	0,2->0,6 0,2 > 1,0 0,2 > 1,0		
• End nose for reach	418.MT 428.MT	0,1->0,6 0,1->0,8		









































MICRO-TECH® ELECTRONICS PLIERS

>>> DIAGONAL CUTTERS WITH BULLET NOSE FOR STRENGTH



The bullet nose offers greater resilience compared with other profiles. The increased cutting capacity and long service life is useful in a wide variety of applications.



AXIAL CUT
All materials,
any application.



SEMI-FLUSH CUT Clean, long-life cut in semi-hard materials.



FLUSH CUT Smooth cut for sound soldered connections.


■ Slim-joint models for precision


D ISO 9654

• Suitable for miniature electronic components. $\Delta\!\!\!/ \Delta$ 60g.

3 0	Cut	Cu-Ni wire	Piano wire	Fe wire 30 HRc
		Ø mm	Ømm	Ø mm
405.8MT	\wedge	0,2 - 1	•	0,5
406.8MT		0,1 - 1		
407.8MT		0.1 - 1	(m)	








■ Compact models for manoeuvrability


- Slimmer bullet-nose profile combines cutting performance with manoeuvrability.
- Available with offcut retaining system. Models 405.MT and 405.RMT are suitable for cutting piano wire Ø 0,4 mm.

 Δ\u03c4 60g.



= 0	Cut	Cu-Ni wire Ø mm	Fe wire 30 HRc Ø mm	Piano wire Ø mm	Offcut retainer
405.MT	\wedge	0,3 - 1,3	0,7	0,4	
405.RMT	\wedge	0,3 - 1,1	0,6	0,4	•
406.MT		0,1 - 1,3	0,7	600	
406.RMT		0,1 - 1,1	0,6		•
407.MT		0.1 - 1.3	100	─	





■ Stocky models for versatility


> ISO 9654


- \bullet Clean cut in a variety of materials from copper to piano wire up to Ø 0,5 mm.
- Available with offcut retaining system.
 △△ 60g.

38	PART PROPERTY					
N. Co.	•					



= 0	Cut	Cu-Ni wire Ø mm	Fe wire 30 HRc Ø mm	Piano wire	Offcut retainer
405.10MT	$\overline{}$	0,3 - 1,4	0,8	0,5	
405 10RMT	\wedge	03.12	0.7	0.5	•





■ Long-reach models for accessibility

D ISO 9654

- Up to 1,5 to 2 mm more reach than standard cutting pliers.
- Available with offcut retaining system. ∆™∆ 60g.

= 0	Cut	Cu-Ni wire Ø mm	Fe wire 30 HRc Ø mm	Offcut retainer
435.MT		0,1 - 1,3	0,7	
435.RMT		0,1 - 1,1	0,7	•
425.MT		0.1 - 1.3	(512P)	



















■ Slim-nose model with back clearance

D ISO 9654


• For cutting behind components and reaching under obstacles such as coil or resistor. ∆1∆ 60g.
















■ Heavy-duty models for power


D ISO 9654

- For tough applications and repetitive work on a wide range of materials.
- Piano wire: 405.12MT up to 0,8 mm; 405.12RMT up to 0,6 mm.
- Available with offcut retaining system. ∆™ 95g.





₹ 0	Cut	Cu-Ni wire	Fe wire 30 HRc	Piano	Offcut
		Ø mm	Ømm	wire	retainer
405.12MT	\wedge	0,4 - 2,0	1,0	0,8	
405.12RMT	\wedge	0,4 -1,5	0,9	0,6	•
415.MT		0,3 - 2,0	0,9		
415.RMT		0,3 - 1,5	0,8		•











The pointed nose is ideal where clearance is restricted and allows better visibility of the wire being cut.



SEMI-FLUSH CUT
Clean, long-life Sr
cut in semi-hard materials. so



FLUSH CUT Smooth cut for sound soldered connections.


■ Pointed models


D ISO 9654

- Taper nose for improved accessibility.
- Available with offcut retaining system. $\Delta\Delta$ 60g.

五	Cut	Cu-Ni wire Ø mm	Fe wire 30 HRc Ø mm	Offcut retainer
416.MT		0,1 - 1,0	0,5	
416.RMT		0.1 - 0.9	0,5	•







Pointed slim-nose models for manoeuvrability


⊳ ISO 9654

 \bullet Slots in and around printed-circuit components, allowing good visibility. $\Delta T\!\Delta$ 60g.

3 0	Cut	Cu-Ni wire Ø mm	Fe wire 30 HRc Ø mm	Offcut retainer
416.PMT		0,1 - 0,8	0,4	
417.PMT		0,1 - 0,8		







■ 416.12MT


Heavy-duty taper nose

D ISO 9654

- Suitably sized for production applications.
- Semi-flush cut.
- Cu-Ni wire Ø 0,3 to 1,6 mm.
- Fe wire 30 HRc up to Ø 0,7 mm.

∆1∆ 95g.









F101

ANGLED-NOSE CUTTING PLIERS FOR PRECISION



- Ideal for use on printed circuits, electronic modules and hybrid circuits.
- Designed for cutting right up against the board in the minutest spaces.
- Flush cutting edges.



FLUSH CUT Smooth cut for clean soldered connections.




































FACOM



30° cutters

- Cutting edges at 30° with back clearance.
- Flush cut.
- Cu-Ni wire Ø 0,2 to 0,6 mm.
- le wire 30 HRc.

∆1∆ 65g.



■ 429.MT

70° cutters

D ISO 9654

- Wide edges at 70° with large back clearance.
- Cu-Ni wire Ø 0,2 to 1,0 mm.
- Fe wire 30 HRc.

∆1∆ 60g.



■ 430.MT


70° narrow cutters


D ISO 9654

- Narrow edges at 70° with back clearance.
- Flush cut.
- \bullet Cu-Ni wire \varnothing 0,2 to 1,0 mm.
- Fe wire 30 HRc.

∆1∆ 60g.













- End cutting edges allow vertical access.
- Extended profile reaches wires or components on crowded boards.



AXIAL CUT
All materials,
any application.



FLUSH CUT Smooth cut for sound soldered connections.

■ 418.MT


End cutters


D ISO 9654

- Long, narrow nose for vertical access.
- Flush cut.
- \bullet Cu-Ni wire Ø 0,1 to 0,6 mm.
- @ Fe wire 30 HRc.

∆1∆ 75g.









■ 428.MT


End cutters with adjustable stop


⊳ ISO 9654

- Similar to 418 but with 0 to 4 mm adjustment for precision cut at set distance from board.
- Flush cut.
- Cu-Ni wire Ø 0,1 to 0,6 mm.
- Fe wire 30 HRc.

∆™ 75g.









■ 408.MT


Heavy-duty end cutters


D ISO 9654

- Long nose for vertical access.
- Axial cut.
- \bullet Cu-Ni wire Ø 0,4 to 1,5 mm.
- \bullet Fe wire 30 HRc Ø up to 0,5 mm. $\Delta \Delta = 100 \, \mathrm{g}$.













- Ideal for use on printed circuits, electronic modules and hybrid circuits.
- Designed for cutting right up against the board in very tight spaces.
- Flush cutting edges.















































FACOM

■ 417.SPMT

Diagonal cutters for DIP-SMD components

- Designed to slot in the 0,65 mm gap between lugs of DIP components. The slender nose of this tool precludes its use for other purposes.
- Flush cut.
- Cu-Ni wire Ø 0,1 to 0,6 mm. ∆™∆ 60g.






■ 437.MT

Diagonal cutters for DIP components

- Pointed, slim nose allows full access to DIP or SMD components.
- Flush cut.
- Cu-Ni wire Ø 0,1 to 0,6 mm. ∆™ 40g.







■ 419.MT

Inverted 45° cutters

- Designed to reach DIP pins from behind on crowded boards.
- Flush cut.
- Cu-Ni wire Ø 0,1 to 0,5 mm. ∆™ 50g.






434.MT

45° cutters

- Cutting pliers angled at 45°.
- Nose aligning pin.
- Flush cut.
- \bullet Cu-Ni wire \varnothing 0,1 to 0,3 mm. ∆™ 40g.











- These pliers serve all professional needs in laboratory, production and maintenance applications.
- Smooth, rectangular-section jaws with contoured inside edges to protect components.
- Matt black non-reflective finish. Leaf spring.

■ 401.MT

Extended-nose pliers

⊳ ISO 9655

• For extra power. $\Delta \Delta 80g$.



■ 421.MT

Rigid long-nose pliers

⊳ ISO 9655
△□ 70g.



■ 420.MT

Shaping pliers

D ISO 9655

• Very slim nose. △□ 60g.



431.MT

Short-nose pliers

D ISO 9655

• Slim joint for precision work. $\Delta \Delta 55g$.



■ 431.LMT

Snipe-nose pliers

D ISO 9655

• Slim joint for precision work. △△ 80g.



■ 443.12MT

Mini combination pliers

- Side wire-cutter, capacity up to \varnothing 1,7 mm in Cu, \varnothing 1 mm in mild steel.
- Stocky serrated nose, with tube-grip.
- Matt black anti-glare finish. △□ 80g.







- These pliers serve all professional needs in laboratory, production and maintenance applications.
- Smooth, half-round jaws with contoured inside edges to protect components.
- Matt black non-reflective finish. Leaf spring.









"Telephone" pliers

D ISO 9655

- Long stocky nose with fine end serrations.
- Side cutter.
- Cu wire max. Ø 2 mm.
- Fe wire 30 HRc max. Ø 1 mm. ∆1∆ 88g.







■ 402.MT

Extended-nose pliers

D ISO 9655

• For extra power. ∆1∆ 76g.







Rigid long-nose pliers

D ISO 9655 ∆1∆ 70g.







■ 432.MT

Short-nose pliers

⊳ ISO 9655

• Slim joint. △□ 55g.









Snipe-nose pliers

D ISO 9655

• Slim joint for precision work. ∆™ 65g.











Extended-nose 40° pliers

D ISO 9655

• For extra power. △□△ 75g.








■ 423.MT

Rigid-nose 60° pliers

⊳ ISO 9655 ∆™ 70g.






■ 433.LMT

Thin-nose 45° pliers

D ISO 9655

• Slim joint for precision work. $\Delta \Delta 5g$.





>>> ROUND-NOSE GRIPPING PLIERS




- These pliers serve all professional needs in laboratory, production and maintenance applications.
- Smooth and very slim round jaws, excellent for handling small wiring.
- Ideal for curling and shaping wire.

■ 404.MT

Stocky pointed-nose pliers

D ISO 9655

• Powerful forming tool ideal for loops. △△ 63g.





■ 424.MT

Rigid short-nose pliers

► ISO 9655△□ 55g.



