

High Value Surface Mounted Resistors

HR Series

- Custom designs / sizes available
- Resistance range to 50G ohms
- Terminations available for wire bonding or soldering
- Low voltage coefficient of resistance



Electrical Data

Power Rating

The high resistance value of these devices is such that power dissipation is always small. The rating is therefore determined by voltage considerations only, as shown in the table below.

		0503	0805	1005	1206	Notes
Resistance range*	ohms	10M to 20G	100M to 50G			Measured at 10 volts
Limiting element voltage	volts	50	100	150	200	
Ambient temperature range	°C	-55 to + 155				
TCR	ppm/°C	0 to -2500	0 to -2000	0 to -1500	0 to -1000	Measured at 10 volts
Resistance tolerance	%	10M to 500M:10 >500M : 25, 50	100M to 1G:5,10 > 1G to 50G:25, 50			

*Higher values available, consult factory for details

Physical Data

Dimensions (mm) & Weight (g)							
Style	L	W	T max.	Wrap around		Planar	Wt
				A	B [†]	C	
0503	1.25 ± 0.2	0.63 ± 0.15	0.5	Not available		0.2 ± 0.1	0.005
0805	2.0 ± 0.3	1.25 ± 0.2	0.6	0.3 ± 0.15	0.9min	0.3 ± 0.1	0.009
1005	2.5 ± 0.3	1.25 ± 0.2	0.7	Not available		0.4 ± 0.15	0.015
1206	3.2 ± 0.4	1.6 ± 0.2	0.7	0.4 ± 0.2	1.7min	0.4 ± 0.15	0.020

[†]This dimension determines the number of conductors which may pass under the surface mounted device.

Construction

The resistor material is screen printed onto a 96% alumina substrate and covered with a protection comprising of a glaze followed by an organic coating. This construction gives an insulated device.

Marking

All relevant information is recorded on the primary package or reel.

Terminations

Planar (or single-sided) termination is gold and suitable for wire-bonding; wrap around is suitable for soldering.

Solderability

Wrap-around terminations on HR resistors have good 'leach' resistance properties. They will withstand immersion in solder at 260°C for 30 seconds.

General Note

TT electronics reserves the right to make changes in product specification without notice or liability. All information is subject to TT electronics' own data and is considered accurate at time of going to print.

Performance Data

		Maximum	Typical
Load at rated power: 1000 hours at 70°C	ΔR%	2	1
Overload	ΔR%	1	0.2
Shelf life: 12 months at room temperature	ΔR%	2	1
Temperature rapid change	ΔR%	1	0.3
Change on Wave Soldering	ΔR%	1	0.5
Voltage proof	volts	0503 : 100	0805 to 1206 : 500
Voltage coefficient of resistance (10V - 25V)	%/V		
	0805	1	0.4
	1005	0.8	0.3
	1206	0.2	0.05

Application Notes

Mounting

This chip resistor is ideally suited for handling by automatic methods due to its rectangular shape and the small dimensional tolerances. Electrical connection to a ceramic substrate or to a printed circuit board can be made by wire bonding to planar terminations or by reflow soldering of wrap-around terminations. The 'F' terminations provide good leach properties and ensure reliable contact. Due to the robust construction the resistor chip can be immersed in the solder bath for 30 seconds at 260°C. This enables the resistor to be mounted on one side of a printed circuit and wire-leaded components on the other side. The resistor must be kept dry during use to avoid leakage. The presence of moisture will not damage the resistor in any way.

Packaging

Resistor chips are supplied taped and reeled on standard 8mm tape to IEC 286-3. Quantity per reel 3000 max.

Planar Terminations

Resistor chips are supplied in waffle packs.

Ordering Procedure

Example: HR1206 with solderable wraparound terminations at 10 gigohms and 50% tolerance on a reel of up to 3000 pieces -

HR 1206 F - 10 G Y I

Type _____

Size _____

Termination _____

F	Solderable wraparound	0805, 1206 only
G	Gold pad planar	All sizes

Value (use IEC62 code) _____

Tolerance (use IEC62 code) _____

J	5%	5	25%
K	10%	Y	50%

Packing _____

I	Tape	0805F, 1206F	Up to 3000/reel	Standard
	Waffle	G Termination		

General Note

TT electronics reserves the right to make changes in product specification without notice or liability. All information is subject to TT electronics' own data and is considered accurate at time of going to print.