

Microsoft® Wired Desktop 600



Technical Data Sheet

Version Information	
Product Name	Microsoft® Wired Desktop 600
Product Version	Microsoft Wired Desktop 600
Keyboard Version	Microsoft Wired Keyboard 600
Mouse Version	Microsoft Basic Optical Mouse v2.0
Product Dimensions	
Keyboard Length	17.9 inches (456 millimeters)
Keyboard Width	6.28 inches (160 millimeters)
Keyboard Depth/Height	1.68 inches (42.7 millimeters) with tilt legs extended
Keyboard Weight	20.1 ounces (595 grams)
Keyboard Cable Length	78.7 inches (2000 millimeters)
Mouse Length	4.47 inches (113 millimeters)
Mouse Width	2.28 inches (57.9 millimeters)
Mouse Depth/Height	1.54 inches (39.2 millimeters)
Mouse Weight	3.27 ounces (92.8 grams)
Mouse Cable Length	72 +6/-0 inches (1830 +150/-0 millimeters)
Compatibility and Localization	
Interface	<ul style="list-style-type: none"> • Keyboard: USB compatible • Mouse: USB compatible
Operating Systems	<ul style="list-style-type: none"> • Microsoft Windows® 7, Windows Vista®, and Windows XP (excluding Windows XP 64-bit) • Macintosh Mac OS X v10.2-10.4
Top-line System Requirements	<p>For a Microsoft Windows-based PC: Requires a PC that meets the requirements for and has installed one of these operating systems:</p> <ul style="list-style-type: none"> • Windows 7, Windows Vista, or Windows XP (excluding Windows XP 64-bit) • 60 MB of available hard disk space (Install 100 MB free) • USB port • CD Drive <p>For a Macintosh PC:</p> <ul style="list-style-type: none"> • Macintosh Mac OS X v10.2-10.4 • 30 MB of available hard disk space (Install 30 MB free) • CD Drive • USB port
Compatibility Logos	<ul style="list-style-type: none"> • Compatible with Microsoft Windows 7 • Certified for Microsoft Windows Vista • Mac logo • Certified USB logo
Software Localization	No software required
Keyboard Localization	<p>Available language sets will vary by product and sales channel.</p> <p>104 key configuration: Arabic, Chinese (Simplified), Chinese (Traditional), English (Canada), English (North America), Greek, International English (EURO), International English (ROW), and Russian</p> <p>105 key configuration: English (UK), French (Canada), French (France), German (Germany), Hungarian, Polish/Romanian, Spanish (Latin America), and Turkish</p> <p>106 key configuration: Korean</p> <p>107 key configuration: Brazilian (Portuguese)</p> <p>109 key configuration: Japanese</p>
Tracking Technology	
Mouse Tracking System	Optical tracking system
Imaging Rate	Up to 3000 frames per second
X-Y Resolution	800 points per inch (31.5 points per millimeter)
Tracking Speed	Up to 20 inches (508 millimeters) per second
Product Feature Performance	
QWERTY Key Life	20,000,000 actuations per key
Multimedia Key Features	Play/Pause, Volume +, Volume -, Mute, and Calculator
Multimedia Key Life	30,000 actuations per key
Typing Speed	1000 characters per minute
Mouse Button Features	3 buttons including scroll wheel button
Right & Left Button Life	3,000,000 actuations
Wheel Button Life	250,000 actuations
Mouse Scrolling Features	Standard vertical scroll wheel
Wheel Vertical Scrolling Life	<ul style="list-style-type: none"> • 100,000 revolutions (away from user) at no more than 60 rotations per minute • 300,000 revolutions (toward user) at no more than 60 rotations per minute
Storage Temperature & Humidity	-40°F (-40°C) to 140°F (60°C) at 5% to 65% relative humidity (non-condensing)
Operating Temperature & Humidity	32°F (0°C) to 104°F (40°C) at 5% to 80% relative humidity (non-condensing)
Certification Information	
Country of Manufacture	People's Republic of China (PRC)
ISO 9001 Qualified Manufacturer	Yes
ISO 14001 Qualified Manufacturer	Yes
Restriction on Hazardous Substances	This device complies with all applicable worldwide regulations and restrictions including, but not limited to: EU directive 2002/95/EC on the Restriction of the Use of Certain Hazardous Substances in Electrical and Electronic Equipment and EU Registration Evaluation and Authorization of Chemicals (REACH) regulation regarding Substances of Very High Concern.
FCC ID	This device complies with part 15 of the FCC Rules and Industry Canada ICES-003. Operation is subject to the following two conditions: (1) This device may not cause harmful interference, and (2) this device must accept any interference received, including interference that may cause undesired operation. Tested to comply with FCC standards. For home and office use. Model numbers: 1366, Wired Keyboard 600 and 1113, Basic Optical Mouse v2.0.

Certification Information	
Agency and Regulatory Marks	<ul style="list-style-type: none"> • ACAMED Declaration of Conformity (Australia and New Zealand) • ICES-003 report on file (Canada) • EIP Pollution Control Mark, EPUP (China) • CE Declaration of Conformity, Safety and EMC (European Union) • WEEE (European Union) • VCCI Certificate (Japan) • KCC Certificate (Korea) • GOST Certificate (Russia) • CITC Letter (Kingdom of Saudi Arabia) • BSMI Certificate (Taiwan) • FCC Declaration of Conformity (USA) • UL and cUL Notice of Approval (USA and Canada) • CB Scheme Certificate (International)
Windows Hardware Quality Labs (WHQL)	ID: Keyboard 1506548 Microsoft Windows 8 ID: Mouse 1329047 Microsoft Windows 7