

Beacons with Sounder Multi-Status LED 108 Series

Edwards 108 Series Chameleon™ LED multi-status indicator is a UL listed and IP65 rated multicolor device designed to function as either a steady-on or flashing visual signal. The 108 Series contains three different colored LED signals in one housing, with the option to add an additional lens module and light source – Strobe, Halogen, Incandescent or LED – for a fourth signal. It features a corrosion resistant Type 3R or 4X enclosure, and can be panel or conduit mounted.

The 108 Series features a multi-tone base module with eight available tones that can be operated as an additional signal or used in conjunction with any of the visual signals.

Features and Specifications

- 3 LED visual signals in one compact housing
- Option to add an additional module for a fourth light using one of the 102LM lens modules and the 102LS light sources
- 89dB at 1m / 79dB at 10ft
- Option to add multi-tone base module
- Suitable for indoor and outdoor applications
- NEMA Type 3R and Type 4X, IP65 rated
Option for panel or conduit mounting



← 3" →




Ordering Information

Description	Cat. No.	Operating Voltage ¹	Current	Lens Color	LED Colors
Pipe Mount (w/ tone module)	108I-RGA-N5	120V AC	0.115 A ²	Clear	Red, Green, Amber
	108I-RBA-N5	120V AC	0.115 A ²	Clear	Red, Blue, Amber
	108I-RGA-G1	24V DC	0.105 A ²	Clear	Red, Green, Amber
	108I-RBA-G1	24V DC	0.105 A ²	Clear	Red, Blue, Amber
Pipe Mount (short base)	108IP-RGA-N5	120V AC	0.045 A	Clear	Red, Green, Amber
	108IP-RBA-N5	120V AC	0.045 A	Clear	Red, Blue, Amber
	108IP-RGA-G1	24V DC	0.055 A	Clear	Red, Green, Amber
	108IP-RBA-G1	24V DC	0.055 A	Clear	Red, Blue, Amber
Direct Mount	108ID-RGA-N5	120V AC	0.045 A	Clear	Red, Green, Amber
	108ID-RBA-N5	120V AC	0.045 A	Clear	Red, Blue, Amber
	108ID-RGA-G1	24V DC	0.055 A	Clear	Red, Green, Amber
	108ID-RBA-G1	24V DC	0.055 A	Clear	Red, Blue, Amber

¹AC voltage frequency is 50/60 Hz.

²Includes tone module.



Beacons with Sounder

Multi-Status LED

108 Series

Ordering Information										
Description	Cat. No.	Operating Voltage	Current	Lens/LED Colors	Peak Candela	Lamp Ratings	Lamp Life Calculated ²	Lamp Life Projected ³	Replacement Lamp	
Lens Module	102LM-A	—	—	Amber	—	—	—	—	—	
	102LM-B	—	—	Blue	—	—	—	—	—	
	102LM-C	—	—	Clear	—	—	—	—	—	
	102LM-G	—	—	Green	—	—	—	—	—	
	102LM-R	—	—	Red	—	—	—	—	—	
	102LM-Y	—	—	Yellow	—	—	—	—	—	
Steady-on Halogen	102LS-SINH-N5	120V AC	0.11 A	—	879	12 Watts	20,000 hr.	—	50LMP-12WH	
	102LS-SINH-G1	24V DC	0.32 A	—	653	9 Watts	12,000 hr.	—	50LMP-9WH	
Steady-on Incandescent	102LS-SIN-N5	120V AC	0.08 A	—	829	10 Watts	2,500 hr.	—	50LMP-10W	
	102LS-SIN-G1	24V DC	0.32 A	—	829	10 Watts	10,000 hr.	—	Ind. Trade 303 ⁵	
Flashing Halogen	102LS-FINH-N5	120V AC	0.11 A	—	879	12 Watts	20,000 hr.	25,000 hr.	50LMP-12WH	
	102LS-FINH-G1	24V DC	0.32 A	—	653	9 Watts	12,000 hr.	15,000 hr.	50LMP-9WH	
Flashing Incandescent	102LS-FIN-N5	120V AC	0.08 A	—	829	10 Watts	2,500 hr.	3,000 hr.	50LMP-10W	
	102LS-FIN-G1	24V DC	0.32 A	—	829	10 Watts	10,000 hr.	12,500 hr.	Ind. Trade 303 ⁵	
Strobe	102LS-ST-N5	120V AC	0.12 A	—	300,000	3 Joule	3,000 hr. ⁴	—	—	
	102LS-ST-G1	24V DC	0.30 A	—	300,000	3 Joule	3,000 hr. ⁴	—	—	
Steady-on LED	102LS-SLEDA-N5 ¹	120V AC	0.022 A	Amber	—	—	120,000 hr.	—	—	
	102LS-SLEDA-G1 ¹	24V DC	0.062 A							
	102LS-SLEDB-N5 ¹	120V AC	0.022 A	Blue	—	—	120,000 hr.	—	—	
	102LS-SLEDB-G1 ¹	24V DC	0.062 A							
	102LS-SLEDG-N5 ¹	120V AC	0.022 A	Green	—	—	120,000 hr.	—	—	
	102LS-SLEDG-G1 ¹	24V DC	0.062 A							
	102LS-SLEDR-N5 ¹	120V AC	0.022 A	Red	—	—	120,000 hr.	—	—	
	102LS-SLEDR-G1 ¹	24V DC	0.062 A							
	102LS-SLEDW-N5 ¹	120V AC	0.022 A	Clear/ White	—	—	120,000 hr.	—	—	
	102LS-SLEDW-G1 ¹	24V DC	0.062 A							
	Flashing LED	102LS-FLEDA-N5 ¹	120V AC	0.022 A	Amber	—	—	120,000 hr.	—	—
		102LS-FLEDA-G1 ¹	24V DC	0.062 A						
102LS-FLEDB-N5 ¹		120V AC	0.022 A	Blue	—	—	120,000 hr.	—	—	
102LS-FLEDB-G1 ¹		24V DC	0.062 A							
102LS-FLEDG-N5 ¹		120V AC	0.022 A	Green	—	—	120,000 hr.	—	—	
102LS-FLEDG-G1 ¹		24V DC	0.062 A							
102LS-FLEDR-N5 ¹		120V AC	0.022 A	Red	—	—	120,000 hr.	—	—	
102LS-FLEDR-G1 ¹		24V DC	0.062 A							
102LS-FLEDW-N5 ¹		120V AC	0.022 A	Clear/ White	—	—	120,000 hr.	—	—	
102LS-FLEDW-G1 ¹		24V DC	0.062 A							

¹NOTE: LED light sources must be used with the corresponding color lens module (e.g., a blue LED light source, 102LS-SLEDB-G1, must be used with a blue lens, 102LM-B).

²At nominal operating voltage.

³Projected lamp life based on manufacturer's calc. lamp life @ 65 fpm and 50% duty cycle.

⁴Strobe tube life @ operating power to 75% efficiency.

⁵User supplied

Accessories		
Description		Cat. No.
Pipe Mount Flange		102PMF
Pipe Extensions (for use with Pipe Mount Flange)	4"	102MP-4
	10"	102MP-10
	15"	102MP-15

Beacons with Sounder

Multi-Status LED

108 Series

Signal Input Load Characteristics

These devices may be operated by PLCs with output characteristics that match the input load requirements of the signal.

Cat. No.	Operating Voltage	Max. Off State Leakage Current (A)	Continuous On Current (A)	Surge (Inrush / Duration)
108I-*-G1	24V DC	0.005	0.105	5 A / 1 millisecond
108I-*-N5	120V AC	0.005	0.115	30 A / 0.002 millisecond
108IP-*-G1	24V DC	0.005	0.055	5 A / 1 millisecond
108IP-*-N5	120V AC	0.005	0.045	13 A / 0.002 millisecond
108ID-*-G1	24V DC	0.005	0.055	5 A / 1 millisecond
108ID-*-N5	120V AC	0.005	0.045	13 A / 0.002 millisecond

*Letter in this position designates the colors of the LED clusters: RGA - red, green and amber or RBA - red, blue and amber

Weights and Dimensions

Cat. No.	Approx. Net Weight (lb.)	Approx. Shipping Weight (lb.)
108I-RBA-G1	0.89	1.05
108I-RBA-N5	0.89	1.05
108I-RGA-G1	0.89	1.05
108I-RGA-N5	0.89	1.05
108IP-RBA-G1	0.89	1.05
108IP-RBA-N5	0.89	1.05
108IP-RGA-G1	0.89	1.05
108IP-RGA-N5	0.89	1.05
108ID-RGA-N5	0.69	0.88
108ID-RBA-N5	0.69	0.88
108ID-RGA-G1	0.69	0.88
108ID-RBA-G1	0.69	0.88
102LM-*	0.33	0.43
102LS-FIN-G1	0.70	0.80
102LS-FINH-G1	0.70	0.80
102LS-FINH-N5	0.70	0.80
102LS-FIN-N5	0.70	0.80
102LS-FLED*-G1	0.70	0.80
102LS-FLED*-N5	0.70	0.80
102LS-SIN-G1	0.70	0.80

Weights and Dimensions

Cat. No.	Approx. Net Weight (lb.)	Approx. Shipping Weight (lb.)
102LS-SINH-G1	0.70	0.80
102LS-SINH-N5	0.70	0.80
102LS-SIN-N5	0.70	0.80
102LS-SLED*-G1	0.70	0.80
102LS-SLED*-N5	0.70	0.80
102LS-ST-G1	0.70	0.80
102LS-ST-N5	0.70	0.80
102MP-10	0.83	0.83
102MP-15	1.14	1.14
102MP-4	0.31	0.31
102PMF	0.58	0.68
102SIN-RBA-G1	1.44	1.61
102SIN-RBA-N5	1.44	1.61
102SIN-RGA-G1	1.44	1.61
102SIN-RGA-N5	1.44	1.61

*Letter in this position designates lens/LED color: A - amber, B - blue, G - green, R - red, or W - clear/white

