


# Compound leverage snips

## Shape and straight cutting snips



N <sup>o</sup>	← a →		← b →		kg	5	€
	mm	"	mm	"			
D16A	240	9 1/2	33	1 5/16	0,40	5	28,00
D16AL	240	9 1/2	33	1 5/16	0,40	5	28,00
D16A-SB	240	9 1/2	33	1 5/16	0,40	5	29,00
D16AL-SB	240	9 1/2	33	1 5/16	0,40	5	29,00




- For continuous, straight and curved cuts
- Edges with micro-serrations for slip-proof working
- Very good price to performance ratio
- Available in right- or left cutting versions

## MULTISNIP Longstyle



N <sup>o</sup>	← a →		← b →		kg	5	€
	mm	"	mm	"			
D22A	280	11	64	2 1/2	0,45	5	33,70



- For long continuous straight and large radius cuts
- Extra long cutting blades, laterally displaced for continuous cuts
- Angled cutter head for greater safety – keep the material at a distance and keep your hand out of the danger zone
- Available only in left cutting version
- On carded hang pack