



SPRINT cable glands, metric



Protection class to EN 60 529: IP 68 to 5 bar (30 min)

Protection class to DIN 40 050-T9: IP 69K






Temperature range: -40°C to 100°C, interm. up to approx. 120°C

Material:

- Cable gland: brass nickel-plated
- Clamping cage: polyamide
- Gasket: EPDM

Equipment:

- Maximum traction relief through WISKA patent lamella
- Seal-tight to enclosure rack through additional EPDM sealing ring
- Same sealing range and key width on all SPRINT-glands
- Also available with reduction insert, multiple sealing insert, special sealing insert and dust-protection gasket

Type	WISKA-No. Ni		 D mm	 mm	 mm	 SW mm	E1 mm	TL mm
EMSKV 12	10065000	50	M 12x1,5	5	3 - 7	16	18	23 - 30
EMSKV 16	10065001	50	M 16x1,5	5	4,5 - 10	20	22	26 - 34
EMSKV 20	10065002	50	M 20x1,5	6	6 - 13	24	27	29 - 37
EMSKV 25	10065003	50	M 25x1,5	7	9 - 17	29	32	33 - 42
EMSKV 32	10065004	25	M 32x1,5	8	13 - 21	36	40	36 - 44
EMSKV 40	10065005	10	M 40x1,5	8	16 - 28	46	51	44 - 55
EMSKV 50	10065006	10	M 50x1,5	9	21 - 35	55	61	51 - 62
EMSKV 63	10065007	10	M 63x1,5	10	34 - 48	68	75	56 - 67
EMSKV 75	10100865	1	M 75x1,5	12	48 - 62	82	90	67 - 81

© 2013 WISKA Hoppmann & Mulsow GmbH
 Kisdorfer Weg 28
 D-24568 Kaltenkirchen
 Phone: +49 (0)4191 / 508-100
 Fax: +49 (0)4191 / 508-209