



SAFETY DATA SHEET SAFEPAD CLEANING CLOTHS

SECTION 1: IDENTIFICATION OF THE SUBSTANCE/MIXTURE AND OF THE COMPANY/UNDERTAKING

1.1. Product identifier

Product name SAFEPAD CLEANING CLOTHS
Product No. SPA
ASPA010
ASPA100
ZA

1.2. Relevant identified uses of the substance or mixture and uses advised against

Identified uses Cleaning Product
Uses advised against At this moment in time we do not have information on use restrictions. They will be included in this safety data sheet when available

1.3. Details of the supplier of the safety data sheet

Supplier AF INTERNATIONAL. A division of HK WENTWORTH LTD
ASHBY PARK
COALFIELD WAY
ASHBY de la ZOUCH
LEICESTERSHIRE. LE65 1JR
UNITED KINGDOM
+44 (0) 1530 419600
+44 (0) 1530 416640
info@hkw.co.uk

1.4. Emergency telephone number

+44 (0)1530 419600 between 8.30am - 5.00pm Mon – Fri

SECTION 2: HAZARDS IDENTIFICATION

2.1. Classification of the substance or mixture

Classification (1999/45/EEC) Xi;R36. F;R11. R67.

2.2. Label elements

Labelling



Irritant



Highly flammable

Risk Phrases

R11	Highly flammable
R36	Irritating to eyes.
R67	Vapours may cause drowsiness and dizziness.

Safety Phrases

S9	Keep container in a well-ventilated place.
S16	Keep away from sources of ignition - No smoking.
S25	Avoid contact with eyes.
S26	In case of contact with eyes, rinse immediately with plenty of water and seek medical advice.
S51	Use only in well-ventilated areas.

2.3. Other hazards

SAFEPAD CLEANING CLOTHS

SECTION 3: COMPOSITION/INFORMATION ON INGREDIENTS

3.2. Mixtures

PROPAN-2-OL	30-60%
CAS-No.: 67-63-0	EC No.: 200-661-7
Classification (EC 1272/2008)	Classification (67/548/EEC)
Flam. Liq. 2 - H225	F;R11
Eye Irrit. 2 - H319	Xi;R36
STOT SE 3 - H336	R67

The Full Text for all R-Phrases and Hazard Statements are Displayed in Section 16.

Composition Comments

Ingredients not listed are classified as non-hazardous or at a concentration below reportable levels.

SECTION 4: FIRST AID MEASURES

4.1. Description of first aid measures

Inhalation

Move the exposed person to fresh air at once. Get medical attention if any discomfort continues.

Ingestion

Provide rest, warmth and fresh air. Immediately rinse mouth and drink plenty of water (200-300 ml). Get medical attention.

Skin contact

Remove contaminated clothing immediately and wash skin with soap and water. Get medical attention if irritation persists after washing.

Eye contact

Make sure to remove any contact lenses from the eyes before rinsing. Promptly wash eyes with plenty of water while lifting the eye lids. Continue to rinse for at least 15 minutes. Get medical attention if any discomfort continues.

4.2. Most important symptoms and effects, both acute and delayed

Inhalation.

Vapours may cause drowsiness and dizziness.

Ingestion

May cause discomfort if swallowed.

Skin contact

Prolonged contact may cause redness, irritation and dry skin.

Eye contact

May cause severe irritation to eyes.

4.3. Indication of any immediate medical attention and special treatment needed

Treat symptomatically

SECTION 5: FIREFIGHTING MEASURES

5.1. Extinguishing media

Extinguishing media

Extinguish with alcohol-resistant foam, carbon dioxide, dry powder or water fog.

Unsuitable extinguishing media

Do not use water jet as an extinguisher, as this will spread the fire.

5.2. Special hazards arising from the substance or mixture

Hazardous combustion products

Thermal decomposition or combustion may liberate carbon oxides and other toxic gases or vapours.

Specific hazards

Oxides of: Carbon.

5.3. Advice for firefighters

Protective equipment for fire-fighters

Self contained breathing apparatus and full protective clothing must be worn in case of fire.

SAFEPAD CLEANING CLOTHS

SECTION 6: ACCIDENTAL RELEASE MEASURES

6.1. Personal precautions, protective equipment and emergency procedures

Follow precautions for safe handling described in this safety data sheet. Do not smoke, use open fire or other sources of ignition. Take precautionary measures against static discharges. Provide adequate ventilation.

6.2. Environmental precautions

Do not discharge into drains, water courses or onto the ground.

6.3. Methods and material for containment and cleaning up

Absorb with inert, damp, non-combustible material, then flush area with water. Collect spillage in containers, seal securely and deliver for disposal according to local regulations.

6.4. Reference to other sections

Wear protective clothing as described in Section 8 of this safety data sheet. See section 11 for additional information on health hazards. For waste disposal, see section 13.

SECTION 7: HANDLING AND STORAGE

7.1. Precautions for safe handling

Avoid spilling, skin and eye contact. Keep away from heat, sparks and open flame. Avoid inhalation of vapours and spray mists.

7.2. Conditions for safe storage, including any incompatibilities

Keep containers tightly closed. Keep in original container. Keep away from heat, sparks and open flame.

Storage Class

Flammable liquid storage.

7.3. Specific end use(s)

The identified uses for this product are detailed in Section 1.2.

SECTION 8: EXPOSURE CONTROLS/PERSONAL PROTECTION

8.1. Control parameters

Name	STD	TWA - 8 Hrs		STEL - 15 Min		Notes
PROPAN-2-OL	WEL	400 ppm	999 mg/m ³	500 ppm	1250 mg/m ³	

WEL = Workplace Exposure Limit.

PROPAN-2-OL (CAS: 67-63-0)

DNEL

Industry	Dermal	888	mg/kg/day
Industry	Inhalation.	500	mg/m ³
Consumer	Dermal	319	mg/kg/day
Consumer	Inhalation.	89	mg/m ³
Consumer	Oral	26	mg/kg/day

PNEC

Freshwater	140.9	mg/l	
Marinewater	140.9	mg/l	
Sediment	552	mg/kg	
Soil	28	mg/kg	

8.2. Exposure controls

Protective equipment



Process conditions

Use engineering controls to reduce air contamination to permissible exposure level. Provide eyewash station.

SAFEPAD CLEANING CLOTHS

Engineering measures

Provide adequate ventilation, including appropriate local extraction, to ensure that the defined occupational exposure limit is not exceeded.

Respiratory equipment

No specific recommendation made, but respiratory protection must be used if the general level exceeds the recommended occupational exposure limit. Use respiratory equipment with combination filter, type A2/P3. EN14387

Hand protection

Use protective gloves. The most suitable glove must be chosen in consultation with the gloves supplier, who can inform about the breakthrough time of the glove material. Butyl rubber gloves are recommended. Gloves should conform to EN374

Eye protection

Wear approved, tight fitting safety glasses where splashing is probable. EN166

Other Protection

Wear appropriate clothing to prevent any possibility of liquid contact and repeated or prolonged vapour contact.

Hygiene measures

DO NOT SMOKE IN WORK AREA! Wash hands at the end of each work shift and before eating, smoking and using the toilet. Wash promptly with soap & water if skin becomes contaminated. When using do not eat, drink or smoke. Eating, smoking and water fountains prohibited in immediate work area.

SECTION 9: PHYSICAL AND CHEMICAL PROPERTIES

9.1. Information on basic physical and chemical properties

Appearance	Impregnated cloth, card or tissue
Colour	Colourless.
Solubility	Miscible with water
Initial boiling point and boiling range	82 (179.6 F)
Melting point (°C)	-89 (-128.2 F)
Relative density	0.780 @ 20 °c (68 F)
Vapour density (air=1)	2.8
Vapour pressure	4.16 kPa @ 20 °c (68 F)
Evaporation rate	2.93
Viscosity	3.06 cSt @ 20 °c (68 F)
Flash point	12 (53.6 F) CC (Closed cup).
Auto Ignition Temperature (°C)	425 (797 F)
Flammability Limit - Lower(%)	2.3
Flammability Limit - Upper(%)	12

9.2. Other information

SECTION 10: STABILITY AND REACTIVITY

10.1. Reactivity

Reaction with: Strong oxidising agents.

10.2. Chemical stability

Stable under normal temperature conditions and recommended use.

10.3. Possibility of hazardous reactions

Hazardous Polymerisation

Will not polymerise.

10.4. Conditions to avoid

Avoid heat, flames and other sources of ignition. Avoid excessive heat for prolonged periods of time.

10.5. Incompatible materials

Materials To Avoid

Strong oxidising substances.

10.6. Hazardous decomposition products

Thermal decomposition or combustion may liberate carbon oxides and other toxic gases or vapours.

SECTION 11: TOXICOLOGICAL INFORMATION

SAFEPAD CLEANING CLOTHS

11.1. Information on toxicological effects

Acute toxicity:

Acute Toxicity (Oral LD50)

5280 mg/kg Rat

Acute Toxicity (Dermal LD50)

12800 mg/kg Rabbit

Acute Toxicity (Inhalation LC50)

72.6 mg/l (vapours) Rat 4 hours

Respiratory or skin sensitisation:

Skin sensitisation

Buehler test: Guinea Pig

Not Sensitising.

Inhalation

May cause irritation to the respiratory system. Vapours may cause drowsiness and dizziness.

Ingestion

May cause stomach pain or vomiting. May cause nausea, headache, dizziness and intoxication.

Skin contact

Irritating to skin. Prolonged contact may cause dryness of the skin. Acts as a defatting agent on skin. May cause cracking of skin, and eczema.

Eye contact

Irritating to eyes.

Route of entry

Skin absorption. Ingestion. Skin and/or eye contact.

Target Organs

Central nervous system Eyes Respiratory system, lungs Skin

Medical Symptoms

Irritation of eyes and mucous membranes. Dilated pupils. Rhinitis (inflammation of the nasal mucous membranes). Upper respiratory irritation. General respiratory distress, unproductive cough. Skin irritation. Central nervous system depression. Drowsiness, dizziness, disorientation, vertigo.

Toxicological information on ingredients.

PROPAN-2-OL (CAS: 67-63-0)

Acute toxicity:

Acute Toxicity (Oral LD50)

5280 mg/kg Rat

Acute Toxicity (Dermal LD50)

12800 mg/kg Rabbit

Acute Toxicity (Inhalation LC50)

72.6 mg/l (vapours) Rat 4 hours

SECTION 12: ECOLOGICAL INFORMATION

Ecotoxicity

The product components are not classified as environmentally hazardous. However, this does not exclude the possibility that large or frequent spills can have a harmful or damaging effect on the environment.

12.1. Toxicity

SAFEPAD CLEANING CLOTHS

Acute Fish Toxicity

Not considered toxic to fish.

Acute Toxicity - Fish

LC50 96 hours 9640 mg/l Pimephales promelas (Fat-head Minnow)

Acute Toxicity - Aquatic Invertebrates

EC50 48 hours 13299 mg/l Daphnia magna

Acute Toxicity - Aquatic Plants

EC50 72 hours > 1.000 mg/l Scenedesmus subspicatus

Acute Toxicity - Microorganisms

EC50 > 1.000 mg/l Activated sludge

Ecological information on ingredients.

PROPAN-2-OL (CAS: 67-63-0)

Acute Toxicity - Fish

LC50 96 hours 9640 mg/l Pimephales promelas (Fat-head Minnow)

Acute Toxicity - Aquatic Invertebrates

EC50 48 hours 13299 mg/l Daphnia magna

Acute Toxicity - Aquatic Plants

EC50 72 hours > 1.000 mg/l Scenedesmus subspicatus

Acute Toxicity - Microorganisms

EC50 > 1.000 mg/l Activated sludge

12.2. Persistence and degradability

Degradability

The product is biodegradable.

12.3. Bioaccumulative potential

Bioaccumulative potential

Will not bio-accumulate.

12.4. Mobility in soil

Mobility:

The product is soluble in water.

12.5. Results of PBT and vPvB assessment

This product does not contain any PBT or vPvB substances.

12.6. Other adverse effects

Not determined.

SECTION 13: DISPOSAL CONSIDERATIONS

General information

Waste is classified as hazardous waste. Disposal to licensed waste disposal site in accordance with the local Waste Disposal Authority. Do not puncture or incinerate even when empty. Rags and the like, moistened with flammable liquids, must be discarded into designated fireproof bucket.

13.1. Waste treatment methods

Dispose of waste and residues in accordance with local authority requirements.

SECTION 14: TRANSPORT INFORMATION

Road Transport Notes	Exempt from regulations through Special Provision 216
Sea Transport Notes	Exempt from regulations through Special Provision 216
Air Transport Notes	Exempt from regulation through Special Provision A46

14.1. UN number

UN No. (ADR/RID/ADN)	3175
UN No. (IMDG)	3175

SAFEPAD CLEANING CLOTHS

UN No. (ICAO) 3175

14.2. UN proper shipping name

Proper Shipping Name SOLIDS CONTAINING FLAMMABLE LIQUID, N.O.S.

14.3. Transport hazard class(es)

ADR/RID/ADN Class 4.1

ADR/RID/ADN Class Class 4.1: Flammable solids, self-reactive substances and solid desensitized explosives.

ADR Label No. 4.1

IMDG Class 4.1

ICAO Class/Division 4.1

Transport Labels

**14.4. Packing group**

ADR/RID/ADN Packing group II

IMDG Packing group II

ICAO Packing group II

14.5. Environmental hazards

Environmentally Hazardous Substance/Marine Pollutant

No.

14.6. Special precautions for user

EMS F-A, S-I

Emergency Action Code 1Z

Hazard No. (ADR) 40

Tunnel Restriction Code (E)

14.7. Transport in bulk according to Annex II of MARPOL73/78 and the IBC Code

Not applicable.

SECTION 15: REGULATORY INFORMATION**15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture****Uk Regulatory References**

Chemicals (Hazard Information & Packaging) Regulations.

The Control of Substances Hazardous to Health Regulations 2002 (S.I 2002 No. 2677) with amendments.

Environmental Listing

Rivers (Prevention of Pollution) Act 1961. Control of Pollution (Special Waste Regulations) Act 1980. Control of Pollution Act 1974.

Approved Code Of Practice

Classification and Labelling of Substances and Preparations Dangerous for Supply. Safety Data Sheets for Substances and Preparations.

Guidance Notes

Workplace Exposure Limits EH40.

EU Legislation

Dangerous Substance Directive 67/548/EEC.

Dangerous Preparations Directive 1999/45/EC.

System of specific information relating to Dangerous Preparations. 2001/58/EC.

SAFEPAD CLEANING CLOTHS

Commission Directive 2000/39/EC of 8 June 2000 establishing a first list of indicative occupational exposure limit values in implementation of Council Directive 98/24/EC on the protection of the health and safety of workers from the risks related to chemical agents at work.

Regulation (EC) No 1907/2006 of the European Parliament and of the Council of 18 December 2006 concerning the Registration, Evaluation, Authorisation and Restriction of Chemicals (REACH), establishing a European Chemicals Agency, amending Directive 1999/45/EC and repealing Council Regulation (EEC) No 793/93 and Commission Regulation (EC) No 1488/94 as well as Council Directive 76/769/EEC and Commission Directives 91/155/EEC, 93/67/EEC, 93/105/EC and 2000/21/EC, including amendments.

Regulation (EC) No 1272/2008 of the European Parliament and of the Council of 16 December 2008 on classification, labelling and packaging of substances and mixtures, amending and repealing Directives 67/548/EEC and 1999/45/EC, and amending Regulation (EC) No 1907/2006 with amendments.

Authorisations (Title VII Regulation 1907/2006)

No specific authorisations are noted for this product.

Restrictions (Title VIII Regulation 1907/2006)

No specific restrictions of use are noted for this product.

15.2. Chemical Safety Assessment

SECTION 16: OTHER INFORMATION

Revision Comments

Revised in accordance with CHIP3 and EU Directives 1999/45/EC and 2001/58/EC

Issued By Helen O'Reilly

Revision Date JULY 2012

Revision 4

SDS No. 11039

Risk Phrases In Full

R11 Highly flammable

R36 Irritating to eyes.

R67 Vapours may cause drowsiness and dizziness.

Hazard Statements In Full

H222 Extremely flammable aerosol.

H225 Highly flammable liquid and vapour.

H319 Causes serious eye irritation.

H336 May cause drowsiness or dizziness.

Disclaimer

This information relates only to the specific material designated and may not be valid for such material used in combination with any other materials or in any process. Such information is, to the best of the company's knowledge and belief, accurate and reliable as of the date indicated. However, no warranty guarantee or representation is made to its accuracy, reliability or completeness. It is the user's responsibility to satisfy himself as to the suitability of such information for his own particular use.