

Item no.: 281-530
Product description: RAIL-MOUNTED QUADRUPLE DECK TERMINAL BLOCK
Rail-mounted terminal blocks for fast electric motor wiring L1 -
L2 - L3 - PE



Produkt kann von Bild abweichen / product may differ

Packing unit 50 pieces

RoHS compliant

Cross section [AWG]	28 - 28 AWG
Cross section [mm ²]	0.08 - 4 mm ²
Product group	1 (Rail Mounted Terminal Blocks)
Number of levels	4
Cross section [mm ²]	0.08 - 2.5 mm ²
Cross section [AWG]	28 - 12 AWG
Connection method	CAGE CLAMP® CONNECTION
Measured voltage EN	400 V
Measured shock voltage	6 kV
Pollution degree	3
Current intensity EN	20 A
Current intensity EN	25 A
Weight	23.332 g
Color	gray
Wiring type	Front-entry
No. of connection Points	7
No. of potentials	4
Height	62.5 mm

Height	2.46 in
Width	6 mm
Width	0.236 in
Depth	100 mm



Depth	3.94 in
Strip length from	8 mm
Strip length to	9 mm
Strip length	0.33 in
Mounting	TS 35



Item no.	Admission office	Approval no.	Voltage [V]	Current [A]	Cross section [mm ²]
281-530	ABS	05-HG476175/3-PDA	400	25	4,0
281-530	BV	07436/C0	400	25	4,0
281-530	CCA	NL5591/1	400	25	4,0
281-530	CSA	154112-1505034	300	25	28-12
281-530	cURus	E45172	600	20	28-12
281-530	GL	17295-00HH	400	25	4,0
281-530	KEMA	2076376.01	400	25	4
281-530	LR	91/20112(E6)	400	25	4,0
281-530	PRS	TE/1718/880590/08	400	25	4,0
281-530	RMR	11130002	400	25	4,0

Sorting criteria: admission office - approval number

© WAGO Kontakttechnik GmbH & Co. KG

Specifications are subject to changes and errors may be expected